


## Mounting Plates Types MP and MSMP

### Features and Benefits


Allowing multiple cables to be run in parallel these mounting plates are simply fixed by two screws. The cables are attached to the mounting plate by using a cable tie through any combination of the available slots.

### Application

Many applications require each cable run to be firmly held in place but separately from adjacent cable runs (example - control cabinets, machinery and military systems). The MP series of mounts help achieve this.



Mounting Plates Types MP and MSMP



Mounting Plates Types MP and MSMP

| Material Data         |                                                  |
|-----------------------|--------------------------------------------------|
| Material              | Polyamide 6.6 (PA66)                             |
| Colour                | Black (BK), Natural (NA)                         |
| Operating Temperature | -40 °C to +85 °C Continuous, (+105 °C for 500 h) |
| Flammability          | UL94 V2                                          |



Technical Table


| Article-No. | Type  | Length (L) | Width (W) | Height (H) | Fixing Hole Ø (FH) | Fixing Hole Centres (F) | Hole Size (HS) | Strap Width max. (G) | Material | No. of bundles |
|-------------|-------|------------|-----------|------------|--------------------|-------------------------|----------------|----------------------|----------|----------------|
| 151-24219   | MP2M3 | 76.2       | 12.7      | 3.2        | 3.5                | 31.8                    | 6.4            | 5.2                  | PA66     | 2              |
| 151-24319   | MP3M3 | 108.0      | 12.7      | 3.2        | 3.7                | 31.8                    | 6.4            | 5.2                  | PA66     | 3              |
| 151-24419   | MP4M3 | 139.8      | 12.7      | 3.2        | 3.7                | 31.8                    | 6.4            | 5.2                  | PA66     | 4              |
| 150-83499   | MSMP4 | 167.0      | 15.9      | 5.2        | 5.1                | 19                      | 7.6            | 8.2                  | PA66     | 4              |
| 151-24519   | MP5M3 | 171.6      | 12.7      | 3.2        | 3.7                | 31.8                    | 6.4            | 5.2                  | PA66     | 5              |
| 151-25519   | MSMP5 | 204.0      | 15.7      | 5.3        | 5.1                | 38                      | 7.7            | 8.2                  | PA66     | 5              |
| 151-25619   | MSMP6 | 242.0      | 15.7      | 5.3        | 5.1                | 38                      | 7.7            | 8.2                  | PA66     | 6              |

All dimensions in mm. Subject to technical changes.


## Cable Fixing Accessory TM1SF

### Features and Benefits

The TM1SF mount is ideal for applications with restricted access, or where space-saving is required. The arrowhead simply pushes into a pre-drilled or pre-punched hole giving a very secure fixing.



TM1SF Fixing Base



TM1SF Fixing Base

Technical Table

| Article-No. | Type  | Length (L) | Width (W) | Height (H) | Height (H2) | Fixing Hole Ø (FH) | Panel Thickness max. | Strap Width max. (G) | Material | Colour       |
|-------------|-------|------------|-----------|------------|-------------|--------------------|----------------------|----------------------|----------|--------------|
| 151-40119   | TM1SF | 10.2       | 7.6       | 15.6       | 4.6         | 6.3                | 3.4                  | 5.2                  | PA66     | Natural (NA) |

All dimensions in mm. Subject to technical changes.



Please Note for Product Specific Approvals please refer to the Appendix