





RECOMMENDED PANEL CUT-OUT




PRODUCT NO	NUMBER OF POS.	LOADED POSITION	HSG COLOR	PLATING
61885-0661	6	ALL POS.	BLACK	5u" Au + high performance lubricant
61885-0641		2,3,4,5		
61885-0621		3,4		
61885-0661LF		ALL POS.		
61885-0641LF		2,3,4,5		
61885-0621LF		3,4		




LEAD FREE PRODUCT NO.

NOTES:


1. RECOMMENDED P.C.B. THICKNESS 1.60 MM
2. HOUSING MAT'L: NYLON 66, 25% GLASS REINFORCED, COLOR: SEE TABLE
3. CONTACTS: PHOS BRONZE ALLOY UNS-C51000, Ø 0.460 ROUND WIRE, PLATING SEE TABLE.
- ④ METAL SHELL MATERIAL:
COPPER ALLOY, 0.20MM THICK.
FINISH: FOR 61885-XXXX TIN-LEAD 100 u" THICK .
FOR 61885-XXXXLF PURE TIN 80 u" THICK .
5. PACKAGING PER GES-14-361, USING TUBE
6. IF LF P/N THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED INS GS-22-008
7. IF LF P/N THE HOUSING WILL WITHSTAND EXPOSURE TO 260° PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.60mm MINIMUM THICK CIRCUIT BOARD
8. IF LF P/N PACKAGING MEETS GS-14-920 SPECIFICATION



RECOMMENDED P.C.B. LAOUT



POS. NO. CONFIGURATION



mat'l. code				surface		tolerance		projection		product family					
				ISO1302 ✓		ISO1101 ISO406				MOD JACK					
ltr		ecn		nodr		date		tolerances unless otherwise specified		title					
C	T80510		MW		11/18/98		angle	0.X±0.3			LOW PROFILE PCB III 6 POS MOD JACK, FULLY SHIELDED				
D	T03-0443		WL		10/06/03			0.XX±0.15							
E	N04-0125		YS		12/15/04			0.XXX±0.05							
F	ELX-N-011021		SH MM		03/25/12		line lead	C M HSU 03/27/97			dwg no		sheet 1 of 1	size	
								engr TONY CHIEN 03/27/97			61885		A4		
								chr TONY CHIEN 03/27/97							
								appd JENN TSAO 03/27/97			type Product Customer Drawing				
sheet index		revision		F											
sheet 1															