









Copyright FCI.



rev	ecn no	dr	date
A	N07-0076	TAI	03/19/07
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ☒		tolerance std ASME Y14.5		projection 		MM 			
			TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	KENNY TAI	05/19/05	ANGULAR	LINEAR	0.X	±.5	size A4	Scale 1.000				
Eng	KENNY TAI	05/19/05			0.XX	±.3						
Chr	KENNY TAI	05/19/05	0°	±2°	0.XXX	±	ECN		N07-0076			
Appr	PAUL WANG	05/19/05	Product family					Spec ref		*		
			title CARD PUSH, BELOW MOUNT EXPRESSCARD HOST MECH.				dwg no 10056423		Rev. A			
			catalog									
			PDM: Rev A				10056423		CUSTOMER		sheet 1 of 2	
			Sales									

PART NO.	MOUNTING	STAND-OFF	DIM A	DIM B	DIM C	HOST CONN P/N	PRODUCT SPEC.	PACKING SPEC.
10056423-18BLF	BELOW	1.8MM	1.8	7.7	2.75	10056422-X18BXXLF	GS-12-301	GS-14-295
10056423-22BLF	BELOW	2.2MM	2.2	8.1	3.15	10056422-X22BXXLF	GS-12-301	GS-14-295



 MOUNTING PARTS HEIGHT
SEE NOTE 6

NOTE:

1. 2 M2*0.4P SCREWS WITH WASHER ARE REQUIRED.
2. SHOW DIMENSION AFTER FASTENED TO PCB.
3. SEE HOST CONNECTOR DRAWINGS FOR PCB LAYOUT DETAIL.
4. RECOMMENDED TIGHTING TORQUE 1.6~1.8 KGF-CM.
5. SEE DETAIL 2 FOR RECOMMENDED SCREW LENGTH.
6. 1.8MM FOR 2.2MM STAND-OFF & 1.4MM FOR 1.8MM STAND-OFF

	title	CARD PUSH, BELOW MOUNT	dwg no	10056423	Rev.	A
	EXPRESSCARD HOST MECH.					
catalog	PDM: Rev:A	10056423	CUSTOMER	sheet 2 of 2	Printed: Oct 12, 2010	