

## Relay Module - RIF-1-RSC-LV-24AC/2X21AU - 2903345

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Pre-assembled relay module with screw connection, consisting of: relay base, multi-layer contact relay, plug-in display/interference suppression module, and retaining bracket. Contact type: 2 changeover contacts. Input voltage: 24 V AC

RoHS

### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 10 pc                                                                                                   |
| GTIN         | <br>4 046356 732789 |
| GTIN         | 4046356732789                                                                                           |

### Technical data

#### Note

|                         |                                                                           |
|-------------------------|---------------------------------------------------------------------------|
| Utilization restriction | EMC: class A product, see manufacturer's declaration in the download area |
|-------------------------|---------------------------------------------------------------------------|

#### Dimensions

|        |       |
|--------|-------|
| Width  | 16 mm |
| Height | 89 mm |
| Depth  | 75 mm |

#### Ambient conditions

|                                         |                  |
|-----------------------------------------|------------------|
| Ambient temperature (operation)         | -40 °C ... 50 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

#### Coil side

|                                           |                |
|-------------------------------------------|----------------|
| Nominal input voltage $U_N$               | 24 V AC        |
| Input voltage range in reference to $U_N$ | see diagram    |
| Mains frequency                           | 50/60 Hz       |
| Typical input current at $U_N$            | 33 mA          |
| Typical response time                     | 3 ms ... 12 ms |
| Typical release time range                | 3 ms ... 20 ms |

# Relay Module - RIF-1-RSC-LV-24AC/2X21AU - 2903345

## Technical data

### Coil side

|                           |            |
|---------------------------|------------|
| Coil voltage              | 24 V AC    |
| Protective circuit        | Varistor   |
| Operating voltage display | Yellow LED |

### Contact side

|                                       |                        |
|---------------------------------------|------------------------|
| Contact type                          | 2 PDT                  |
| Type of switch contact                | Single contact         |
| Contact material                      | AgNi, hard gold-plated |
| Maximum switching voltage             | 30 V AC                |
|                                       | 36 V DC                |
| Minimum switching voltage             | 100 mV (at 10 mA)      |
| Min. switching current                | 1 mA (at 24 V)         |
| Maximum inrush current                | 50 mA                  |
| Limiting continuous current           | 50 mA                  |
| Interrupting rating (ohmic load) max. | 1.2 W (at 24 V DC)     |

### Contact side (with destroyed gold layer)

|                                       |                                                                  |
|---------------------------------------|------------------------------------------------------------------|
| Contact material                      | AgNi                                                             |
| Note                                  | the following values are applicable if a gold layer is destroyed |
| Maximum switching voltage             | 250 V AC/DC                                                      |
| Minimum switching voltage             | 5 V (at 10 mA)                                                   |
| Limiting continuous current           | 12 A (20 ms, N/O contact)                                        |
| Min. switching current                | 10 mA (At 5 V)                                                   |
| Interrupting rating (ohmic load) max. | 192 W (at 24 V DC)                                               |
|                                       | 96 W (at 48 V DC)                                                |
|                                       | 60 W (at 60 V DC)                                                |
|                                       | 44 W (at 110 V DC)                                               |
|                                       | 57 W (at 220 V DC)                                               |
|                                       | 2000 VA (for 250 V AC)                                           |
| Switching capacity                    | 2 A (at 24 V, DC13)                                              |
|                                       | 0.2 A (at 110 V, DC13)                                           |
|                                       | 0.2 A (at 250 V, DC13)                                           |
|                                       | 2 A (at 24 V, AC15)                                              |
|                                       | 2 A (at 120 V, AC15)                                             |
|                                       | 2 A (at 250 V, AC15)                                             |

### Connection data input side

|                                                                      |                     |
|----------------------------------------------------------------------|---------------------|
| Connection name                                                      | Coil side           |
| Connection method                                                    | Screw connection    |
| Stripping length                                                     | 8 mm                |
| Conductor cross section solid                                        | 0.5 mm² ... 4 mm²   |
| Conductor cross-section solid (2 conductors with same cross section) | 0.5 mm² ... 2.5 mm² |

# Relay Module - RIF-1-RSC-LV-24AC/2X21AU - 2903345

## Technical data

### Connection data input side

|                                                                         |                                                                                |
|-------------------------------------------------------------------------|--------------------------------------------------------------------------------|
| Conductor cross section flexible                                        | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>                                      |
|                                                                         | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup> (Ferrule with plastic sleeve)        |
| Conductor cross section flexible (2 conductors with same cross section) | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                                    |
|                                                                         | 0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (TWIN ferrule with plastic sleeve) |
| Conductor cross section AWG                                             | 20 ... 10 (solid)                                                              |
|                                                                         | 20 ... 12 (flexible)                                                           |
| Torque                                                                  | 0.5 Nm ... 0.6 Nm                                                              |

### Connection data output side

|                                                                         |                                                                                |
|-------------------------------------------------------------------------|--------------------------------------------------------------------------------|
| Connection name                                                         | Contact side                                                                   |
| Connection method                                                       | Screw connection                                                               |
| Stripping length                                                        | 8 mm                                                                           |
| Conductor cross section solid                                           | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>                                      |
| Conductor cross-section solid (2 conductors with same cross section)    | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                                    |
| Conductor cross section flexible                                        | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>                                      |
|                                                                         | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup> (Ferrule with plastic sleeve)        |
| Conductor cross section flexible (2 conductors with same cross section) | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                                    |
|                                                                         | 0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (TWIN ferrule with plastic sleeve) |
| Conductor cross section AWG                                             | 20 ... 10 (solid)                                                              |
|                                                                         | 20 ... 12 (flexible)                                                           |
| Torque                                                                  | 0.5 Nm ... 0.6 Nm                                                              |

## General

|                                          |                                                                                                             |
|------------------------------------------|-------------------------------------------------------------------------------------------------------------|
| Type of note                             | Notes on operation                                                                                          |
| Note                                     | FBS 2-6... plug-in bridge for the input side (A2) and FBS-2-8... plug-in bridge for the output side (11/21) |
| Test voltage relay winding/relay contact | 4 kV <sub>rms</sub> (50 Hz, 1 min.)                                                                         |
| Test voltage PDT/PDT                     | 2.5 kV <sub>rms</sub> (50 Hz, 1 min.)                                                                       |
| Operating mode                           | 100% operating factor                                                                                       |
| Degree of protection                     | IP20 (Relay base)                                                                                           |
|                                          | RT III (Relay)                                                                                              |
| Mechanical service life                  | approx. 10 <sup>7</sup> cycles                                                                              |
| Mounting position                        | any                                                                                                         |
| Assembly instructions                    | In rows with zero spacing                                                                                   |

## Standards and Regulations

|                                        |                                                                                                 |
|----------------------------------------|-------------------------------------------------------------------------------------------------|
| Standards/regulations                  | DIN EN 50178                                                                                    |
| Rated surge voltage                    | 6 kV                                                                                            |
| Insulation                             | Safe isolation, basic insulation, and 4 kV rated surge voltage between all changeover contacts. |
| Degree of pollution                    | 2                                                                                               |
| Overvoltage category                   | III                                                                                             |
| Flammability rating according to UL 94 | V2                                                                                              |

Relay Module - RIF-1-RSC-LV-24AC/2X21AU - 2903345


Technical data

Environmental Product Compliance

|            |                                                                                                     |
|------------|-----------------------------------------------------------------------------------------------------|
| China RoHS | Environmentally Friendly Use Period = 50                                                            |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |


Drawings

Circuit diagram




AC coils

Diagram




Operating voltage range

Diagram



Interrupting rating


Diagram




Contact derating

## Relay Module - RIF-1-RSC-LV-24AC/2X21AU - 2903345

Diagram



Diagram



Electrical service life

Service life reduction factor

### Articles in set

Relay base - RIF-1-BSC/2X21 - 2900930



RIF-1... relay base, for miniature power relay with 1 or 2 changeover contacts or identical solid-state relays, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

Single relay - REL-MR- 24AC/21-21AU - 2961464



Plug-in miniature power relay, with multi-layer gold contact, 2 PDTs, input voltage 24 V AC

Plug-in module - RIF-LV-12-24 UC - 2900942



Plug-in module, for mounting on RIF-1, RIF-2, RIF-3, and RIF-4, with varistor and yellow LED, input voltage: 12 ... 24 V AC/DC  $\pm 20\%$

Retaining bracket - RIF-RH-1 - 2900953



Relay retaining bracket, with ejector function and holder for marking material, suitable for RIF-1 relay base, for 16 mm tall miniature power relay and solid-state relay

## Relay Module - RIF-1-RSC-LV-24AC/2X21AU - 2903345

### Articles in set

---

### Approvals

#### Approvals

---

#### Approvals

DNV GL / EAC

---

#### Ex Approvals

---

### Approval details

|        |                                                                           |            |
|--------|---------------------------------------------------------------------------|------------|
| DNV GL | <a href="http://exchange.dnv.com/tari/">http://exchange.dnv.com/tari/</a> | TAA000018V |
|--------|---------------------------------------------------------------------------|------------|

|     |                                                                                     |                          |
|-----|-------------------------------------------------------------------------------------|--------------------------|
| EAC |  | RU C-<br>DE.A*30.B.01082 |
|-----|-------------------------------------------------------------------------------------|--------------------------|

---

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>