

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1885	A	RELEASED	BYF	02/08/06	HO	2/6/06	JWM	2/6/06

Description: Plastic, PNP, TO-220 power transistor General purpose amplifier and switching applications



Features:

- Collector Emitter Saturation Voltage $I_C = 1A$, $I_B = 0.2A$, $V_{CE} = 0.7V$ (Max)
- D.C. Current Gain $I_C = 2A$, $V_{CE} = 4V$ $h_{FE} = 40$ (Min)

Absolute Maximum Ratings:

- Collector-Base Voltage, $V_{CBO} = 115V$
- Collector-Emitter Voltage, $V_{CEO} = 100V$
- Emitter-Base Voltage, $V_{EBO} = 5V$
- Continuous Collector Current, $I_C = 2A$
- Base Current, I_B
- Total Device Dissipation ($T_C = +25^\circ C$), $P_D = 30W$
Derate above $25^\circ C = 0.24mW/^\circ C$
- Operating Junction Temperature Range, $T_J = -65^\circ C$ to $+150^\circ C$
- Storage Temperature Range, $T_{stg} = -65^\circ C$ to $+150^\circ C$

Electrical Characteristics: ($T_C = +25^\circ C$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Max	Unit
-----------	--------	-----------------	-----	-----	------

OFF Characteristics

Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C = 30mA$, $I_B = 0$ (Note 1)	100	—	V
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	$I_C = 1mA$, $I_E = 0$	115	—	V
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	$I_E = 1mA$, $I_C = 0$	5	—	V
Collector Cut-Off Current	I_{CES}	$V_{CE} = 100V$, $V_{BE} = 0$	—	0.2	mA
	I_{CEO}	$V_{CB} = 60V$, $I_B = 0$	—	0.3	mA
Emitter Cut-Off Current	I_{EBO}	$V_{EB} = 5V$, $I_C = 0$	—	1	mA

ON Characteristics (Note 1)



DC Current Gain	h_{FE}	$V_{CE} = 4V$, $I_C = 0.2A$	40	—	—
		$V_{CE} = 4V$, $I_C = 1A$	15	—	—
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 1A$, $I_B = 0.2A$	—	0.7	V
Base-Emitter Saturation Voltage	$V_{BE(on)}$	$I_C = 1A$, $V_{CE} = 4V$	—	1.3	V

Small-Signal Characteristics

Current Gain-Bandwidth Product	f_T	$V_{CE} = 10V$, $I_C = 0.2A$, $f = 1MHz$	3	—	MHz
Small-Signal Current Gain	h_{fe}	$V_{CE} = 10V$, $I_C = 0.2A$, $f = 1kHz$	20	—	—

Note 1. Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 2\%$.

Dimensions	A	B	C	D	E	F	G	H	J	K	L	M	N	O
Min.	14.42	9.63	3.56	—	1.15	3.75	2.29	2.54	—	12.70	2.80	2.03	—	7*
Max.	16.51	10.67	4.83	0.90	1.40	3.88	2.79	3.43	0.56	14.73	4.07	2.92	31.24	



Pin Configuration:

1. Base
2. Collector
3. Emitter
4. Collector

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:
BASAM YOUSIF
02/08/06
CHECKED BY:
HISHAM ODISH
2/6/06
APPROVED BY:
JEEF MCVICKER
2/6/06

DRAWING TITLE:
General Purpose Power Transistor, Plastic, TO-220, PNP
SIZE DWG. NO. ELECTRONIC FILE REV
A BD240C 02H2178.DWG A
SCALE: NTS U.O.M.: MILLIMETERS SHEET: 1 OF 1