






REV.	DATE	ECR NO.	DESCRIPTION
NC	09/07/08	—	INITIAL RELEASE
A	12/07/08	—	ADD CRIMP NOTES



RECOMMENDED CABLE
STRIPPING DIM'S



NOTES:

1. CRIMPED FERRULE HEX CRIMP SIZE .151" [3.83]
2. CONTACT PIN TO SOLDER.

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex					
8						DRAWN	GRS						12/07/08
7						CHECKED							
6					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm	ISSUED		PART DESCRIPTION F BULKHEAD CRIMP JACK (FOR RG-179 DOUBLE BRAID CABLE)					
5	FERRULE	BRASS	TIN LEAD	1		SHEET	1 OF 1						
4	INSULATOR	P.P.	NATURAL	1				PART NO. 222167-10					
3	CONTACT PIN	BER. COPPER	BRT. TIN	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”								
2	INSULATOR	P.P.	NATURAL	1				DWG. NO. 222167-10.DWG					
1	BODY	BRASS	TIN LEAD	1									
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	C:/222/222167-10.DWG	REV.	A	SIZE	A	SCALE	NA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[222167-10](#)