


THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION
ALL RIGHTS RESERVED.

© COPYRIGHT - By -


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G2	REVISED PER ECO-11-005027	11MAR11	RK	HMR
	G3	REVISED PER ECO-17-004099	24AUG2017	BDA	DR

AMP WIRE RANGE	 E13288 Listed
1/0 AWG SOLID OR STRANDED	1/0 AWG STRANDED
 LR7189 Certified	MILITARY P/N AND CLASS 
1/0 AWG SOLID OR STRANDED	MS 20659-118 CLASS 2

-  TIN PL 0.00254[.000100] MIN EXT. THK
PER ASTM B-545
- 2 NOTE DELETED



	-	-	CLEANED	COPPER ASTM B-152 1.78 ±0.08 [.070 ±.003] ANNEALED	2-321868-2
	50	LOOSE PIECE			321868
	QTY.	PACKAGE TYPE	FINISH	MATERIAL	PART NUMBER

MAX RECOMMENDED OPERATING TEMPERATURE: 170°[338°F]C	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 8/30/91		TE Connectivity			
			CHK RD HEIM 9/30/91					
VOLTAGE RATING: N/A	DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD AJ KAUFMAN 9/30/91	NAME TERMINAL, RING TONGUE, SOLISTRAND WIRE SIZE 50.0mm2 [1/0] AWG			
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.13(.005) 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC —				
MATERIAL SEE TABLE		FINISH SEE TABLE		APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO —
				A3	00779	C=321868		
CIRCULAR MIL AREA: 42.4–60.6mm² [83,700–118,500] SOLID OR STRANDED			CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1	REV G3