



## General Specifications

Motor Protection: Auto Restart / Polarity Protection  
Insulation Resistance: 10M Ohm or over with a DC500V Megger  
Dielectric Withstand Voltage: AC 700V 1st  
Allowable Ambient Temperature Range:  
B70 Class: -10 degree C ~ +60 degree C (Operating)  
B10 ~ B60 Class: -10 degree C ~ +70 degree C (Operating)  
All Class: -40 degree C ~ +70 degree C (Storage)  
(non-condensing environment)  
(non-condensing environment)

**order part 3110KL-04W-B50-P00 Ball Bearing Fan DC Fans**




### 3110KL panel cut out




## Material

Casing: Plastic (Black) UL94V-0  
Impeller: Plastic (Black) UL94V-0  
Lead Wire: UL1007, AWG24, +Red, -Black

### 3110KL characteristic curve



### 3110KL product drawing



## Detailed Specifications

**Expected Life:** 25 degree C 100,000 Hours (E00) 25 degree C 70,000 Hours (D00)

**DC Fan:** Ball Bearing Fan

**Nominal Voltage:** 12[V]

**Operating Voltage Lower:** 6[V]

**Operating Voltage Upper:** 13.8[V]

**Current:** 0.23[A]

**Input Power:** 2.76[W]

**Speed:** 3250[ $\text{min}^{-1}$ ]

**Max. Air Flow:** 1.1[m<sup>3</sup>/min]

**Max. Air Flow:** 38.8[CFM]

**Max. Static Pressure:** 37.2[Pa]

**Max. Static Pressure:** 0.15[In H<sub>2</sub>O]

**Noise:** 34[dB]

**Mass:** 95[g]

**Fan Size:** 80[mm]

**Fan Width:** 25[mm]

DC Fans