



Product: [6341PC](#)

Security & Sound, 2 Pair 18 AWG, BC, Individually Shielded, CMP

Product Description

Security, Pro Audio & Intercom Cable, Plenum-CMP, 2 PR-18 AWG stranded bare copper pairs with FEP insulation, Individually Beldfoil® shielded and Flam arrest® jacket

Technical Specifications

Product Overview

Suitable Applications:	Pro Audio, Intercom/PA Systems, Security Systems
------------------------	--------------------------------------------------

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	2	18 AWG	7x26	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	FEP - Fluorinated Ethylene Propylene	0.01 in (0.25 mm)	0.066 in (1.7 mm)	Black and Red, Black and White

Inner Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Outer Shield

Material
No Shield

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.0165 in (0.419 mm)	0.281 in	Yes

Overall Cable Diameter (Nominal):	0.281 in
-----------------------------------	----------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
6.93 Ohm/1000ft	14.4 Ohm/1000ft (47.2 Ohm/km)	44 pF/ft (140 pF/m)	79.2 pF/ft (260 pF/m)	14 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	0°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
2.81 in (71.4 mm)	2.81 in

Max. Pull Tension:	95.1 lbs (43.1 kg)
Bulk Cable Weight:	41 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Flammability / Reaction to Fire:	NFPA 262 (UL 910), FT6
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.553 Revision Date: 02-03-2025
----------------------	--------------------------------------------------

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
6341PC 877500	Natural	Reel	500 ft	612825176251	
6341PC 8771000	Natural	Reel	1,000 ft	612825176275	C
6341PC 877U1000	Natural	UnReel	1,000 ft	612825176350	

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.