





LOC	DIST	REVISIONS					
HM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			U	REV ECO-12-020241	26NOV2012	JM	MS



1. ALL DIMENSIONS SHOWN ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
2. CABLE ASSEMBLY SHALL BE WIRED PER WIRING DIAGRAM.
3. MATERIAL:
- CONNECTOR HOUSINGS- POLYCARBONATE, UL 94V-0 RATED, WHITE.
- STRAIN RELIEFS- CARBON STEEL WITH NICKEL PLATING 5.08µm [1.000200] MINIMUM THICK.
- CONTACTS- COPPER ALLOY WITH SILVER PLATED STRIP 3.81µm [1.000150] MINIMUM THICK.
4. DIMENSION A SHALL BE MEASURED WITH CONDUIT IN THE RELAXED POSITION.
5. DESIGNATIONS IN PARENTHESES () ARE FOR REFERENCE ONLY.
6. MANUFACTURING LOCATION, DATE CODE, PART NUMBER AND LENGTH SHALL BE INK STAMPED WHERE INDICATED.
7. APPLICATION: AMPINNERGY - MODULAR POWER DISTRIBUTION SYSTEM, A MANUFACTURED WIRING SYSTEM.
8. USE GROUND WIRE INSPECTION WINDOW TO VERIFY BONDING AND GROUNDING CONDUCTOR.

.305 [1.00]	1-555858-1	15.24 [50.00]
	2-555858-7	12.19 [40.00]
	2-555858-4	9.14 [30.00]
	1-555858-0	7.62 [25.00]
	1-555858-3	6.10 [20.00]
	1-555858-5	4.57 [15.00]
	555858-9	3.05 [10.00]
	2-555858-6	1.52 [5.00]
	555858-3	1.22 [4.00]
B DIM M [FEET]	555858-2	0.91 [3.00]
	555858-1	0.61 [2.00]
	PART NO.	A DIM M [FEET]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J MCNEAL	11AUG2005	 TE Connectivity					
		CHK	F LINCOLN	11AUG2005						
DIMENSIONS:		APVD	F LINCOLN	11AUG2005	NAME	CABLE ASSEMBLY, POWER ENTRY, 5 WIRE				
mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC						
		0 PLC ±								
		1 PLC ±								
		2 PLC ±								
		3 PLC ±								
		4 PLC ±								
ANGLES		FINISH		APPLICATION SPEC						
MATERIAL		FINISH		WEIGHT			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-		 3		-			A1	100779	C=555858	-
CUSTOMER DRAWING		SCALE		SHEET			OF	REV	U	