


PIN RECEPTACLES

FOR 0,38 - 0,64 DIAMETER PINS

7132

7132-0-15-XX-30-XX-04-0


Square press-fit for $0,81 \pm 0,05$
plated through-hole



8445

8445-0-15-XX-30-XX-04-0


Square press-fit for $0,99 \pm 0,05$
plated through-hole



1038

1038-0-15-XX-30-XX-04-0


Press-fit in 1,5 mounting hole



1261

1261-0-15-XX-30-XX-04-0


Press-fit in 1,45 mounting hole



0153

0153-X-15-XX-30-XX-04-0

Press-fit in 1,45 mounting hole




Basic Part Number	Height A
0153-1	5,99
0153-2	8,0
0153-3	10,21
0153-4	11,99
0153-5	15,09
0153-6	17,75

1602/1610

16XX-0-15-XX-30-XX-04-0

Press-fit in 1,45 mounting hole




Basic Part Number	Height A
1602-0	11,2
1610-0	16,31

0903/0904

090X-0-15-XX-30-XX-04-0

Press-fit in 1,45 mounting hole




Basic Part Number	Height A
0903-0	21,36
0904-0	28,98

8252

8252-0-15-XX-30-XX-10-0


Press-fit in 1,45 plated through-hole



4078

4078-0-15-XX-30-XX-40-0

Press-fit in 1,45 mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$

Diameters: $\pm 0,051$

Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 15 - XX - 30 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 5,08μm TIN/LEAD OVER NICKEL
- ◆ 80 5,08μm TIN OVER NICKEL (RoHS)
- ◆ 15 0,25μm GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 02 2,54μm TIN/LEAD OVER NICKEL
- ◆ 84 2,54μm TIN OVER NICKEL (RoHS)
- ◆ 27 0,76μm GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#30 CONTACT (DATA ON PAGE 253)

(For alternate contact choices, see groups B and C on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[7132-0-15-01-30-02-04-0](#) [1602-0-15-01-30-02-04-0](#) [1602-0-15-01-30-27-04-0](#) [1038-0-15-80-30-84-04-0](#) [1038-0-15-80-30-27-04-0](#) [0904-0-15-80-30-84-04-0](#) [0904-0-15-80-30-27-04-0](#) [0903-0-15-80-30-84-04-0](#) [0903-0-15-80-30-27-04-0](#) [0153-6-15-80-30-84-04-0](#) [0153-6-15-80-30-27-04-0](#) [0153-5-15-80-30-84-04-0](#) [0153-2-15-80-30-84-04-0](#) [0153-2-15-80-30-27-04-0](#) [1261-0-15-01-30-02-04-0](#) [1261-0-15-01-30-27-04-0](#) [1038-0-15-01-30-02-04-0](#) [1038-0-15-01-30-27-04-0](#) [0904-0-15-01-30-02-04-0](#) [0904-0-15-01-30-27-04-0](#) [0903-0-15-01-30-27-04-0](#) [0153-6-15-01-30-02-04-0](#) [0153-6-15-01-30-27-04-0](#) [0153-5-15-01-30-02-04-0](#) [0153-5-15-01-30-27-04-0](#) [0153-4-15-01-30-02-04-0](#) [0153-4-15-01-30-27-04-0](#) [0153-3-15-01-30-02-04-0](#) [0153-2-15-01-30-02-04-0](#) [0153-2-15-01-30-27-04-0](#) [8445-0-15-80-30-84-04-0](#) [8445-0-15-80-30-27-04-0](#) [7132-0-15-80-30-84-04-0](#) [1610-0-15-80-30-84-04-0](#) [1602-0-15-80-30-84-04-0](#) [1602-0-15-80-30-27-04-0](#) [1261-0-15-80-30-84-04-0](#) [0153-2-15-15-30-27-04-0](#) [0153-5-15-15-30-27-04-0](#) [0153-6-15-15-30-27-04-0](#) [0903-0-15-15-30-27-04-0](#) [0904-0-15-15-30-27-04-0](#) [1038-0-15-15-30-27-04-0](#) [1602-0-15-15-30-27-04-0](#) [8445-0-15-15-30-27-04-0](#)