


REV	DOCUMENT	CHANGED BY	CHECK
A	0005631	KR 25JAN05	AK
B	0016074	MPH 28.09.05	RK



WIRE	28 AWG, STRANDED, TEFLON INSULATED
HOUSING	ALUMINUM
THERM. CURVE, MAT'L	16, L

RESISTANCE	TEMP. (°C)	MINIMUM (OHMS)	NOMINAL (OHMS)	MAXIMUM (OHMS)	REF. TOL.
	0	32489	32740	32993	±0.15°C
	37	6002	6014.2	6026.5	±0.05°C
	45	4351.5	4368.5	4385.6	±0.1°C
	50	3583	3603.5	3624	±0.15°C

USED ON: ECO 11390

DESIGN UNITS: INCH	DRAWN	MPH	28.09.05	Honeywell				
TOLERANCES UNLESS NOTED:	CHECK	RK	28.09.05					
NO PLACE X ± 0.400	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE PROBE ASSEMBLY OUTLINE				
ONE PLACE .X ± 0.030								
TWO PLACE .XX ± 0.015								
THREE PLACE .XXX ± 0.005	INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
FOUR PLACE .XXXX ± 0.0005				A3	I	590-33AA38-103		B
ANGLES X ± 3	AUTOCAD			SCALE	4:1	SHEET		1 OF 1
THIRD ANGLE PROJECTION								
								