

## 12.5 (1/2") SQUARE DRIVE

12.5 1/2" 12.5 1/2"



## RATCHETS 12.5 (1/2")



## 1993 U-20

## REVERSIBLE RATCHET 1/2"

- Acc. to DIN 3122, ISO 3315
- Small, drop shaped head for confined areas
- Fine-toothed, with lever change and push-button release
- Non-slip 2-component handle with hanging hole
- For hand-operated sockets and accessories with square drive as per DIN 3120 - C 12.5, ISO 1174, ball locking device
- GEDORE vanadium steel 31CrV3, chrome-plated

12.5  
1/2"

| Code    | No.       | Ø " | Ø    | Δ° | mm  | Δ    | mm  | Δ | mm | £ |
|---------|-----------|-----|------|----|-----|------|-----|---|----|---|
| 1436686 | 1993 U-20 | 1/2 | 12.5 | 6  | 270 | 37.5 | 536 | 5 |    |   |

## 1993 U-20 SK

## REVERSIBLE RATCHET 1/2"

- With 1/2" hexagon drive
- Torques specification required to standard DIN 3122 is exceeded
- Small, drop shaped head for confined areas
- Fine-toothed, with lever change
- Non-slip 2-component handle with hanging hole
- For hand-operated sockets with 1/2" hexagon no. 19 SK
- GEDORE vanadium steel 31CrV3, chrome-plated

12.5  
1/2"

-45 %





| Code    | No.          | Ø " | Ø    | Δ° | mm  | Δ  | mm  | Δ | mm | £ |
|---------|--------------|-----|------|----|-----|----|-----|---|----|---|
| 2219492 | 1993 U-20 SK | 1/2 | 12.5 | 6  | 270 | 21 | 510 | 1 |    |   |

## 1993 U-10 L

## REVERSIBLE RATCHET 1/2" long pattern

- Acc. to DIN 3122, ISO 3315
- With lever change
- Push-button release
- Non-slip 2-component handle with hanging hole
- Locks in the middle position: When the lever is flipped, it automatically engages for clockwise or counterclockwise operation
- For hand-operated sockets and accessories with square drive as per DIN 3120 - C 12.5, ISO 1174, ball locking device
- GEDORE vanadium steel 31CrV3, chrome-plated

12.5  
1/2"

| Code    | No.         | Ø "  | Ø   | Δ°    | mm  | Δ  | mm  | Δ | mm | £ |
|---------|-------------|------|-----|-------|-----|----|-----|---|----|---|
| 6154550 | 1993 U-10 L | 12.5 | 1/2 | 11,25 | 350 | 41 | 696 | 5 |    |   |

