

InGaAs PIN photodiode with preamp G8339/G8342/G7881/G8796 series

Receptacle type, 1.3/1.55 μm , 156, 622 Mbps/1.25, 2.5 Gbps



G8339/G8342/G7881/G8796 series are high-speed receivers specifically developed for 1.3/1.55 μm band optical fiber communications. These devices incorporate a high-speed, high-sensitivity InGaAs PIN photodiode and a high-speed preamp integrated in a receptacle module. Packages are available with various connectors and mounting styles.

Features

- Wide dynamic range
G8339 series (156 Mbps) : -37 to -5 dBm
G8342 series (622 Mbps) : -32 to -5 dBm
G7881 series (1.25 Gbps) : -25 to -1 dBm
G8796 series (2.5 Gbps) : -22 to +1 dBm
- Integrated with trans-impedance amplifier
- Supply voltage
G8339/G8342 series: 3.3 V
G7881/G8796 series: 3.3 V, 5 V
- Differential output

Applications

- Optical fiber communications
- Fiber channel
- Gigabit Ethernet
- HDTV
- SDH

■ Absolute maximum ratings (Ta=25 °C)

Parameter	Symbol	G8339 series	G8342 series	G7881 series	G8796 series	Unit
Supply voltage	Vcc	-0.3, +3.8	-0.3, +3.8	-0.3, +5.5	-0.5, +6	V
Operating temperature	T _{opr}	-20 to +70				°C
Storage temperature	T _{stg}	-40 to +85				°C

■ Specifications (Typ. Ta=25 °C, V_{ee}=0 V, capacitive coupling, λ =1.31 μm , unless otherwise noted)

Parameter	Symbol	Condition	G8339 series	G8342 series	G7881 series	G8796 series	Unit
			V _{cc} =3.3 V R _L =500 Ω *1	V _{cc} =3.3 V R _L =500 Ω *1	V _{cc} =3.3/5 V R _L =50 Ω	V _{cc} =3.3/5 V R _L =50 Ω	
Photo sensitivity	S	*2, *3	27	17	2.8	1.2	V/mW
Supply current	I _{cc}	dark state, R _L = ∞	25	30	35	35	mA
Output bias voltage	V _o	dark state, R _L = ∞	1.5	1.65	V _{cc} - 1.7	V _{cc} - 0.25	V
Rise time	t _r	*3, 20 to 80 %	2000	500	250	150	ps
Data rate	B		156 M	622 M	1.25 G	2.5 G	bps

*1: G8339/G8342 series cannot be operated with R_L=50 Ω , so they should be used with a load resistance larger than 500 Ω .

*2: Single ended (V_{out}+) measurement using a single mode optical fiber with a master plug.

*3: G8339/G8342 series: Pin= -30 dBm

G7881 series: Pin= -22 dBm

G8796 series: Pin= -17 dBm


■ Package lineup

Parameter	G8339/G8342/G7881/G8796				
	-21	-22	-23	-32	-44
Mounting style	Board			Panel	Board & panel
Connector	SC	FC	MU	FC	LC
Dimensional outline	①	②	③	④	⑤

InGaAs PIN photodiode with preamp G8339/G8342/G7881/G8796 series


■ Dimensional outlines (unit: mm, tolerance unless otherwise noted: ± 0.2 mm)

① G8339/G8342/G7881/G8796-21




KIRDA0081EB

② G8339/G8342/G7881/G8796-22




KIRDA0082EB

③ G8339/G8342/G7881/G8796-23




KIRDA0109EA

④ G8339/G8342/G7881/G8796-32



KIRDA0083EB

⑤ G8339/G8342/G7881/G8796-44



KIRDA0110EB

■ Pin connection

Pin No.	G8339/G8342/ G8796 Series	G7881 Series
①	Vcc	Vcc
②	Vout -	Vout +
③	Vee	Vee
④	Vout +	Vout -

HAMAMATSU

HAMAMATSU PHOTONICS K.K., Solid State Division

1126-1 Ichino-cho, Hamamatsu City, 435-8558 Japan, Telephone: (81) 053-434-3311, Fax: (81) 053-434-5184, <http://www.hamamatsu.com>

U.S.A.: Hamamatsu Corporation, 360 Foothill Road, P.O. Box 6910, Bridgewater, N.J. 08807-0910, U.S.A., Telephone: (1) 908-231-0960, Fax: (1) 908-231-1218

Germany: Hamamatsu Photonics Deutschland GmbH: Arzbergerstr. 10, D-82211 Herrsching am Ammersee, Germany, Telephone: (49) 08152-3750, Fax: (49) 08152-2658

France: Hamamatsu Photonics France S.A.R.L.: 8, Rue du Saule Trapu, Parc du Moulin de Massy, 91882 Massy Cedex, France, Telephone: 33-(1) 69 53 71 00, Fax: 33-(1) 69 53 71 10

United Kingdom: Hamamatsu Photonics UK Limited: 2 Howard Court, 10 Tewin Road, Welwyn Garden City, Hertfordshire AL7 1BW, United Kingdom, Telephone: (44) 1707-294888, Fax: (44) 1707-325777

North Europe: Hamamatsu Photonics Norden AB: Smidesvägen 12, SE-171 41 Solna, Sweden, Telephone: (46) 8-509-031-00, Fax: (46) 8-509-031-01

Italy: Hamamatsu Photonics Italia S.R.L.: Strada della Moia, 1/E, 20020 Arese, (Milano), Italy, Telephone: (39) 02-935-81-733, Fax: (39) 02-935-81-741

Cat. No. KIRD1030E04
Jan. 2002 DN