



SBL20xxCT, SBLF20xxCT & SBLB20xxCT Series

Dual Low V_F Schottky Rectifier


Reverse Voltage 30 and 40V
Forward Current 20A



TO-220AB (SBL20xxCT)



Mounting Pad Layout TO-263AB




Dimensions in inches and (millimeters)


Features

- Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- Dual rectifier construction, positive center tap
- Metal silicon junction, majority carrier conduction
- Low power loss, high efficiency
- Guardring for overvoltage protection
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications
- High temperature soldering guaranteed: 250°C/10 seconds, 0.25" (6.35mm) from case

ITO-220AB (SBLF20xxCT)



TO-263AB (SBLB20xxCT)



Mechanical Data

Case: JEDEC TO-220AB, ITO-220AB & TO-263AB molded plastic body

Terminals: Plated leads, solderable per MIL-STD-750, Method 2026

Polarity: As marked

Mounting Position: Any

Mounting Torque: 10 in-lbs maximum

Weight: 0.08 ounce, 2.24 grams

5/8/00

SBL20xxCT, SBLF20xxCT & SBLB20xxCT Series

Dual Low V_F Schottky Rectifier

Maximum Ratings ($T_C = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	SBL2030CT	SBL2040CT	Unit
Maximum repetitive peak reverse voltage	V_{RRM}	30	40	V
Working peak reverse voltage	V_{RWM}	21	28	V
Maximum DC blocking voltage	V_{DC}	30	40	V
Maximum average forward rectified current <i>Total device</i> at $T_C = 105^\circ\text{C}$ <i>Per leg</i>	$I_{F(AV)}$	20 10		A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method) per leg	I_{FSM}	175		A
Peak repetitive reverse surge current per leg at $t_p = 2.0\mu\text{s}$, 1KHz	I_{RRM}	1.0		A
Operating junction and storage temperature range	T_J, T_{STG}	-40 to +125		$^\circ\text{C}$
RMS Isolation voltage (SBLF type only) from terminals to heatsink with $t = 1.0$ second, $RH \leq 30\%$	V_{ISOL}	4500 (NOTE 1) 3500 (NOTE 2) 1500 (NOTE 3)		V

Electrical Characteristics ($T_C = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Maximum instantaneous forward voltage per leg at 10 A (Note 4)	V_F	0.60	V
Maximum instantaneous current at rated $T_C = 25^\circ\text{C}$ DC blocking voltage per leg (Note 4) $T_C = 100^\circ\text{C}$	I_R	1.0 50	mA

Thermal Characteristics ($T_C = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	SBL	SBLF	SBLB	Unit
Typical thermal resistance from junction to case per leg	$R_{\theta JC}$	2.0	4.0	2.0	$^\circ\text{C}/\text{W}$

Notes:


- (1) Clip mounting (on case), where lead does not overlap heatsink with 0.110" offset
- (2) Clip mounting (on case), where leads do overlap heatsink
- (3) Screw mounting with 4-40 screw, where washer diameter is ≤ 4.9 mm (0.19")
- (4) Pulse test: 300 μs pulse width, 1% duty cycle

SBL20xxCT, SBLF20xxCT & SBLB20xxCT Series


Dual Low V_F Schottky Rectifier

Ratings and Characteristic Curves ($T_A = 25^\circ\text{C}$ unless otherwise noted)


Forward Current Derating Curve




**Maximum Non-Repetitive Peak
Forward Surge Current Per Leg**




**Typical Instantaneous
Forward Characteristics per Leg**



Typical Reverse Characteristics Per Leg



Typical Junction Capacitance Per Leg



**Typical Transient
Thermal Impedance Per Leg**

