





1 STAMP AMP 1/0C 100 275/24 APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
		WIRE CROSS SECTIONAL AREA RANGE: 42.41-60.55mm² [83,700-119,500] CIR MILS STRANDED
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.
FOR ORDER ENTRY	1-800-526-5142	

				PART NO							
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN 30AUG94 DK SCHRUM		TE TE Connectivity					
				CHK 31AUG94 AJ KAUFMAN							
				APVD 31AUG94 RE ROSER							
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		NAME TERMINAL, AMPPOWER, WIRE SIZE: 1/0 AWG					
		0 PLC ± -		APPLICATION SPEC							
		1 PLC ± -		—							
		2 PLC ± 0.20[.008]				SIZE CAGE CODE DRAWING NO RESTRICTED TO					
		3 PLC ± -									
		4 PLC ± -				A200779C-325302					
		ANGLES ± -									
MATERIAL		FINISH		WEIGHT							
COPPER PER ASTM B-75 ANNEALED		TIN PLATE 0.00381[.000150] MIN THK PER MIL-T-10727		—							
CUSTOMER DRAWING						SCALE		SHEET		REV	
						4:1		1 of 1		Y1	