


**Part Number: 68107-0961**

D-Subminiature Shielded I/O PCB Female Receptacle, Right Angle, 9 Circuits, Standard Nut, Lead-Free



Status: **OBsolete**
Replacement: Contact Molex
Series: 68107
Category: I/O Connectors

Series image - Reference only

Product Environmental ComplianceEU RoHS: ELV and RoHS CompliantChina RoHS: REACH SVHC:Low-Halogen Status: Not Reviewed**Part Detail****General**

Status	Obsolete
Category	I/O Connectors
Series	68107
Application	Wire-to-Board
Component Type	Plug
Product Name	D-Sub
Type	N/A

Physical

Boot Color	N/A
Circuits (Loaded)	9
Circuits (maximum)	9
Durability (mating cycles max)	200
Gender	Plug
Keying to Mating Part	None
Lock to Mating Part	No
Material - Plating Mating	Gold
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.18mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	0.80mm
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	1.37mm
Pitch - Termination Interface	1.37mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +105°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A
Wire Size AWG	N/A

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	5A
Grounding to Panel	Yes
Shielded	No
Voltage - Maximum	125V AC (RMS)/DC

Material Info**Reference - Drawing Numbers**

Product Specification	PS-68107-001
Sales Drawing	SD-68107-002

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)