

LOC	DIST	REVISIONS					
A1	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B3	REWORKED PER ECR 09-026789	08DEC2009	MH	BR
			B4	ECR-11-002636	05APR2011	SR	AR



PN 1-1,2-1,3-1,4-1,5-1,1-2,2-2,3-2
4-2,5-2,6-1,4-3,1-8,2-8,3-8,4-8,5-8,
4-9,2-9,3-9,4-9 & 5-9



$\varnothing A_{-0.05}$



Dimension line for $B+0.05$

NOTES

- | | |
|---|---|
| 1 | MATERIAL SEE TABLE |
| 2 | SURFACE SEE TABLE |
| 3 | ASSEMBLY WEIGHT SEE TABLE |
| 4 | PACKAGING: 50 PIECES IN POLY-BAG 0-1243085-8 |
| 5 | PACKAGING: 500 PIECES IN POLY-BAG 0-1243085-8 |
| 6 | PACKAGING: 10 PIECES IN POLY-BAG 0-1243085-8 |
| 7 | CROSS-SECTION MARKING |



OBSOLETE	OBSOLETE	OBSOLETE														△3	△1	△2	△7			2
			1	1	1	1	1	1	1	1	1	1	1	1	Catch Spring		Stainless Steel					
															Socket Contact 1.5 mm ²	0.00062	Brass	Ag/Ni	1.8	3.0	4	1
															Socket Contact 4.0 mm ²	0.00059	Brass	Ag/Ni	2.4	3.2	6	
															Socket Contact 2.5 mm ²	0.00067	Brass	Au	2.2	3.2	5	
															Socket Contact 1.5 mm ²	0.00067	Brass	Au	1.8	3.0	4	
															Socket Contact 0.75-10 mm ²	0.00063	Brass	Au	1.45	2.6	3	
															SocketContact 0.5 mm ²	0.00062	Brass	Au	1.1	2.6	2	
															Socket Contact 0.14-0.37 mm ²	0.00061	Brass	Au	0.9	2.6	1	
															Socket Contact 2.5 mm ²	0.00065	Brass	Ag/Cu	2.2	3.2	5	
															Socket Contact 1.5 mm ²	0.00067	Brass	Ag/Cu	1.8	3.0	4	
															Socket Contact 0.75-10 mm ²	0.00063	Brass	Ag/Cu	1.45	2.6	3	
															Socket Contact 0.5 mm ²	0.00062	Brass	Ag/Cu	1.1	2.6	2	
OBSOLETE															Socket Contact 0.14-0.37 mm ²	0.00061	Brass		0.9	2.6	1	
OBSOLETE															Socket Contact 0.14-0.37 mm ²	0.00065	Fe	Au	0.9	2.6	1	
															Socket Contact 0.14-0.37 mm ²	0.00067	Brass	Ag/Cu	0.9	2.6	1	

[illegible]

HN.D-C-Bu,Ag,Ni,1.5 mm ²
HN.D-C-Bu,Ag,Ni,4,0 mm ²
HN.D-C-Bu,Cu,Ni,0.14 -0.37 mm ²
HN.D-C-Bu,Fe,Au,0.14 -0.37 mm ²
HN.D-C-Bu,Au,2.5 mm ²
HN.D-C-Bu,Au,1.5 mm ²
HN.D-C-Bu,Au,0.75-1,00 mm ²
HN.D-C-Bu,Au,0.5 mm ²
HN.D-C-Bu,Au,0.14 -0.37 mm ²
HN.D-C-Bu,Ag,2.5 mm ²
HN.D-C-Bu,Ag,1.5 mm ²
HN.D-C-Bu,Ag,0.75-1,00 mm ²
HN.D-C-Bu,Ag,0.5 mm ²
HN.D-C-Bu,Ag,0.14 -0.37 mm ²

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 23.07.1997 Braun CHK 23.07.1997 Schnurpfeil		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768 DIN 152 2768 mH-e DIN 9001-120		NAME SOCKET CONTACT SERIES HN.D	
		APVD - PRODUCT SPEC 108-74018 APPLICATION SPEC 114-74015		SIZE CAGE CODE DRAWING NO	
MATERIAL 		FINISH 		RESTRICTED TO -	
1		2		WEIGHT - A2 00779 C=1105051	
CUSTOMER DRAWING				SCALE 10:1 SHEET 1 OF 1 REV B4	