

## Description

The 74AHC595 is an advanced high speed CMOS device.

An eight bit shift register accepts data from the serial input (DS) on each positive transition of the shift register clock (STCP). When asserted low the reset function ( $\overline{MR}$ ) sets all shift register values to zero and is independent of all clocks.

Data from the input serial shift register is placed in the output register with a rising pulse on the storage register clock (SHCP). With the output enable ( $\overline{OE}$ ) asserted low the 3-state outputs Q0-Q7 become active and present.

All registers capture data on rising edge and change output on the falling edge. If both clocks are connected together, the input shift register is always one clock cycle ahead of the output register.

## Pin Assignments

### (Top View)

Q1	1	16	Vcc
Q2	2	15	Q0
Q3	3	14	DS
Q4	4	13	$\overline{OE}$
Q5	5	12	STCP
Q6	6	11	SHCP
Q7	7	10	$\overline{MR}$
GND	8	9	Q7S

SO-16 / TSSOP-16

## Features

- Wide Supply Voltage Range from 2.0 V to 5.5V
- Sinks or sources 8mA at  $V_{CC} = 4.5V$
- CMOS low power consumption
- Schmitt Trigger Action at All Inputs
- Inputs Accept up to 5.5V
- ESD Protection Tested per JESD 22
  - Exceeds 200-V Machine Model (A115-A)
  - Exceeds 2000-V Human Body Model (A114-A)
  - Exceeds 1000-V Charged Device Model (C101C)
- Latch-Up Exceeds 250mA per JESD 78, Class II
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- Halogen and Antimony Free. "Green" Device (Note 3)

## Applications

- General Purpose Logic
- Serial to Parallel Data conversion
- Capture and hold data for extended periods of time
- Allow simple serial bit streams from a microcontroller to control as many peripheral lines as needed
- Wide array of products such as:
  - Computer peripherals
  - Appliances
  - Industrial control

Notes:


- No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
- See [http://www.diodes.com/quality/lead\\_free.html](http://www.diodes.com/quality/lead_free.html) for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

[Click here for ordering information, located at the end of datasheet](#)


## Pin Descriptions

Pin Number	Pin Name	Description
1	Q1	Parallel Data Output 1
2	Q2	Parallel Data Output 2
3	Q3	Parallel Data Output 3
4	Q4	Parallel Data Output 4
5	Q5	Parallel Data Output 5
6	Q6	Parallel Data Output 6
7	Q7	Parallel Data Output 7
8	GND	Ground
9	Q7S	Serial Data Output
10	MR	Master Reset Input
11	SHCP	Shift Register Clock Input
12	STCP	Storage Register Clock Input
13	OE	Output Enable Input
14	DS	Serial Data Input
15	Q0	Parallel Data Output 0
16	Vcc	Supply Voltage

## Functional Diagram



## Logic Diagram



## Functional Description and Timing Diagram

Control				Input	Output		Function
SHCP	STCP	$\overline{OE}$	MR	DS	Q7S	Qn	
X	X	L	L	–	L	NC	Low-level asserted on MR clears shift register. Storage register is unchanged
X	↑	L	L	–	L	L	Empty shift register transferred to storage register
X	X	H	L	–	L	Z	Shift register remains clear; All Q outputs in Z state.
↑	X	L	H	–	Q6S	NC	HIGH is shifted into first stage of Shift Register Contents of each register shifted to next register The content of Q6S has been shifted to Q7S and now appears on device pin Q7S
X	↑	L	H	–	NC	QnS	Contents of shift register copied to storage register. With output now in active state the storage register contents appear on Q outputs.
↑	↑	L	H	–	Q6S	QnS	

H=HIGH voltage state


L=LOW voltage state

↑=LOW to HIGH transition

X= don't care – high or low (not floating)

NC= No change

Z= high-impedance state



Absolute Maximum Ratings (Note 4) (@ $T_A = +25^\circ\text{C}$ , unless otherwise specified.)

Symbol	Parameter	Rating	Unit
ESD HBM	Human Body Model ESD Protection	2	KV
ESD CDM	Charged Device Model ESD Protection	1	KV
ESD MM	Machine Model ESD Protection	200	V
$V_{CC}$	Supply Voltage Range	-0.5 to 7.0	V
$V_I$	Input Voltage Range	-0.5 to 7.0	V
$V_O$	Voltage applied to output in high or low state	-0.3 to $V_{CC}$ + 0.5	V
$I_{IK}$	Input Clamp Current $V_I < -0.5\text{V}$	-20	mA
$I_{OK}$	Output Clamp Current $V_O < -0.5\text{V}$	-20	mA
$I_{OK}$	Output Clamp Current $V_O > V_{CC} + 0.5\text{V}$	25	mA
$I_O$	Continuous output current	+/- 25	mA
$I_{CC}$	Continuous current through $V_{CC}$ or GND	75	mA
$I_{GND}$	Continuous current through $V_{CC}$ or GND	-75	mA
$T_J$	Operating Junction Temperature	-40 to 150	°C
$T_{STG}$	Storage Temperature	-65 to 150	°C
$P_{TOT}$	Total Power Dissipation	500	mW

Note: 4. Stresses beyond the absolute maximum may result in immediate failure or reduced reliability. These are stress values and device operation should be within recommend values.

 Recommended Operating Conditions (Note 5) (@ $T_A = +25^\circ\text{C}$ , unless otherwise specified.)

Symbol	Parameter	Conditions	Min	Max	Unit
$V_{CC}$	Supply Voltage	–	2.0	5.5	V
$V_I$	Input Voltage	–	0	5.5	V
$V_O$	Output Voltage	Active Mode	0	$V_{CC}$	V
$\Delta t/\Delta V$	Input transition Rise or Fall Rate	$V_{CC} = 3.0\text{V}$ to $3.6\text{V}$	–	100	ns/V
		$V_{CC} = 4.5\text{V}$ to $5.5\text{V}$	–	20	
$T_A$	Operating Free-Air Temperature	–	-40	+125	°C

Note: 5. Unused inputs should be held at  $V_{CC}$  or Ground.

 Electrical Characteristics (@ $T_A = +25^\circ\text{C}$ , unless otherwise specified.)

Symbol	Parameter	Test Conditions	$V_{CC}$	$T_A = +25^\circ\text{C}$			$T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$		$T_A = -40^\circ\text{C}$ to $+125^\circ\text{C}$		Unit
				Min	Typ	Max	Min	Max	Min	Max	
$V_{IH}$	High-level Input Voltage	–	2.0V	1.5	–	–	1.5	–	1.5	–	V
		–	3.0V	2.1	–	–	2.1	–	2.1	–	
		–	5.5V	3.85	–	–	3.85	–	3.85	–	
$V_{IL}$	Low-level input voltage	–	2.0V	–	–	0.5	–	0.5	–	0.5	V
		–	3.0V	–	–	0.9	–	0.9	–	0.9	
		–	5.5V	–	–	1.65	–	1.65	–	1.65	
$V_{OH}$	High Level Output Voltage	$I_{OH} = -50\mu\text{A}$	2.0V	1.9	2.0	–	1.9	–	1.9	–	V
		$I_{OH} = -50\mu\text{A}$	3.0V	2.9	3.0	–	2.9	–	2.9	–	
		$I_{OH} = -50\mu\text{A}$	4.5V	4.4	4.5	–	4.4	–	4.4	–	
		$I_{OH} = -4\text{mA}$	3.0V	2.58	–	–	2.48	–	2.40	–	
		$I_{OH} = -8\text{mA}$	4.5V	3.94	–	–	3.80	–	3.70	–	
$V_{OL}$	Low-level Output Voltage	$I_{OL} = 50\mu\text{A}$	2.0V	–	0	0.1	–	0.1	–	0.1	V
		$I_{OL} = 50\mu\text{A}$	3.0V	–	0	0.1	–	0.1	–	0.1	
		$I_{OL} = 50\mu\text{A}$	4.5V	–	0	0.1	–	0.1	–	0.1	
		$I_{OL} = 4\text{mA}$	3.0V	–	–	0.36	–	0.44	–	0.55	
		$I_{OL} = 8\text{mA}$	4.5V	–	–	0.36	–	0.44	–	0.55	
$I_I$	Input Current	$V_I = \text{GND}$ to $5.5\text{V}$	5.5V	–	0.1	$\pm 0.1$	–	$\pm 1$	–	$\pm 2$	µA
$I_{OZ}$	OFF-state output current	$V_I = V_{IH}$ or $V_{IL}$ ; $V_O = V_{CC}$ or GND	5.5V	–	–	$\pm 0.25$	–	$\pm 2.5$	–	$\pm 10$	µA
$I_{CC}$	Supply Current	$V_I = \text{GND}$ or $V_{CC}$ $I_O = 0$	5.5V	–	–	4.0	–	40	–	80	µA
$C_I$	Input Capacitance	$V_I = V_{CC}$ or GND	5.5V	–	4	10	–	10	–	10	pF


## Switching Characteristics

Symbol / Parameter	Pins	Test Conditions	V <sub>CC</sub>	T <sub>A</sub> = +25°C			-40°C to +85°C		-40°C to +125°C		Unit
				Min	Typ	Max	Min	Max	Min	Max	
f <sub>MAX</sub> Maximum Frequency	SHCP or STCP	Figure 2	3.0V to 3.6V	80	125	—	60	—	40	—	MHz
			4.5V to 5.5V	130	70	—	110	—	90	—	
t <sub>W</sub> Pulse Width	SHCP HIGH or LOW	Figure 2	3.0V to 3.6V	5.0	—	—	5.0	—	5.0	—	ns
			4.5V to 5.5V	5.0	—	—	5.0	—	5.0	—	
	STCP HIGH or LOW	Figure 2	3.0V to 3.6V	5.0	—	—	5.0	—	5.0	—	
			4.5V to 5.5V	5.0	—	—	5.0	—	5.0	—	
	M̄R LOW	Figure 2	3.0V to 3.6V	5.0	—	—	5.0	—	5.0	—	
			4.5V to 5.5V	5.0	—	—	5.0	—	5.0	—	
t <sub>SU</sub> Set-up Time	DS to SHCP	Figure 2	3.0V to 3.6V	3.5	—	—	3.5	—	3.5	—	ns
			4.5V to 5.5V	3.0	—	—	3.0	—	3.0	—	
	SHCP to STCP	Figure 2	3.0V to 3.6V	8.5	—	—	8.5	—	8.5	—	ns
			4.5V to 5.5V	5.0	—	—	5.0	—	5.0	—	
t <sub>H</sub> Hold Time	DS to SHCP	Figure 2	3.0V to 3.6V	1.5	—	—	1.5	—	1.5	—	ns
			4.5V to 5.5V	2.0	—	—	2.0	—	2.0	—	
t <sub>REC</sub> Recovery Time	M̄R to SHCP	Figure 2	3.0V to 3.6V	3.0	—	—	3.0	—	3.0	—	ns
			4.5V to 5.5V	2.5	—	—	2.5	—	2.5	—	
t <sub>PD</sub> Propagation Delay	SHCP to Q7S	Figure 2	3.0V to 3.6V	—	5.7	13.0	1.0	15.0	1.0	16.5	ns
			4.5V to 5.5V	—	4.0	8.2	1.0	9.4	1.0	10.5	
		Figure 2	3.0V to 3.6V	—	7.7	16.5	1.0	18.5	1.0	20.1	
			4.5V to 5.5V	—	5.4	10.0	1.0	11.4	1.0	12.5	
	STCP to Qn	Figure 2	3.0V to 3.6V	—	5.9	11.9	1.0	13.5	1.0	15.0	ns
			4.5V to 5.5V	—	4.2	7.4	1.0	8.5	1.0	10.5	
		Figure 2	3.0V to 3.6V	—	7.7	15.4	1.0	17.0	1.0	18.5	
			4.5V to 5.5V	—	5.5	9.0	1.0	10.5	1.0	11.5	
	M̄R to Q7S	Figure 2	3.0V to 3.6V	—	5.9	12.8	1.0	13.7	1.0	15.0	ns
			4.5V to 5.5V	—	4.4	8.0	1.0	9.1	1.0	10.5	
		Figure 2	3.0V to 3.6V	—	7.4	16.3	1.0	17.2	1.0	18.7	
			4.5V to 5.5V	—	5.6	10.0	1.0	11.1	1.0	12.0	
t <sub>EN</sub> Enable Time	OE to Qn	Figure 2	3.0V to 3.6V	—	5.6	11.5	1.0	13.5	1.0	15.0	ns
			4.5V to 5.5V	—	4.0	8.6	1.0	10.0	1.0	10.5	
		Figure 2	3.0V to 3.6V	—	7.4	15.0	1.0	17.0	1.0	18.5	
			4.5V to 5.5V	—	5.3	10.6	1.0	12.0	1.0	13.0	
t <sub>DIS</sub> Disable Time	OE to Qn	Figure 2	3.0V to 3.6V	—	5.4	11.0	1.0	13.0	1.0	14.5	ns
			4.5V to 5.5V	—	3.8	8.0	1.0	9.5	1.0	10.5	
		Figure 2	3.0V to 3.6V	—	8.7	15.7	1.0	16.2	1.0	17.5	
			4.5V to 5.5V	—	5.8	10.3	1.0	11.0	1.0	12.0	

## Operating Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)





Parameter	Test Conditions	V <sub>CC</sub> = 5V	Unit
C <sub>pd</sub>	Power dissipation capacitance f = 1 MHz all outputs switching-no load	42	pF

## Parameter Measurement Information



TEST	Vload
t <sub>PLH</sub> /t <sub>PHL</sub>	Open
t <sub>PLZ</sub> /t <sub>PZL</sub>	V <sub>CC</sub>
t <sub>PHZ</sub> /t <sub>PZH</sub>	GND

V <sub>CC</sub>	Inputs		V <sub>M</sub>	C <sub>L</sub>
	V <sub>I</sub>	t <sub>r</sub> /t <sub>f</sub>		
3.3V -3.6V	V <sub>CC</sub>	3ns	V <sub>CC</sub> /2	15pF, 50pF
4.5V to 5.5V	V <sub>CC</sub>	3ns	V <sub>CC</sub> /2	15pF, 50pF



Notes:


- A .Includes test lead and test apparatus capacitance.
- B. Output Waveform 1 depends on the internal Q<sub>N</sub> node being low and behaves in this manner based on OE pin. Output Waveform 2 depends on the internal Q<sub>N</sub> node being high and behaves in this manner based on OE pin.
- C. All pulses are supplied at pulse repetition rate  $\leq 10$  MHz
- D. Inputs are measured separately one transition per measurement
- E. t<sub>PLH</sub> and t<sub>PHL</sub> are the same as t<sub>PD</sub>.

Figure 2. Load Circuit and Voltage Waveforms

---

## Ordering Information

---



Part Number	Package Code	Packaging	7" Tape and Reel (Note 6)	
			Quantity	Part Number Suffix
74AHC595S16-13	S16	SO-16	2500/Tape & Reel	-13
74AHC595T16-13	T16	TSSOP-16	2500/Tape & Reel	-13


Note: 6. The taping orientation is located on our website at <http://www.diodes.com/datasheets/ap02007.pdf>

---

## Marking Information

---

(1) SO-16, TSSOP16




Part Number	Package
74AHC595S16	SO-16
74AHC595T16	TSSOP-16


## Package Outline Dimensions (All dimensions in mm.)

Please see AP02002 at <http://www.diodes.com/datasheets/ap02002.pdf> for latest version.

### Package Type: SO-16




### Package Type: TSSOP-16



## Suggested Pad Layout


Please see AP02001 at <http://www.diodes.com/datasheets/ap02001.pdf> for the latest version.

### Package Type: SO-16



Dimensions	Value (in mm)
C	1.270
X	0.670
X1	9.560
Y	1.450
Y1	6.400

### Package Type: TSSOP-16



Dimensions	Value (in mm)
C	0.650
X	0.350
X1	4.900
Y	1.400
Y1	6.800

**IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

**LIFE SUPPORT**

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2013, Diodes Incorporated

[www.diodes.com](http://www.diodes.com)