

	1	2	3	4	5	6	7																																																																	
A	23,2±0,5 23,2±0,5 PLUG TYPE 41,5±1.0 2010±50 61,75±1,0 15,55±0,25 22,75±0,25 180±30 Hank Dimension Wire cross section BLACK WHITE GREEN COPPER CONDUCTOR(N/mm): 41/0.254±0.003 or Substitute PVC INSULATION AVERAGE THICKNESS: 0.76mm ID: 3.40±0.1mm PVC JACKET AVERAGE THICKNESS: 0.76mm OD: 9.3±0.2mm							A																																																																
B								B																																																																
C								C																																																																
D	NOTES: Material: 1.SJT 3x14AWG(2.08MM²) VW-1, 60°C 300V, Without Filler 2.Jacket Color: Black. 3.E-Green, L-Black, N-White. Electrical Test: 1.100% Open & Short Testing. 2.Insulation Resistance: 100MΩ(Min). 3.Voltage: 500V DC/1Min.							D																																																																
E								E																																																																
F								F																																																																
G	RoHS compliant Unit: mm <table><tr><td>Scale</td><td>Free</td><td></td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td colspan="2">Customer-No.</td></tr><tr><td colspan="2">TOLERANCE</td><td></td><td></td><td></td><td></td><td>Drawn</td><td>28.01.2019</td><td>Segal</td><td colspan="2" rowspan="2">ASSMANN WSW-No. A-PC2302-020026-1</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td>Approved</td><td>28.01.2019</td><td>Segal</td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td colspan="2">Drawing-No.</td></tr><tr><td></td><td></td><td>①</td><td>Drawn</td><td>28.01.2019</td><td>Segal</td><td colspan="3" rowspan="2"></td><td colspan="2">ASS 8472 CA</td><td>rev00</td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td colspan="2">Replace</td><td colspan="2">Sheet</td></tr></table>							Scale	Free						Date	Name	Customer-No.		TOLERANCE						Drawn	28.01.2019	Segal	ASSMANN WSW-No. A-PC2302-020026-1								Approved	28.01.2019	Segal	DIM	TOL								Drawing-No.				①	Drawn	28.01.2019	Segal				ASS 8472 CA		rev00	Angle	TOL	Id.	Modification	Date	Name	Replace		Sheet		G
Scale								Free						Date	Name	Customer-No.																																																								
TOLERANCE												Drawn	28.01.2019	Segal	ASSMANN WSW-No. A-PC2302-020026-1																																																									
						Approved	28.01.2019	Segal																																																																
DIM	TOL								Drawing-No.																																																															
		①	Drawn	28.01.2019	Segal				ASS 8472 CA		rev00																																																													
Angle	TOL	Id.	Modification	Date	Name				Replace		Sheet																																																													
H								H																																																																
	1	2	3	4	5	6	7																																																																	