



# NPN SILICON GERMANIUM RF TRANSISTOR

## NESG250134

### NPN SiGe RF TRANSISTOR FOR MEDIUM OUTPUT POWER AMPLIFICATION (800 mW) 3-PIN POWER MINIMOLD (34 PACKAGE)

#### FEATURES

- This product is suitable for medium output power (800 mW) amplification  
 $P_O = 29 \text{ dBm TYP. @ } V_{CE} = 3.6 \text{ V, } P_{in} = 15 \text{ dBm, } f = 460 \text{ MHz}$   
 $P_O = 29 \text{ dBm TYP. @ } V_{CE} = 3.6 \text{ V, } P_{in} = 20 \text{ dBm, } f = 900 \text{ MHz}$
- MSG (Maximum Stable Gain) = 23 dB TYP., @  $V_{CE} = 3.6 \text{ V, } I_c = 100 \text{ mA, } f = 460 \text{ MHz}$
- Using UHS2-HV process (SiGe technology),  $V_{CBO}$  (ABSOLUTE MAXIMUM RATINGS) = 20 V
- 3-pin power minimold (34 package)

#### ORDERING INFORMATION

| Part Number     | Quantity          | Supplying Form                                                                          |
|-----------------|-------------------|-----------------------------------------------------------------------------------------|
| NESG250134-A    | 25 pcs (Non reel) | • 12 mm wide embossed taping<br>• Pin 2 (Emitter) face the perforation side of the tape |
| NESG250134-T1-A | 1 kpcs/reel       |                                                                                         |

**Remark** To order evaluation samples, contact your nearby sales office.  
Unit sample quantity is 25 pcs.

#### ABSOLUTE MAXIMUM RATINGS ( $T_A = +25^\circ\text{C}$ )

| Parameter                    | Symbol                    | Ratings     | Unit             |
|------------------------------|---------------------------|-------------|------------------|
| Collector to Base Voltage    | $V_{CBO}$                 | 20          | V                |
| Collector to Emitter Voltage | $V_{CEO}$                 | 9.2         | V                |
| Emitter to Base Voltage      | $V_{EBO}$                 | 2.8         | V                |
| Collector Current            | $I_c$                     | 500         | mA               |
| Total Power Dissipation      | $P_{tot}$ <sup>Note</sup> | 1.5         | W                |
| Junction Temperature         | $T_j$                     | 150         | $^\circ\text{C}$ |
| Storage Temperature          | $T_{stg}$                 | -65 to +150 | $^\circ\text{C}$ |

**Note** Mounted on  $34.2 \text{ cm}^2 \times 0.8 \text{ mm (t)}$  glass epoxy PWB

**Caution: Observe precautions when handling because these devices are sensitive to electrostatic discharge**

The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version.

**THERMAL RESISTANCE ( $T_A = +25^\circ\text{C}$ )**

| Parameter                                                   | Symbol      | Ratings | Unit               |
|-------------------------------------------------------------|-------------|---------|--------------------|
| Thermal Resistance from Junction to Ambient <sup>Note</sup> | $R_{thj-a}$ | 80      | $^\circ\text{C/W}$ |

**Note** Mounted on  $34.2\text{ cm}^2 \times 0.8\text{ mm}$  (t) glass epoxy PWB

**RECOMMENDED OPERATING RANGE ( $T_A = +25^\circ\text{C}$ )**

| Parameter                    | Symbol   | MIN. | TYP. | MAX. | Unit |
|------------------------------|----------|------|------|------|------|
| Collector to Emitter Voltage | $V_{CE}$ | –    | 3.6  | 4.5  | V    |
| Collector Current            | $I_C$    | –    | 400  | 500  | mA   |
| Input Power <sup>Note</sup>  | $P_{in}$ | –    | 12   | 17   | dBm  |

**Note** Input power under conditions of  $V_{CE} \leq 4.5\text{ V}$ ,  $f = 460\text{ MHz}$

**ELECTRICAL CHARACTERISTICS (T<sub>A</sub> = +25°C)**

| Parameter                 | Symbol                            | Test Conditions                                                                                          | MIN. | TYP. | MAX. | Unit |
|---------------------------|-----------------------------------|----------------------------------------------------------------------------------------------------------|------|------|------|------|
| DC Characteristics        |                                   |                                                                                                          |      |      |      |      |
| Collector Cut-off Current | I <sub>CBO</sub>                  | V <sub>CB</sub> = 5 V, I <sub>E</sub> = 0 mA                                                             | –    | –    | 1    | μA   |
| Emitter Cut-off Current   | I <sub>EBO</sub>                  | V <sub>EB</sub> = 0.5 V, I <sub>C</sub> = 0 mA                                                           | –    | –    | 1    | μA   |
| DC Current Gain           | h <sub>FE</sub> <sup>Note 1</sup> | V <sub>CE</sub> = 3 V, I <sub>C</sub> = 100 mA                                                           | 80   | 120  | 180  | –    |
| RF Characteristics        |                                   |                                                                                                          |      |      |      |      |
| Gain Bandwidth Product    | f <sub>T</sub>                    | V <sub>CE</sub> = 3.6 V, I <sub>C</sub> = 100 mA, f = 460 MHz                                            | –    | 10   | –    | GHz  |
| Insertion Power Gain      | S <sub>21e</sub>   <sup>2</sup>   | V <sub>CE</sub> = 3.6 V, I <sub>C</sub> = 100 mA, f = 460 MHz                                            | –    | 19   | –    | dB   |
| Maximum Satble Gain       | MSG <sup>Note 2</sup>             | V <sub>CE</sub> = 3.6 V, I <sub>C</sub> = 100 mA, f = 460 MHz                                            | –    | 23   | –    | dB   |
| Linner gain (1)           | G <sub>L</sub>                    | V <sub>CE</sub> = 3.6 V, I <sub>C (set)</sub> = 30 mA (RF OFF),<br>f = 460 MHz, P <sub>in</sub> = 0 dBm  | 16   | 19   | –    | dB   |
| Linner gain (2)           | G <sub>L</sub>                    | V <sub>CE</sub> = 3.6 V, I <sub>C (set)</sub> = 30 mA (RF OFF),<br>f = 900 MHz, P <sub>in</sub> = 0 dBm  | –    | 16   | –    | dB   |
| Output Power (1)          | P <sub>O</sub>                    | V <sub>CE</sub> = 3.6 V, I <sub>C (set)</sub> = 30 mA (RF OFF),<br>f = 460 MHz, P <sub>in</sub> = 15 dBm | 27   | 29   | –    | dBm  |
| Output Power (2)          | P <sub>O</sub>                    | V <sub>CE</sub> = 3.6 V, I <sub>C (set)</sub> = 30 mA (RF OFF),<br>f = 900 MHz, P <sub>in</sub> = 20 dBm | –    | 29   | –    | dBm  |
| Collector Efficiency (1)  | η <sub>c</sub>                    | V <sub>CE</sub> = 3.6 V, I <sub>C (set)</sub> = 30 mA (RF OFF),<br>f = 460 MHz, P <sub>in</sub> = 15 dBm | –    | 60   | –    | %    |
| Collector Efficiency (2)  | η <sub>c</sub>                    | V <sub>CE</sub> = 3.6 V, I <sub>C (set)</sub> = 30 mA (RF OFF),<br>f = 900 MHz, P <sub>in</sub> = 20 dBm | –    | 60   | –    | %    |






**Notes 1.** Pulse measurement: PW ≤ 350 μs, Duty Cycle ≤ 2%

$$2. \text{MSG} = \left| \frac{S_{21}}{S_{12}} \right|$$

**h<sub>FE</sub> CLASSIFICATION**


|                       |           |
|-----------------------|-----------|
| Rank                  | FB        |
| Marking               | SN        |
| h <sub>FE</sub> Value | 80 to 180 |

■ TYPICAL CHARACTERISTICS ( $T_A = +25^\circ\text{C}$ , unless otherwise specified)




**Remark** The graphs indicate nominal characteristics.


DC CURRENT GAIN vs.  
COLLECTOR CURRENT




DC CURRENT GAIN vs.  
COLLECTOR CURRENT




GAIN BANDWIDTH PRODUCT  
vs. COLLECTOR CURRENT




GAIN BANDWIDTH PRODUCT  
vs. COLLECTOR CURRENT



GAIN BANDWIDTH PRODUCT  
vs. COLLECTOR CURRENT




INSERTION POWER GAIN,  
MAG, MSG vs. FREQUENCY




**Remark** The graphs indicate nominal characteristics.


INSERTION POWER GAIN,  
MAG, MSG vs. FREQUENCY




INSERTION POWER GAIN,  
MAG, MSG vs. FREQUENCY




INSERTION POWER GAIN, MAG, MSG  
vs. COLLECTOR CURRENT




INSERTION POWER GAIN, MAG, MSG  
vs. COLLECTOR CURRENT



INSERTION POWER GAIN, MAG, MSG  
vs. COLLECTOR CURRENT




INSERTION POWER GAIN, MAG, MSG  
vs. COLLECTOR CURRENT




**Remark** The graphs indicate nominal characteristics.


INSERTION POWER GAIN, MAG, MSG  
vs. COLLECTOR CURRENT




INSERTION POWER GAIN, MAG, MSG  
vs. COLLECTOR CURRENT




OUTPUT POWER, POWER GAIN,  
COLLECTOR CURRENT, COLLECTOR  
EFFICIENCY vs. INPUT POWER



OUTPUT POWER, POWER GAIN,  
COLLECTOR CURRENT, COLLECTOR  
EFFICIENCY vs. INPUT POWER




NOISE FIGURE, ASSOCIATED GAIN  
vs. COLLECTOR CURRENT



**Remark** The graphs indicate nominal characteristics.


PA EVALUATION BOARD (f = 460 MHz)



Notes

1. 38 × 90 mm, t = 0.8 mm double sided copper clad glass epoxy PWB.
2. Back side: GND pattern
3. Solder gold plated on pattern
4. ○: Through holes


PA EVALUATION CIRCUIT (f = 460 MHz)



The application circuits and their parameters are for reference only and are not intended for use in actual design-ins.


## COMPONENT LIST

|         | Value       | Maker  |
|---------|-------------|--------|
| C1      | 30 pF       | Murata |
| C2      | 6 pF        | Murata |
| C3, C4  | 7 pF        | Murata |
| C5      | 3 pF        | Murata |
| C6      | 0.5 pF      | Murata |
| C7      | 5 pF        | Murata |
| C8      | 10 pF       | Murata |
| C9, C10 | 100 nF      | Murata |
| L1      | 100 nH      | Toko   |
| L2      | 3 nH        | Toko   |
| R1      | 30 $\Omega$ | SSM    |

 PA EVALUATION CIRCUIT TYPICAL CHARACTERISTICS


**Remark** The graph indicates nominal characteristics.


**DISTORTION EVALUATION BOARD (f = 460 MHz)**



**Notes**

1. 38 × 90 mm, t = 0.8 mm, double sided copper clad glass epoxy PWB.
2. Back side: GND pattern
3. Solder gold plated on pattern
4. ○○: Through holes

**DISTORTION EVALUATION CIRCUIT (f = 460 MHz)**




The application circuits and their parameters are for reference only and are not intended for use in actual design-ins.

## COMPONENT LIST

|          | Value       | Maker  |
|----------|-------------|--------|
| C1       | 47 pF       | Murata |
| C2       | 12 pF       | Murata |
| C3, C4   | 7 pF        | Murata |
| C5       | 3 pF        | Murata |
| C6       | 6 pF        | Murata |
| C7       | 0.5 pF      | Murata |
| C8       | 5 pF        | Murata |
| C9       | 51 pF       | Murata |
| C10, C12 | 100 nF      | Murata |
| C11      | 1 $\mu$ F   | Murata |
| L1       | 100 nH      | Toko   |
| L2       | 15 nH       | Toko   |
| R1       | 30 $\Omega$ | SSM    |

## DISTORTION EVALUATION CIRCUIT TYPICAL CHARACTERISTICS


### 3RD ORDER INTERMODULATION DISTORTION vs. 1 TONE OUTPUT POWER



**Remark** The graph indicates nominal characteristics.

## PACKAGE DIMENSIONS

3-PIN POWER MINIMOLD (34 PACKAGE) (UNIT: mm)



## PIN CONNECTIONS

1. Collector
2. Emitter
3. Base

- **The information in this document is current as of July, 2004. The information is subject to change without notice. For actual design-in, refer to the latest publications of NEC's data sheets or data books, etc., for the most up-to-date specifications of NEC semiconductor products. Not all products and/or types are available in every country. Please check with an NEC sales representative for availability and additional information.**
- No part of this document may be copied or reproduced in any form or by any means without prior written consent of NEC. NEC assumes no responsibility for any errors that may appear in this document.
- NEC does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from the use of NEC semiconductor products listed in this document or any other liability arising from the use of such products. No license, express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC or others.
- Descriptions of circuits, software and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software and information in the design of customer's equipment shall be done under the full responsibility of customer. NEC assumes no responsibility for any losses incurred by customers or third parties arising from the use of these circuits, software and information.
- While NEC endeavours to enhance the quality, reliability and safety of NEC semiconductor products, customers agree and acknowledge that the possibility of defects thereof cannot be eliminated entirely. To minimize risks of damage to property or injury (including death) to persons arising from defects in NEC semiconductor products, customers must incorporate sufficient safety measures in their design, such as redundancy, fire-containment, and anti-failure features.
- NEC semiconductor products are classified into the following three quality grades:  
 "Standard", "Special" and "Specific". The "Specific" quality grade applies only to semiconductor products developed based on a customer-designated "quality assurance program" for a specific application. The recommended applications of a semiconductor product depend on its quality grade, as indicated below. Customers must check the quality grade of each semiconductor product before using it in a particular application.  
 "Standard": • Computers, office equipment, communications equipment, test and measurement equipment, audio  
 • and visual equipment, home electronic appliances, machine tools, personal electronic equipment  
 • and industrial robots  
 "Special": • Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster  
 • systems, anti-crime systems, safety equipment and medical equipment (not specifically designed  
 • for life support)  
 "Specific": • Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life  
 • support systems and medical equipment for life support, etc.  
 The quality grade of NEC semiconductor products is "Standard" unless otherwise expressly specified in NEC's data sheets or data books, etc. If customers wish to use NEC semiconductor products in applications not intended by NEC, they must contact an NEC sales representative in advance to determine NEC's willingness to support a given application.  
 (Note)  
 (1) "NEC" as used in this statement means NEC Corporation, NEC Compound Semiconductor Devices, Ltd.  
 • and also includes its majority-owned subsidiaries.  
 (2) "NEC semiconductor products" means any semiconductor product developed or manufactured by or for  
 • NEC (as defined above).

M8E 00.4-0110

---

► **For further information, please contact**

**NEC Compound Semiconductor Devices, Ltd.** <http://www.ncsd.necel.com/>

E-mail: [salesinfo@ml.ncsd.necel.com](mailto:salesinfo@ml.ncsd.necel.com) (sales and general)

[techinfo@ml.ncsd.necel.com](mailto:techinfo@ml.ncsd.necel.com) (technical)

Sales Division TEL: +81-44-435-1588 FAX: +81-44-435-1579

**NEC Compound Semiconductor Devices Hong Kong Limited**

E-mail: [ncsd-hk@elhk.nec.com.hk](mailto:ncsd-hk@elhk.nec.com.hk) (sales, technical and general)

Hong Kong Head Office TEL: +852-3107-7303 FAX: +852-3107-7309

Taipei Branch Office TEL: +886-2-8712-0478 FAX: +886-2-2545-3859

Korea Branch Office TEL: +82-2-558-2120 FAX: +82-2-558-5209

**NEC Electronics (Europe) GmbH** <http://www.ee.nec.de/>

TEL: +49-211-6503-0 FAX: +49-211-6503-1327

**California Eastern Laboratories, Inc.** <http://www.cel.com/>

TEL: +1-408-988-3500 FAX: +1-408-988-0279