





Bidirectional Asymmetrical (BiAs) Single Line ESD Protection Diode in LLP1006-2L



MARKING (example only)



Bar = pin 1 marking

Y = type code (see table below)

X = date code

DESIGN SUPPORT TOOLS click logo to get started



FEATURES

- Ultra compact LLP1006-2L
- Low package height < 0.4 mm
- 1-line ESD protection
- Working range -7 V up to +14 V or -14 V up to +7 V
- Low leakage current < 0.1 μ A
- Low load capacitance typical C_D = 8 pF
- ESD immunity acc. IEC 61000-4-2
± 25 kV contact discharge
± 30 kV air discharge
- e4 - precious metal (e.g. Ag, Au, NiPd, NiPdAu) (no Sn)
- e3 - Sn
Tin plated exposed side wall of leadframe.
Soldering can be checked by standard vision inspection.
(AOI = Automated Outgoing Inspection)
No X-ray necessary
- PATENT(S): www.vishay.com/patents
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

ORDERING INFORMATION

PIN PLATING	DEVICE NAME	ORDERING CODE	TAPED UNITS PER REEL (8 mm TAPE ON 7" REEL)	MINIMUM ORDER QUANTITY
e4	VCUT0714A-HD1	VCUT0714A-HD1-GS08	8000	8000
e3	VCUT0714AHD1	VCUT0714AHD1-G3-08	10 000	100 000

PACKAGE DATA

DEVICE NAME	PACKAGE NAME	PIN PLATING	TYPE CODE	WEIGHT	MOLDING COMPOUND FLAMMABILITY RATING	MOISTURE SENSITIVITY LEVEL	SOLDERING CONDITIONS
VCUT0714A-HD1	LLP1006-2L	e4	B	0.72 mg	UL 94 V-0	MSL level 1 (according J-STD-020)	260 °C/10 s at terminals
VCUT0714AHD1	LLP1006-2L	e3	7	0.72 mg	UL 94 V-0	MSL level 1 (according J-STD-020)	260 °C/10 s at terminals

ABSOLUTE MAXIMUM RATINGS VCUT0714A-HD1


PARAMETER	TEST CONDITIONS	SYMBOL	VALUE	UNIT
Peak pulse current	Pin 1 to pin 2 acc. IEC 61000-4-5, 8/20 μ s/single shot	I_{PPM}	5	A
	Pin 2 to pin 1 acc. IEC 61000-4-5, 8/20 μ s/single shot		2	A
Peak pulse power	Pin 1 to pin 2 acc. IEC 61000-4-5, 8/20 μ s/single shot	P_{PP}	63	W
	Pin 2 to pin 1 acc. IEC 61000-4-5, 8/20 μ s/single shot		54	W
ESD immunity	Contact discharge acc. IEC 61000-4-2; 10 pulses	V_{ESD}	± 25	kV
	Air discharge acc. IEC 61000-4-2; 10 pulses		± 30	kV
Operating temperature	Junction temperature	T_J	-40 to +125	°C
Storage temperature		T_{STG}	-55 to +150	°C

PATENT(S): www.vishay.com/patents

This Vishay product is protected by one or more United States and international patents.

CUT THE SPIKES WITH VCUT0714A-HD1

The VCUT0714A-HD1 is a bidirectional but asymmetrical (BiAs) ESD protection device which clamps positive and negative overvoltage transients to ground. Connected between the signal or data line and the ground the VCUT0714A-HD1 offers a high isolation (low leakage current, small capacitance) within the specified working range of -7 V to +14 V or -14 V and +7 V. Due to the short leads and small package size of the tiny LLP1006-2L package the line inductance is very low, so that fast transients like an ESD strike can be clamped with minimal over- or undershoots.



22286

ELECTRICAL CHARACTERISTICS VCUT0714A-HD1 (pin 2 to pin 1)

(T_{amb} = 25 °C, unless otherwise specified)

PARAMETER	TEST CONDITIONS/REMARKS	SYMBOL	MIN.	TYP.	MAX.	UNIT
Protection paths	Number of lines which can be protected	N _{channel}	-	-	1	lines
Reverse stand-off voltage	Max. reverse working voltage	V _{RWM}	-	-	14	V
Reverse voltage	At I _R = 0.1 μA	V _R	14	-	-	V
Reverse current	At V _{RWM} = 14 V	I _R	-	-	0.1	μA
Reverse breakdown voltage	At I _R = 1 mA	V _{BR}	14.5	-	-	V
Reverse clamping voltage	At I _{PP} = 1 A	V _C	-	-	27	V
	At I _{PP} = I _{PPM} = 2 A	V _C	-	-	30	V
Capacitance	At V _R = 0 V; f = 1 MHz	C _D	-	8	8.5	pF
	At V _R = 7 V; f = 1 MHz	C _D	-	4	-	pF

ELECTRICAL CHARACTERISTICS (pin 1 to pin 2)

(T_{amb} = 25 °C, unless otherwise specified)

PARAMETER	TEST CONDITIONS/REMARKS	SYMBOL	MIN.	TYP.	MAX.	UNIT
Protection paths	Number of lines which can be protected	N _{channel}	-	-	1	lines
Reverse stand-off voltage	Max. reverse working voltage	V _{RWM}	-	-	7	V
Reverse voltage	At I _R = 0.1 μA	V _R	7	-	-	V
Reverse current	At V _{RWM} = 7 V	I _R	-	-	0.1	μA
Reverse breakdown voltage	At I _R = 1 mA	V _{BR}	7.3	-	-	V
Reverse clamping voltage	At I _{PP} = 1 A	V _C	-	-	13	V
	At I _{PP} = I _{PPM} = 5 A	V _C	-	-	17	V
Capacitance	At V = 0 V; f = 1 MHz	C _D	-	8	8.5	pF
	At V = 3.5 V; f = 1 MHz	C _D	-	6.4	-	pF



TYPICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)




Fig. 1 - ESD Discharge Current Wave Form
acc. IEC 61000-4-2 (330 Ω /150 pF)




Fig. 2 - 8/20 μ s Peak Pulse Current Wave Form
acc. IEC 61000-4-5




Fig. 3 - Typical Capacitance C_D vs. Reverse Voltage V_R




Fig. 4 - Typical Reverse Voltage V_R vs. Reverse Current I_R




Fig. 5 - Typical Peak Clamping Voltage V_C vs.
Peak Pulse Current I_{PP}




Fig. 6 - Typical Clamping Performance at +8 kV
Contact Discharge (acc. IEC 61000-4-2)




Fig. 7 - Typical Clamping Performance at - 8 kV Contact Discharge (acc. IEC 61000-4-2)






Fig. 8 - Typical Peak Clamping Voltage at ESD Contact Discharge (acc. IEC 61000-4-2)


PACKAGE DIMENSIONS in millimeters (inches): LLP1006-2L



Foot print recommendation:



Pad Design Patented:
(©US 9.018.537 B2)



S8-V-3906.04-017 (4)
02.05.2017
22965



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.