

1:1 RF Transformer 5-1200MHz

Rev. V3

Features

- Key Surface Mount
- 1:1 RF Transformer
- 260°C Reflow Compatible
- RoHS Compliant and Pb Free
- RoHS version of ETC1-1T-75
- Available on Tape and Reel

Description


M/A-COM's MABA-007748-CT1160 is a 1:1 RF Transformer in a low cost, surface mount package. Ideally suited for high volume CATV/ Broadband applications.



Ordering Information

Part Number	Package	
MABA-007748-CT1160	2000 piece reel	
MABA-007748-CT11TB	Sample Board	


Functional Schematic



Pin Configuration

Pin No.	Function	
1	Secondary (Dot)	
2	Not connected	
3	Secondary	
4	Primary	
5	Primary (Dot)	

Case Style: SM-22



Dimensions in inches [mm] Tolerance: .xx ± .02, .xxx ± .010

MABA-007748-CT1160



1:1 RF Transformer

5-1200MHz Rev. V3


Electrical Specifications: Freq. = 5-1200MHz, $T_A = +25$ °C, $Z_0 = 75\Omega$

Parameter	Test Conditions	Units	Min.	Тур.	Max.
	5 - 40 MHz	dB	-	0.27	0.5
Insertion Loss	40 - 600 MHz	dB	-	0.32	1.0
IIISELIIOII LOSS	600 - 1000 MHz	dB	-	0.57	2.0
	1000 - 1200 MHz	dB	-	1.62	3.0
Amplitude Balance	5 - 1200 MHz	dB	-	0.36	1.0
Phase Balance	5 - 1000 MHz	О	-	0.58	10
That Balance	1000 - 1200 MHz	O	-	9.15	20
	5 - 40 MHz	dB	17	27	-
	40 - 200 MHz	dB	22	29	-
Input Return Loss	200 - 400 MHz	dB	15	22	-
	400 - 600 MHz	dB	10	17	-
	600 - 1200 MHz	dB	6	11	-

Absolute Maximum Ratings

Parameter	Absolute Maximum		
raiailletei	Absolute Maximum		
RF Power	250 mW		
DC current	30mA		
Operating Temperature	-40°C to +85°C		
Storage Temperature	-40°C to +85°C		

Recommended PCB Configuration




MABA-007748-CT1160




1:1 RF Transformer 5-1200MHz Rev. V3

Typical Performance Curves: $TA = 25^{\circ}C$, $Z0 = 75\Omega$


Insertion Loss 1: Pin5 - Pin3




Insertion Loss 2: Pin5 - Pin1




Amplitude Balance



Phase Balance



Return Loss: Input



Frequency (MHz)

3

MABA-007748-CT1160



1:1 RF Transformer 5-1200MHz

Rev. V3

MACOM Technology Solutions Inc. All rights reserved.

Information in this document is provided in connection with MACOM Technology Solutions Inc ("MACOM") products. These materials are provided by MACOM as a service to its customers and may be used for informational purposes only. Except as provided in MACOM's Terms and Conditions of Sale for such products or in any separate agreement related to this document, MACOM assumes no liability whatsoever. MACOM assumes no responsibility for errors or omissions in these materials. MACOM may make changes to specifications and product descriptions at any time, without notice. MACOM makes no commitment to update the information and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to its specifications and product descriptions. No license, express or implied, by estoppels or otherwise, to any intellectual property rights is granted by this document.

THESE MATERIALS ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, CONSEQUENTIAL OR INCIDENTAL DAMAGES, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT. MACOM FURTHER DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. MACOM SHALL NOT BE LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS, WHICH MAY RESULT FROM THE USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.

4