








- 1 PARTS COMPLY WITH AMP SOLDERABILITY SPECIFICATION 109-11-3.
- 4 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5 CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- 6 CONTACT IS PLATED OVERALL WITH .000050[0.00127] NICKEL, THEN .000030[0.00076] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN LEAD ON SOLDER TAIL END.
- 7 CONTACT IS PLATED OVERALL WITH .000050[0.00127] NICKEL, THEN .000030[0.00076] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
- 8 SUPERSEDED BY 350583-4



RECOMMENDED MOUNTING HOLE PATTERN
FOR 3.18 [0.125] THICK P.C. BOARD



PHOSPHOR BRONZE, GOLD		NYLON,UL94V-2,NATURAL	350583-4
PHOSPHOR BRONZE, GOLD		NYLON,UL94V-2,NATURAL	350583-2
PHOSPHOR BRONZE, PRE-TIN		NYLON,UL94V-2,NATURAL	350583-1
PIN CONTACT MATERIAL AND FINISH		HOUSING MATERIAL	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 2-19-97 CHK R. SWING 2-19-97 APVD -	TE Connectivity
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [0.005] 3 PLC ± - 4 PLC ± - ANGLES ± -	NAME PRODUCT SPEC APPLICATION SPEC SIZE CAGE CODE DRAWING NO RESTRICTED TO
MATERIAL SEE TABLE		FINISH SEE TABLE	WEIGHT -
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1 REV U1