

**Cable glands  
VG 11-MS54****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



An economical plastic cable gland, such as you often find in industrial applications. With their soft rubber seal, they offer a secure fit for the cable and a good IP protection degree (IP 54). In addition, the nickel-plated brass gives you good corrosion protection from external influences.

**General ordering data**

|            |                                                        |
|------------|--------------------------------------------------------|
| Order No.  | <a href="#">0260700000</a>                             |
| Type       | VG 11-MS54                                             |
| Version    | Cable glands, Cable gland, Brass, nickel-plated, PG 11 |
| GTIN (EAN) | 4008190170523                                          |
| Qty.       | 50 pc(s).                                              |

## Cable glands VG 11-MS54

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|        |       |            |         |
|--------|-------|------------|---------|
| Length | 26 mm | Net weight | 18.72 g |
|--------|-------|------------|---------|

### General information

|                                     |                      |                                          |                |
|-------------------------------------|----------------------|------------------------------------------|----------------|
| AF size 1                           | 18 mm                | AF size 2                                | 20 mm          |
| Cable gland                         | PG                   | Clamping range, bolted connection , max. | 10 mm          |
| Clamping range, min. test adapter   | 8 mm                 | DIN                                      | DIN 46320 / C4 |
| External thread                     | PG 11                | Length of thread                         | 6 mm           |
| Material                            | Brass, nickel-plated | Operating temperature range, max.        | 60 °C          |
| Operating temperature range, min.   | -20 °C               | Protection degree with GWDR              | IP 65          |
| Seal insert                         | NBR                  | Torque for cap nut, max.                 | 12.4 Nm        |
| Torque for cap nut, min.            | 12.4 Nm              | Torque for connecting adapter, max.      | 18.6 Nm        |
| Torque for connecting adapter, min. | 18.6 Nm              |                                          |                |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 2.0   | EC000441    | ETIM 3.0   | EC000441    |
| UNSPSC     | 30-21-18-01 | eClass 4.1 | 27-14-12-09 |
| eClass 5.1 | 27-14-91-09 | eClass 6.0 | 27-14-91-11 |
| eClass 7.0 | 27-14-91-11 |            |             |

### Approvals

Approvals

