

VS-TO-IW-2-F-9010

Order No.: 1653016

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1653016>

Terminal outlet, flush-type mounting, IP20, two slots for contact inserts
with the Freenet system

Commercial data

GTIN (EAN)	4017918962081
sales group	D551
Pack	1 pcs.
Customs tariff	85366990
Weight/Piece	0.0486 KG
Catalog page information	Page 199 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
01/01/2008



[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data

Mechanical characteristics

Number of slots	2
Color	Pure white RAL 9010
Ambient temperature (operation)	5 °C ... 55 °C

Material data

Inflammability class acc. to UL 94	HB
Housing material	PC+ABS
Degree of protection	IP20

Accessories

Item	Designation	Description
Female insert		
1652936	VS-08-BU-RJ45-5-F/PK	RJ45 socket insert, for the Freenet system, CAT5e, 8-pos., shielded, with cable connection (IDC fast connection), for solid wires AWG 24 ... 22
1652949	VS-08-BU-RJ45-6-F/PK	RJ45 socket insert, for the Freenet system, CAT6, 8-pos., shielded, with cable connection (IDC fast connection), for litz and solid wires AWG 24 ... 22
1654358	VS-SCRJ-GOF-KU	SCRJ coupling insert, duplex, for VS-PP-19-1HE-16-F patch panel and VS-TO...F...terminal outlets and VS-SI-FP-2F front plate, can be used for glass multi-mode, HCS and polymer fiber types

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;