


Standard Products!! SLF12575-H TYPE Automotive Target SMD Power Inductor

Component Image & Dimension




Features :

- Component Size :
Mount Area : 12.5mm x 12.5mm
Low Profile : 7.85mm Max. Height
- Generic use for Automotive Appliance.
This product guarantees operation in high temperature.
Operation temperature : -40°C ~ +125°C
(Including self-temperature rise +40°C)
Storage temperature : -40°C ~ +125°C
- High Magnetic Shield Construction should actualize
High Resolution for EMC Protection.
- Automatic Mounting in Tape&Reel Package.
- Qualified acc. AEC-Q200.

Applications :

Automotive Appliance (ECM, HID, Air Bag, Transmission Control, Car Navigation, Car Audio, GPS System) etc.

*Recommended Land Pattern (Unit : mm)



Electrical Specification

TDK Identification		Inductance		Test	DC Resistance		Rated DC Current	
		Spec.	Tol.	Freq.	Spec.	Tol.	Idc 1	Idc 2
		(μH)		(kHz)	(Ω)		(A max.)	(A Typ.)
SLF12575T-	1R2N8R2-H	1.2	+/-30%	1	5.1m	+/-20%	13	8.2
SLF12575T-	2R7N7R0-H	2.7	+/-30%	1	7.4m	+/-20%	10	7.0
SLF12575T-	3R9N6R7-H	3.9	+/-30%	1	10.4m	+/-20%	9.0	6.7
SLF12575T-	5R6N6R3-H	5.6	+/-30%	1	11.6m	+/-20%	7.8	6.3
SLF12575T-	6R8N5R9-H	6.8	+/-30%	1	13.1m	+/-20%	7.2	5.9
SLF12575T-	100M5R4-H	10	+/-20%	1	15.6m	+/-20%	5.5	5.4
SLF12575T-	150M4R7-H	15	+/-20%	1	18.4m	+/-20%	4.7	5.0
SLF12575T-	220M4R0-H	22	+/-20%	1	26.3m	+/-20%	4.0	4.0
SLF12575T-	330M3R2-H	33	+/-20%	1	39.5m	+/-20%	3.2	3.4
SLF12575T-	470M2R7-H	47	+/-20%	1	52.8m	+/-20%	2.7	3.0
SLF12575T-	680M2R0-H	68	+/-20%	1	77.8m	+/-20%	2.0	2.4
SLF12575T-	101M1R9-H	100	+/-20%	1	0.125	+/-20%	1.9	1.9
SLF12575T-	151M1R5-H	150	+/-20%	1	0.175	+/-20%	1.5	1.6
SLF12575T-	221M1R3-H	220	+/-20%	1	0.258	+/-20%	1.3	1.3
SLF12575T-	331M1R0-H	330	+/-20%	1	0.34	+/-20%	1.0	1.1
SLF12575T-	471MR80-H	470	+/-20%	1	0.60	+/-20%	0.8	0.8

Note) Idc 1 : Depend on the Inductance Saturation. (-10% Saturation from Initial L Value)
Idc 2 : Depend on the self temperature rise. (+40°C typ.)

