

BIDIRECTIONAL MONOLITHIC TVS DIODE ARRAY

APPLICATIONS

- ✓ RS-232, RS-423 Data Lines
- ✓ Cellular Phones
- ✓ Audio/Video Inputs
- ✓ Portable Electronics
- ✓ Wireless Network Systems

IEC COMPATIBILITY (EN61000-4)


- ✓ 61000-4-2 (ESD): Air - 15kV, Contact - 8kV
- ✓ 61000-4-4 (EFT): 40A - 5/50ns
- ✓ 61000-4-5 (Surge): 24A, 8/20 μ s Level 2(Line-Gnd) & Level 3(Line-Line)

FEATURES


- ✓ 500 Watts Peak Pulse Power Per Line ($t_p = 8/20\mu$ s)
- ✓ Bidirectional Monolithic Design
- ✓ Available in 4 Voltage Types Ranging from 5V to 24V
- ✓ Protects Up to Four (4) Lines
- ✓ ESD Protection > 40 kilovolts

MECHANICAL CHARACTERISTICS

- ✓ Molded JEDEC SO-8
- ✓ Weight 15 milligrams (Approximate)
- ✓ Flammability Rating UL 94V-0
- ✓ 12mm Tape and Reel Per EIA Standard 481
- ✓ Device Marking: Marking Code & Logo
- ✓ Pin 1 Indicated By Dot on Top of Package



CIRCUIT DIAGRAM



PSMDA05C-4 thru PSMDA24C-4

DEVICE CHARACTERISTICS

MAXIMUM RATINGS @ 25°C Unless Otherwise Specified			
PARAMETER	SYMBOL	VALUE	UNITS
Peak Pulse Power ($t_p = 8/20\mu s$) - See Figure 1	P_{PP}	500	Watts
Operating Temperature	T_J	-55°C to 150°C	°C
Storage Temperature	T_{STG}	-55°C to 150°C	°C


ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified							
PART NUMBER (See Note 1)	DEVICE MARKING	RATED STAND-OFF VOLTAGE V_{WM}	MINIMUM BREAKDOWN VOLTAGE @ 1mA $V_{(BR)}$	MAXIMUM CLAMPING VOLTAGE (See Fig. 2) @ $I_p = 1A$ V_C	MAXIMUM CLAMPING VOLTAGE (See Fig. 2) @ 8/20μs	MAXIMUM LEAKAGE CURRENT @ V_{WM} I_d	MAXIMUM CAPACITANCE 0V @ 1 MHz C
PSMDA05C-4	TEB	5.0	6.0	9.8	19V @ 30A	100	350
PSMDA12C-4	TED	12.0	13.3	19.0	29V @ 20A	1	150
PSMDA15C-4	TEF	15.0	16.7	24.0	32V @ 18A	1	120
PSMDA24C-4	TEH	24.0	26.7	43.0	45V @ 13A	1	100

Note 1: Test individual pins 8 or 5 to pins 1, 2, 3, or 4. Pins 6 and 7 are open.


PSMDA05C-4 thru PSMDA24C-4

GRAPHS


**FIGURE 1
PEAK PULSE POWER VS PULSE TIME**



**FIGURE 2
PULSE WAVE FORM**




**FIGURE 3
POWER DERATING CURVE**



PSMDA05C-4 thru PSMDA24C-4

PACKAGE OUTLINE & DIMENSIONS



TAPE & REEL PACKAGING:

Surface mount product is taped and reeled in accordance with EIA-481, reel quantities and sizes are as follows:

7 Inch Reel - 1,000 pieces per reel; 13 Inch Reel - 2,500 pieces per reel

COPYRIGHT © ProTek Devices 2001

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice (except JEDEC).

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice, and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance, ProTek assumes no responsibility with respect to the selection or specifications of such products.

ProTek Devices

2929 South Fair Lane, Tempe, AZ 85282

Tel: 602-431-8101 Fax: 602-431-2288

E-Mail: sales@protekdevices.com

Web Site: www.protekdevices.com