


**Part Number: 104040-0207****2.0mm Wire-to-Board Power Header Connector, 2 Circuits**

Status: Contact Molex
Series: 104040
Category: Crimp Housings

Series image - Reference only

Mates With Part(s):[1040410290](#) 2.0mm Wire-to-Board Power Connector Housing**Product Environmental Compliance****EU RoHS:** ELV and RoHS Compliant**China RoHS:****REACH SVHC:** Contains SVHC: No**Low-Halogen Status:** Not Reviewed**Part Detail****General**

Status	Contact Molex
Category	Crimp Housings
Series	104040
Application	Power, Signal, Wire-to-Board
Product Name	IllumiMate™

Physical

Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	High Temperature Thermoplastic
Number of Rows	1
Packaging Type	Reel
Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-25°C to +130°C

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	2A
-------------------------------	----

Agency Certification

UL	E29179
----	--------

Material Info

UPC	883906726843
-----	--------------

Reference - Drawing Numbers

Sales Drawing	SD-104040-001
---------------	---------------

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

