





LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			V1	REVISED PER ECR-15-006687	26OCT2015	NK	NL



.045	1.14		
.030	0.76	1.000	25.40
.018	0.46	.700	17.78
.015	0.38	.450	11.43
.012	0.30	.415	10.54
.010	0.25	.250	6.35
.008	0.20	.156	3.96
.005	0.13	.140	3.56
.001	0.03	.125	3.18
.000350	0.00889	.078	1.98
.000150	0.00381	.063	1.60
.000050	0.00127	.060	1.52
.000015	0.00089	.051	1.30
.000	0.00	.046	1.17
IN	MM	IN	MM

CONVERSION TABLE

TIN	3.744	95.10	24	5-641203-4	SUPERCEDED 15	TIN-LEAD	3.744	95.10	24	-2-641203-4
TIN	3.588	91.14	23	5-641203-3		TIN-LEAD	3.588	91.14	23	-2-641203-3
TIN	3.432	87.17	22	5-641203-2		TIN-LEAD	3.432	87.17	22	-2-641203-2
TIN	3.276	83.21	21	5-641203-1		TIN-LEAD	3.276	83.21	21	-2-641203-1
TIN	3.120	79.25	20	5-641203-0		TIN-LEAD	3.120	79.25	20	-2-641203-0
TIN	2.964	75.29	19	4-641203-9		TIN-LEAD	2.964	75.29	19	-1-641203-9
TIN	2.808	71.32	18	4-641203-8		TIN-LEAD	2.808	71.32	18	-1-641203-8
TIN	2.652	67.36	17	4-641203-7		TIN-LEAD	2.652	67.36	17	-1-641203-7
TIN	2.496	63.40	16	4-641203-6		TIN-LEAD	2.496	63.40	16	-1-641203-6
TIN	2.340	59.44	15	4-641203-5		TIN-LEAD	2.340	59.44	15	-1-641203-5
TIN	2.184	55.47	14	4-641203-4		TIN-LEAD	2.184	55.47	14	-1-641203-4
TIN	2.028	51.51	13	4-641203-3		TIN-LEAD	2.028	51.51	13	-1-641203-3
TIN	1.872	47.55	12	4-641203-2		TIN-LEAD	1.872	47.55	12	-1-641203-2
TIN	1.716	43.59	11	4-641203-1		TIN-LEAD	1.716	43.59	11	-1-641203-1
TIN	1.560	39.62	10	4-641203-0	OBSOLETE 15	TIN-LEAD	1.560	39.62	10	-1-641203-0
TIN	1.404	35.66	9	3-641203-9		TIN-LEAD	1.404	35.66	9	-641203-9
TIN	1.248	31.70	8	3-641203-8		TIN-LEAD	1.248	31.70	8	-641203-8
TIN	1.092	27.74	7	3-641203-7		TIN-LEAD	1.092	27.74	7	-641203-7
TIN	.936	23.77	6	3-641203-6		TIN-LEAD	.936	23.77	6	-641203-6
TIN	.780	19.81	5	3-641203-5		TIN-LEAD	.780	19.81	5	-641203-5
TIN	.624	15.85	4	3-641203-4		TIN-LEAD	.624	15.85	4	-641203-4
TIN	.468	11.89	3	3-641203-3		TIN-LEAD	.468	11.89	3	-641203-3
TIN	.312	7.92	2	3-641203-2		TIN-LEAD	.312	7.92	2	-641203-2
FINISH	IN	MM	NUMBER OF POSITIONS	PART NUMBER		FINISH	IN	MM	NUMBER OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN B. LEWIS 15MAY96 QWK R. SWING APPROVED D. CLARK 15MAY96		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± 1. PLC ± 2. PLC ± 3. PLC ±.005 4. PLC ± ANGLES ± FINISH		NAME MTA-156 HEADER ASSEMBLY, PLAIN, STRAIGHT, .045 ROUND POST, 000030 GOLD	
		PRODUCT SPEC — APPLICATION SPEC		SIZE CAGE CODE DRAWING NO A1 00779 C-641203	
MATERIAL 		WEIGHT —		RESTRICTED TO CUSTOMER DRAWING	
		SCALE 5:1		SHEET 1 of 1 REV V1	