


Data Sheet 2583 Rev. -

R2500F THRU R5000F HIGH VOLTAGE FAST RECOVERY RECTIFIER

Reverse Voltage - 2500 to 5000 Volts Forward Current - 0.2 Ampere



Dimensions in inches and (millimeters)

FEATURES

- The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- Construction utilizes void-free molded plastic technique
- Low reverse leakage
- High forward surge current capability
- High temperature soldering guaranteed:
250°C/10 seconds, 0.375" (9.5mm) lead length,
5 lbs. (2.3kg) tension

MECHANICAL DATA

Case: JEDEC DO-41/DO-15 molded plastic body

Terminals: Plated axial leads, solderable per MIL-STD-750, Method 2026

Polarity: Color band denotes cathode end

Mounting Position: Any

Weight: 0.012 ounce, 0.33 grams(DO-41)
0.014 ounce, 0.40 grams(DO-15)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

	SYMBOLS	R2500F	R3000F	R4000F	R5000F	UNITS
Maximum repetitive peak reverse voltage	V _{RRM}	2500	3000	4000	5000	VOLTS
Maximum RMS voltage	V _{RMS}	1750	2100	2800	3500	VOLTS
Maximum DC blocking voltage	V _{DC}	2500	3000	4000	5000	VOLTS
Maximum average forward rectified current 0.375" (9.5mm) lead length (see fig.1)	I _(AV)	0.2				Amp
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}	30.0				Amps
Maximum instantaneous forward voltage at 0.2 A	V _F	4.0	5.0	6.5		Volts
Maximum DC reverse current T _A =25°C at rated DC blocking voltage T _A =100°C	I _R	5.0 50.0				µA
Maximum reverse recovery time (NOTE 1)	t _{rr}	500				ns
Typical junction capacitance (NOTE 2)	C _J	15.0				pF
Typical thermal resistance (NOTE 3)	R _{θJA}	50.0				°C/W
Operating junction and storage temperature range	T _J , T _{STG}	-65 to +150				°C

Note: 1.Reverse recovery condition I_F=0.5A, I_R=1.0A, I_{rr}=0.25A


2.Measured at 1MHz and applied reverse voltage of 4.0V D.C.

3.Thermal resistance from junction to ambient at 0.375" (9.5mm) lead length, P.C.B. mounted


Data Sheet 2583 Rev. -

RATINGS AND CHARACTERISTIC CURVES R2500F THRU R5000F


AVERAGE FORWARD RECTIFIED CURRENT,
AMPERES




PEAK FORWARD SURGE CURRENT,
AMPERES




INSTANTANEOUS FORWARD
CURRENT, AMPERES



INSTANTANEOUS REVERSE CURRENT,
MICROAMPERES



JUNCTION CAPACITANCE, pF



TRANSIENT THERMAL IMPEDANCE,
°C/W

