

## AUTOMOTIVE, TRUCK, BUS, & OFF-ROAD HOUSINGS



✓ Active

TE CONNECTIVITY (TE)

### MQS SOCKET HSG 3 PO

MQS

1-1718346-3

TE Internal Number: 1-1718346-3

EU RoHS Compliant

EU ELV Compliant

**Connector Style** Housing for female terminals

**Mating Tab Width** .63 mm [.025 in]

**Connector System** Wire-to-Wire

**Number of Positions** 3

**Centerline (Pitch)** 2.54 mm [.1 in]

 **PRODUCT DRAWING**  
English

 **3D PDF**

## DOCUMENTATION

Product Drawings

### Micro Quadlok System Buchsengeh., 3 Polig SOCKET HSG., 3POS.

PDF [\(TIFF AVAILABLE\)](#)

English

CAD Files

### Customer View Model

2D\_DXF.ZIP

English

### 3D PDF

PDF

3D

## Customer View Model

3D\_IGS.ZIP

English

## Customer View Model

3D\_STP.ZIP

English

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

### Product Type Features

**Connector Style** Housing for female terminals

**Connector System** Wire-to-Wire

**Sealable** No

**Hybrid Connector** No

**Primary Locking Feature** On the terminal

**Strain Relief** No

### Configuration Features

**Number of Positions** 3

**Number of Rows** 1

### Body Features

**Color** Other

**Cable Exit Angle** 180°

**Body Material** PBT GF

### Contact Features

**Mating Tab Width** .63 mm [.025 in]

### Mechanical Attachment

**Mounting Feature** No

**Terminal Position Assurance** Yes

**Polarized** Yes

### Housing Features

**Centerline (Pitch)** 2.54 mm [.1 in]

### Dimensions

**Width** 16.7 mm [.657 in]

**Height** 6.2 mm [.244 in]

**Length** 11 mm [.433 in]

### Usage Conditions

**Operating Temperature Range** -40 – 80 °C [ -40 – 176 °F ]

---

Operation/Application

**Circuit Application** Signal

---

Industry Standards

**UL Flammability Rating** UL 94-HB

---

Packaging Features

**Packaging Method** Box

---

Other

**Connector Position Assurance Capable** No

**Serviceable** No

---

## PRODUCT COMPLIANCE



Statement of Compliance

**Statement of Compliance**

PDF