







NOTES:
1 - SEAL FURNISHED BY USER
2 - ROLLER LEVER MAY BE LOCKED IN ANY POSITION THRU 360°

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING TORQUE --- 3 IN-LB MAX

SWITCH - BASIC REPLACEMENT --- 2MNI

ELECTRICAL DATA

CONTACT ARRANGEMENT
(SEE CIRCUIT DIAGRAM)

10A-120, 240, OR 480 VAC, 1/3 HP - 120 VAC
3/4 HP - 240 VAC; 0.8A - 115 VDC; 0.4A - 230 VDC
.1A - 550 VDC
PILOT DUTY: 600 VAC MAX

SCALE 1/2 TO 1

DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED
DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT

DRAWING NUMBER		6LS3
RELEASE NO. MPS SR11843		
REPLACES		
CHECK		
REVISIONS		
A	CO18785	
B	SR11843	
C	CO20495	
D	CO23403	
E	CO25182	
F	CO30952-G	
G	CO33005-D	
H	CO57786-B	
J	CO65814-E	
K	CO77031	
DRAWN		
RES		
11 JUNE 64		
22 DEC 93		