






DO NOT SCALE
DIMENSIONS IN mm

METRIC


THIRD ANGLE
PROJECTION




SECTION A-A



WIRE RANGE :
1.0-2.5 mm?
INSULATION RANGE :
3.0-4.3mm DIA.



SECTION B-B



SECTION C-C

NOTES:

- 1 FOR USE ON MINIATURE APPLICATOR (LEFT-RIGHT FEED)
- 2 REELED WITH PAPER.
- 3 CONFIGURATION OF CARRIER-STRIP OPTIONAL.
- 4 FOR USE ON MINIATURE APPLICATOR (LEFT-RIGHT FEED) AMP-O-MATOR APPLICATION.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

5 OBSOLETE	PRE-TIN PLATED	PH.BRONZE	4	6-160831-8
	PRE-TIN PLATED	BRASS	4	6-160831-7
	TIN PLATED	PH.BRONZE	4	1-160831-2
	UNPLATED	BRASS	4	1-160831-1
5 OBSOLETE	TIN PLATED	BRASS	4	1-160831-0
	UNPLATED	NICKEL-SILVER		0-160831-9
	SILVERPLATED	PH.BRONZE		0-160831-8
	SILVERPLATED	BRASS		0-160831-7
5 OBSOLETE	UNPLATED	BRASS	2	0-160831-6
	UNPLATED	PH.BRONZE	2	0-160831-5
	TIN PLATED	PH.BRONZE		0-160831-4
	TIN PLATED	BRASS		0-160831-3
	UNPLATED	PH.BRONZE		0-160831-2
	UNPLATED	BRASS		0-160831-1
	FINISH	MATERIAL		PART NUMBER

					CUSTOMER DRAWING		FOR REFERENCE ONLY WILL NOT BE UPDATED						
					THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION _____, 19____								
					 TE Connectivity								
					NAME								
M2	ECO-11-005294		RK	HMR	19APR11	POSITIVE LOCK RECEPTACLE .250 (6,35) SERIES							
LTR.	REVISION RECORD		DR.	CHK.	DATE								
DR.:	J.v.LIEMPT		CHK.:	M.v.DRIEL		APP.:	M.v.DRIEL		DWG.No.		REV.LTR.	SHEET	
DATE:	07 FEB 97		DATE:	18 FEB 02		DATE:	18 FEB 02		C - 160831		M2	1 OF 1	