




SEE SHEET 2 FOR HOLE PATTERN

DETAIL A

1 HOUSING: HIGH TEMPERATURE THERMOPLASTIC. COLOR - NATURAL

2 CONTACT: PHOSPHOR BRONZE.

3 CONTACT FINISH: .001269[.000050] MIN NICKEL ALL OVER. GOLD FLASH OVER NICKEL IN CONTACT AREA. .002537[.000100] MIN MATTE TIN OVER NICKEL ON SOLDER TAILS.

4 CONTACT FINISH: .001269[.000050] MIN NICKEL ALL OVER. .000375[.000015] MIN GOLD OVER NICKEL IN CONTACT AREA. .002537[.000100] MIN MATTE TIN OVER NICKEL ON SOLDER TAILS.

5 CONTACT FINISH: .001269[.000050] MIN NICKEL ALL OVER. .000757[.000030] MIN GOLD OVER NICKEL IN CONTACT AREA. .002537[.000100] MIN MATTE TIN OVER NICKEL ON SOLDER TAILS.

6 DISTANCE FROM CONTACT POINT TO BOTTOM OF CARD SLOT.

7 AMP PART NUMBER, DATE CODE AND CSA LOGO MARKED IN APPROXIMATE LOCATION SHOWN.

8 CORED OR SOLID SIDE WALLS ARE AT DISCRETION OF AMP INCORPORATED.

9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

W	FINISH	PART NUMBER
3.56 [.140]	1-5145166-2	
3.18 [.125]	5145166-8	
2.54 [.100]	5145166-4	
2.54 [.100]	5145166-2	
2.54 [.100]	5145166-1	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.25 [.01]

3 PLC ± 0.125 [.005]

4 PLC ± ± 2°

ANGLES

MATERIAL

FINISH

1 2 3 4 5

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN AL FRANTUM 23 JUN 05

CHK AL FRANTUM 23 JUN 05

APVD -

NAME

PRODUCT SPEC 108-14034

APPLICATION SPEC 114-26012

WEIGHT 0.0

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 OF 2

REV A

TE Connectivity

CONNECTOR ASSEMBLY, 92 DUAL POSITION, 1.27 [.050] SERIES,

RESTRICTED TO

