



Film Capacitors

Metallized Polyester Film Capacitors (MKT)

Series/Type: B32591 ... B32594

Date: August 2004

© EPCOS AG 2004. Reproduction, publication and dissemination of this data sheet, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

Purchase orders are subject to the General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry recommended by the ZVEI (German Electrical and Electronic Manufacturers' Association), unless otherwise agreed.

Typical applications

- Compact fluorescent lamps (CFL)
- Generators

Climatic

- Max. operating temperature: 125 °C
- Climatic category (IEC 60068-1): 55/100/56

Features

- High pulse strength
- High contact reliability

Construction

- Dielectric: polyethylene terephthalate (polyester, PET)
- Stacked-film technology for lead spacing 10 and 15 mm (100 ... 400 VDC); Wound capacitor technology for lead spacing 10 and 15 mm (630 VDC) as well as for lead spacing 22.5 and 27.5 mm
- Epoxy resin coating (UL 94 V-0)

Terminals

- Crimped wire leads, lead-free tinned, lead length 6 – 1 mm or min. 20 mm
- Straight wire leads, lead-free tinned, lead length 17 ±3 mm
- Different lead spacings (reduced and enlarged) available, lead length 6 – 1 mm

Marking

Manufacturer's logo,
rated capacitance (coded),
capacitance tolerance (code letter),
rated DC voltage,
additional for lead spacing ≥15 mm:
style, type, date of manufacture (coded)

Delivery mode


Bulk (untaped)

Taped (Ammo pack or reel) for lead spacing ≤22.5 mm.


For notes on taping, refer to chapter "Taping and packing".

Dimensional drawing

Crimped leads



Straight leads



Dimensions in mm

Lead spacing $e \pm 0.8$	Lead diameter d_1	Type
10.0	0.6 ¹⁾	B32591
15.0	0.6	B32592
22.5	0.8	B32593
27.5	0.8	B32594

1) 0.5 mm for capacitor width $w \leq 5$ mm


Overview of available types

Lead spacing	10.0 mm				15.0 mm				22.5 mm			
Type	B32591				B32592				B32593			
Page	5				6				7			
Technology	s	s	s	w	s	s	s	w	w	w	w	w
V_R (VDC)	100	250	400	630	100	250	400	630	100	250	400	630
V_{rms} (VAC)	63	160	200	200	63	160	200	200	63	160	200	200
C_R (μF)												
0.010												
0.015												
0.022												
0.033												
0.047												
0.068												
0.10												
0.15												
0.22												
0.33												
0.47												
0.68												
1.0												
1.5												
2.2												
3.3												
4.7												
6.8												

Technology: s = Stacked-film technology / w = Wound capacitor technology

Lead configurations

Series	Standard	Reduced	Enlarged	Straight
				
B32591	10 mm	5 / 7.5 mm	–	10 mm
B32592	15 mm	7.5 / 10 / 12.5 mm	17.5 mm	15 mm
B32593	22.5 mm	17.5 / 20 mm	25 mm	22.5 mm
B32594	27.5 mm	25 mm	–	27.5 mm



B32591 ... B32594

General purpose (stacked/wound)


Overview of available types

Lead spacing	27.5 mm			
Type	B32594			
Page	8			
Technology	w	w	w	w
V_R (VDC)	100	250	400	630
V_{rms} (VAC)	63	160	200	220
C_R (μF)				
0.33				
0.47				
0.68				
1.0				
1.5				
2.2				
3.3				
4.7				
6.8				
10				

Technology: s = Stacked-film technology / w = Wound capacitor technology

Lead configurations

Series	Standard	Reduced	Enlarged	Straight
				
B32591	10 mm	5 / 7.5 mm	—	10 mm
B32592	15 mm	7.5 / 10 / 12.5 mm	17.5 mm	15 mm
B32593	22.5 mm	17.5 / 20 mm	25 mm	22.5 mm
B32594	27.5 mm	25 mm	—	27.5 mm


Ordering codes and packing units (lead spacing 10 mm)

V_R	V_{rms} $f \leq 60 \text{ Hz}$	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Ammo pack pcs./unit	Reel pcs./unit	Untaped pcs./unit
VDC	VAC	μF					
100	63	0.10	$5.0 \times 9.0 \times 13.0$	B32591C1104+***	900	1500	1500
		0.15	$5.0 \times 9.0 \times 13.0$	B32591C1154+***	900	1500	1500
		0.22	$5.0 \times 9.0 \times 13.0$	B32591C1224+***	900	1500	1500
		0.33	$5.5 \times 9.0 \times 13.0$	B32591C1334+***	680	1300	1500
		0.47	$6.0 \times 9.5 \times 13.0$	B32591C1474+***	600	1300	1000
		0.68	$7.0 \times 10.5 \times 13.0$	B32591C1684+***	500	1000	1000
		1.0	$8.0 \times 15.0 \times 13.0$	B32591C1105+***	450	900	500
250	160	0.033	$5.0 \times 9.0 \times 13.0$	B32591C3333+***	900	1500	1500
		0.047	$5.0 \times 9.0 \times 13.0$	B32591C3473+***	900	1500	1500
		0.068	$5.0 \times 9.0 \times 13.0$	B32591C3683+***	900	1500	1500
		0.10	$5.0 \times 9.0 \times 13.0$	B32591C3104+***	900	1500	1000
		0.15	$5.5 \times 10.0 \times 13.0$	B32591C3154+***	680	1300	1000
		0.22	$6.0 \times 10.5 \times 13.0$	B32591C3224+***	680	1300	1000
		0.33	$6.5 \times 11.0 \times 13.0$	B32591C3334+***	580	1100	1000
400	200	0.47	$8.0 \times 13.5 \times 13.0$	B32591C3474+***	450	900	500
		0.010	$5.0 \times 9.0 \times 13.0$	B32591C6103+***	830	1500	1500
		0.015	$5.0 \times 9.0 \times 13.0$	B32591C6153+***	830	1500	1500
		0.022	$5.0 \times 9.0 \times 13.0$	B32591C6223+***	830	1500	1500
		0.033	$5.0 \times 9.0 \times 13.0$	B32591C6333+***	830	1500	1500
		0.047	$5.0 \times 10.5 \times 13.0$	B32591C6473+***	830	1500	1000
		0.068	$5.5 \times 10.5 \times 13.0$	B32591C6683+***	830	1300	1000
630	200	0.10	$6.0 \times 11.5 \times 13.0$	B32591C6104+***	780	1300	1000
		0.010 ▽	$6.5 \times 10.5 \times 13.0$	B32591C8103+***	600	1100	500
		0.015 ▽	$6.5 \times 10.5 \times 13.0$	B32591C8153+***	600	1100	500
		0.022 ▽	$7.5 \times 11.5 \times 13.0$	B32591C8223+***	500	1000	500

▽ Wound capacitor technology

Further E series and intermediate capacitance values on request.

Composition of ordering code

+ = Capacitance tolerance code:

M = $\pm 20\%$

K = $\pm 10\%$

J = $\pm 5\%$

*** = Packaging code:

289 = Ammo pack

189 = Reel


010 = Untaped (lead length 6 – 1 mm)

011 = Untaped (lead length min. 20 mm)

008 = Untaped (straight, lead length 17 ± 3 mm)

Packaging codes for further lead configurations (untaped):

Reduced lead configuration (lead length 6 – 1 mm)	Reduced	Reduced
Lead spacing (mm) / Packaging code	5 / 035	7.5 / 030


B32592
General purpose (stacked/wound)
Ordering codes and packing units (lead spacing 15 mm)

V_R	V_{rms} $f \leq 60 \text{ Hz}$	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Ammo pack pcs./unit	Reel pcs./unit	Untaped pcs./unit
VDC	VAC	μF					
100	63	0.47	$5.0 \times 9.5 \times 18.0$	B32592C1474+***	1170	1500	1000
		0.68	$5.5 \times 10.5 \times 18.0$	B32592C1684+***	1000	1300	1000
		1.0	$6.5 \times 10.5 \times 18.0$	B32592C1105+***	830	1100	500
		1.5	$7.5 \times 14.0 \times 18.0$	B32592C1155+***	780	930	500
		2.2	$9.0 \times 14.0 \times 18.0$	B32592C1225+***	640	830	250
		3.3	$11.0 \times 17.5 \times 18.0$	B32592C1335+***	500	640	250
		4.7	$11.0 \times 17.5 \times 18.0$	B32592C1475+***	500	640	250
250	160	0.22	$5.5 \times 9.0 \times 18.0$	B32592C3224+***	1000	1300	1000
		0.33	$6.0 \times 10.0 \times 18.0$	B32592C3334+***	930	1300	500
		0.47	$7.0 \times 11.0 \times 18.0$	B32592C3474+***	780	1000	500
		0.68	$8.0 \times 11.5 \times 18.0$	B32592C3684+***	680	900	500
		1.0	$9.5 \times 13.0 \times 18.0$	B32592C3105+***	580	780	500
400	200	0.068	$5.0 \times 9.0 \times 18.0$	B32592C6683+***	1170	1500	1000
		0.10	$5.0 \times 10.0 \times 18.0$	B32592C6104+***	1170	1500	1000
		0.15	$6.0 \times 10.5 \times 18.0$	B32592C6154+***	930	1300	1000
		0.22	$7.0 \times 11.0 \times 18.0$	B32592C6224+***	780	1000	500
		0.33	$8.0 \times 12.0 \times 18.0$	B32592C6334+***	680	900	500
		0.47	$9.5 \times 13.0 \times 18.0$	B32592C6474+***	580	780	250
		0.68	$10.0 \times 16.0 \times 18.0$	B32592C6684+***	550	700	250
630	200	0.033 ▽	$6.5 \times 10.5 \times 18.0$	B32592C8333+***	830	1100	1000
		0.047 ▽	$7.0 \times 12.0 \times 18.0$	B32592C8473+***	780	1000	500
		0.068 ▽	$7.5 \times 14.0 \times 18.0$	B32592C8683+***	780	930	500
		0.10 ▽	$8.5 \times 15.0 \times 18.0$	B32592C8104+***	640	830	500

▽ Wound capacitor technology

Further E series and intermediate capacitance values on request.

Composition of ordering code

+ = Capacitance tolerance code:

 M = $\pm 20\%$

 K = $\pm 10\%$

 J = $\pm 5\%$

*** = Packaging code:

289 = Ammo pack

189 = Reel

010 = Untaped (lead length 6 – 1 mm)

011 = Untaped (lead length min. 20 mm)

 008 = Untaped (straight, lead length 17 ± 3 mm)

Packaging codes for further lead configurations (untaped):

Lead configuration (lead length 6 – 1 mm)	Reduced	Reduced	Reduced	Enlarged
Lead spacing (mm)	7.5	10	12.5	17.5
Packaging code	030	040	050	060

Ordering codes and packing units (lead spacing 22.5 mm)

V_R	V_{rms} $f \leq 60 \text{ Hz}$	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Ammo pack pcs./unit	Reel pcs./unit	Untaped pcs./unit
VDC	VAC	μF					
100	63	1.5	$7.0 \times 14.0 \times 26.5$	B32593C1155+***	500	700	500
		2.2	$8.5 \times 15.0 \times 26.5$	B32593C1225+***	450	600	500
		3.3	$10.0 \times 16.5 \times 26.5$	B32593C1335+***	380	540	200
		4.7	$11.5 \times 18.5 \times 26.5$	B32593C1475+***	300	450	200
		6.8	$13.0 \times 21.5 \times 26.5$	B32593C1685+***	280	380	200
250	160	0.68	$7.0 \times 13.0 \times 26.5$	B32593C3684+***	500	700	500
		1.0	$7.0 \times 15.5 \times 26.5$	B32593C3105+***	500	700	500
		1.5	$8.5 \times 17.0 \times 26.5$	B32593C3155+***	400	580	200
		2.2	$10.0 \times 18.5 \times 26.5$	B32593C3225+***	350	500	200
400	200	0.22	$6.5 \times 13.0 \times 26.5$	B32593C6224+***	550	800	500
		0.33	$7.0 \times 14.0 \times 26.5$	B32593C6334+***	550	800	500
		0.47	$7.0 \times 16.5 \times 26.5$	B32593C6474+***	500	700	500
630	200	0.10	$7.0 \times 14.0 \times 26.5$	B32593C8104+***	500	700	500
		0.15	$7.5 \times 16.0 \times 26.5$	B32593C8154+***	450	650	250
		0.22	$8.5 \times 17.0 \times 26.5$	B32593C8224+***	400	580	250

Further E series and intermediate capacitance values on request.

Composition of ordering code

+ = Capacitance tolerance code:

M = $\pm 20\%$

K = $\pm 10\%$

J = $\pm 5\%$

*** = Packaging code:

289 = Ammo pack

189 = Reel


010 = Untaped (lead length 6 – 1 mm)

011 = Untaped (lead length min. 20 mm)

008 = Untaped (straight, lead length 17 ± 3 mm)

Packaging codes for further lead configurations (untaped):

Lead configuration (lead length 6 – 1 mm)	Reduced	Reduced	Enlarged
Lead spacing (mm)	17.5	20	25
Packaging code	060	070	080


B32594
General purpose (wound)
Ordering codes and packing units (lead spacing 27.5 mm)

V_R	V_{rms} $f \leq 60 \text{ Hz}$	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Untaped pcs./unit
VDC	VAC	μF			
100	63	4.7	$10.5 \times 18.5 \times 31.5$	B32594C1475+***	200
		6.8	$12.5 \times 21.0 \times 31.5$	B32594C1685+***	200
		10	$17.0 \times 22.0 \times 31.5$	B32594C1106+***	200
250	160	1.5	$8.5 \times 16.0 \times 31.5$	B32594C3155+***	500
		2.2	$10.0 \times 17.5 \times 31.5$	B32594C3225+***	500
		3.3	$12.0 \times 19.5 \times 31.5$	B32594C3335+***	200
		4.7	$14.0 \times 21.5 \times 31.5$	B32594C3475+***	200
		6.8	$15.0 \times 25.0 \times 31.5$	B32594C3685+***	200
400	200	0.68	$8.0 \times 16.0 \times 31.5$	B32594C6684+***	250
		1.0	$9.5 \times 18.0 \times 31.5$	B32594C6105+***	250
		1.5	$11.5 \times 20.0 \times 31.5$	B32594C6155+***	250
		2.2	$13.5 \times 22.0 \times 31.5$	B32594C6225+***	200
630	220	0.33	$8.0 \times 15.0 \times 31.5$	B32594C8334+***	250
		0.47	$10.0 \times 16.0 \times 31.5$	B32594C8474+***	200
		0.68	$10.5 \times 18.0 \times 31.5$	B32594C8684+***	200

Further E series and intermediate capacitance values on request.

Composition of ordering code

+ = Capacitance tolerance code:

M = $\pm 20\%$

K = $\pm 10\%$

J = $\pm 5\%$

*** = Packaging code:


010 = Untaped (lead length 6 – 1 mm)

011 = Untaped (lead length min. 20 mm)

008 = Untaped (straight, lead length 17 ± 3 mm)


Packaging codes for further lead configurations (untaped):

Lead configuration (lead length 6 – 1 mm)	Reduced
Lead spacing (mm)	25
Packaging code	090



Technical data

Operating temperature range	Max. operating temperature $T_{op,max}$ +125 °C Upper category temperature T_{max} +100 °C Lower category temperature T_{min} −55 °C Rated temperature T_R +85 °C			
Dissipation factor $\tan \delta$ (in 10^{-3}) at 20 °C (upper limit values)	at	$C_R \leq 0.1 \mu F$	$0.1 \mu F < C_R \leq 1 \mu F$	$C_R > 1 \mu F$
	1 kHz	8	10	10
	10 kHz	15	20	—
	100 kHz	30	—	—
Insulation resistance R_{ins} or time constant $\tau = C_R \cdot R_{ins}$ at 20 °C, rel. humidity $\leq 65\%$ (minimum as-delivered values)	V_R	$C_R \leq 0.33 \mu F$		$C_R > 0.33 \mu F$
	100 VDC	3750 M Ω		1250 s
	≥ 250 VDC	7500 M Ω		2500 s
DC test voltage	1.4 · V_R , 2 s			
Category voltage V_C (continuous operation with V_{DC} or V_{AC} at $f \leq 60$ Hz)	T_A (°C)	DC voltage derating		AC voltage derating
	$T_A \leq 85$	$V_C = V_R$		$V_{C,rms} = V_{rms}$
	$85 < T_A \leq 100$	$V_C = V_R \cdot (165 - T_A)/80$		$V_{C,rms} = V_{rms} \cdot (165 - T_A)/80$
Operating voltage V_{op} for short operating periods (V_{DC} or V_{AC} at $f \leq 60$ Hz)	T_A (°C)	DC voltage (max. hours)		AC voltage (max. hours)
	$T_A \leq 100$	$V_{op} = 1.25 \cdot V_C$ (2000 h)		$V_{op} = 1.0 \cdot V_{C,rms}$ (2000 h)
	$100 < T_A \leq 125$	$V_{op} = 1.25 \cdot V_C$ (1000 h)		$V_{op} = 1.0 \cdot V_{C,rms}$ (1000 h)
Damp heat test	56 days/40 °C/93% relative humidity			
Limit values after damp heat test	Capacitance change $ \Delta C/C $		$\leq 5\%$	
	Dissipation factor change $\Delta \tan \delta$		$\leq 5 \cdot 10^{-3}$ (at 10 kHz)	
	Insulation resistance R_{ins}		$\geq 50\%$ of minimum	
	or time constant $\tau = C_R \cdot R_{ins}$		as-delivered values	
Reliability:				
Failure rate λ	2 fit ($\leq 2 \cdot 10^{-9}/h$) at 0.5 · V_R , 40 °C			
Service life t_{sL}	200 000 h at 1.0 · V_R , 40 °C			
	For conversion to other operating conditions and temperatures, refer to chapter "Quality assurance", page .			
Failure criteria:				
Total failure	Short circuit or open circuit			
Failure due to variation of parameters	Capacitance change $ \Delta C/C $		$> 10\%$	
	Dissipation factor $\tan \delta$		$> 2 \cdot$ upper limit value	
	Insulation resistance R_{ins}		< 150 M Ω ($C_R \leq 0.33 \mu F$)	
	or time constant $\tau = C_R \cdot R_{ins}$		< 50 s ($C_R > 0.33 \mu F$)	



B32591 ... B32594

General purpose (stacked/wound)

Pulse handling capability

"dV/dt" represents the maximum permissible voltage change per unit of time for non-sinusoidal voltages, expressed in V/ μ s.

"k₀" represents the maximum permissible pulse characteristic of the waveform applied to the capacitor, expressed in V²/ μ s.

Note:


The values of dV/dt and k₀ provided below must not be exceeded in order to avoid damaging the capacitor.

dV/dt values

Lead spacing		10 mm		15 mm		22.5 mm	27.5 mm
Technology		Stacked	Wound	Stacked	Wound	Wound	Wound
V _R	V _{rms}	dV/dt in V/ μ s					
VDC	VAC						
100	63	75	—	50	—	2.5	2
250	160	150	—	100	—	4	3
400	200	175	—	125	—	7	5
630	200	—	20	—	15	10	—
630	220	—	—	—	—	—	8


k₀ values


Lead spacing		10 mm		15 mm		22.5 mm	27.5 mm
Technology		Stacked	Wound	Stacked	Wound	Wound	Wound
V _R	V _{rms}	k ₀ in V ² / μ s					
VDC	VAC						
100	63	15 000	—	10 000	—	500	400
250	160	75 000	—	50 000	—	2 000	1 500
400	200	140 000	—	100 000	—	5 600	4 000
630	200	—	25 000	—	19 000	12 600	—
630	220	—	—	—	—	—	10 000



Impedance Z versus frequency f

(typical values)





B32591


General purpose (stacked/wound)

Permissible AC voltage V_{rms} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)


For $T_A > 55^\circ\text{C}$, please refer to "General technical information", section 3.2.3.

Lead spacing 10 mm


100 VDC/63 VAC




250 VDC/160 VAC




400 VDC/200 VAC



630 VDC/200 VAC






Permissible AC voltage V_{rms} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)


For $T_A > 55^\circ\text{C}$, please refer to "General technical information", section 3.2.3.

Lead spacing 15 mm


100 VDC/63 VAC




250 VDC/160 VAC




400 VDC/200 VAC



630 VDC/200 VAC





B32593


General purpose (wound)

Permissible AC voltage V_{rms} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)


For $T_A > 55^\circ\text{C}$, please refer to "General technical information", section 3.2.3.

Lead spacing 22.5 mm


100 VDC/63 VAC




250 VDC/160 VAC



400 VDC/200 VAC



630 VDC/200 VAC




Permissible AC voltage V_{rms} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)


For $T_A > 55^\circ\text{C}$, please refer to "General technical information", section 3.2.3.

Lead spacing 27.5 mm


100 VDC/63 VAC



250 VDC/160 VAC



400 VDC/200 VAC



630 VDC/220 VAC

