


REVISIONS		
REV	DESCRIPTION	DATE
F	REVISED PER DCR R060148	03/22/2006




- 1. TUBING VFP21 MARKED AS SHOWN IN WHITE CHARACTERS ON SURFACE INDICATED
- 2. TUBING VFP21 IS UL RECOGNIZED, IS RATED 125°C [257°F], 600 V AND MEETS VW-1 FLAME TEST.
- 3. TUBING VFP21 IS CSA CERTIFIED AND MEETS VW-1 FLAME TEST.
- 4. TUBING FP21 IS UNMARKED AND MEETS REQUIREMENTS OF AMS-DTL-23053/5-112-0
- 5. WEIGHT PER LINEAR FOOT/304.8 mm: 32.7 g/.072 lbs.
- 6. MATERIAL: BLACK POLYOLEFIN

If this document is printed it becomes uncontrolled. Check for the latest revision

4	4	30.48 m [100 ft] MINIMUM	1-603332-2
		1.22 m [4 ft] MINIMUM	603332-5
1	2 3	30.48 m [100 ft] MINIMUM	603332-2
		1.22 m [4 ft] MINIMUM	603332-1
MARKING	NOTES	LENGTH L	PART NUMBER

SPECIFICATION CONTROL DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN mm. INCH DIMENSIONS ARE IN BRACKETS. DECIMALS .XX ± .01 [.0004 in] .X ± .1 [.004 in] ANGLES .X ± 0.5 DEG	DRAWN	UNGUYEN	03/22/2006	tyco Electronics Tyco Electronics Corporation 300 Constitution Drive Menlo Park, CA, USA 94025 Raychem
	APPROVED	JBROOKS	03/22/2006	
	CAD NAME R060148			TITLE AMPSULATION, VFP21 AND FP21, 2.00 INCH ID, BLACK
	THIRD ANGLE PROJECTION 			SIZE B
				CODE IDENT. NO. 06090

DWG. NO. 603332	SHEET 1 OF 1
--------------------	--------------