



REVISIONS




P	LTR	DESCRIPTION	DATE	DWN	APVD
	AB	REV PER ECO 17-000132	5-1-17	CT	DM




- 1 CONTACTS INCLUDED IN ASSEMBLY.
- 2 MATL: STEEL, PER ASTM-A-109.
- 3 FINISH: CADIUM PER QQ-P-416.
- 4 CONTACT
BODY MATL: BERYLLIUM COPPER PER ASTM-B-197.
BODY FINISH: PLATED GOLD, .000050 MIN THK PER
MIL-G-45204 OVER NICKEL, .000050 MIN
THK PER QQ-N-290.

HOOD MATL: STAINLESS STEEL PER ASTM-A-167.
HOOD FINISH: PASSIVATED PER ASTM-A-380
- 5 FINISH: PLATED ZINC .00020 MIN THK PER ASTM-B-633.
YELLOW CHROMATE FINISH.
- 6 MATL: BRASS PER ASTM-B-36.
- 7 FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204
OVER COPPER, .000100 MIN THK PER MIL-C-14550.
- 8 CONTACT
BODY MATL: BERYLLIUM COPPER PER ASTM-B-197.
BODY AND HOOD FINISH: PLATED GOLD, .000050 MIN THK
PER MIL-G-45204 OVER COPPER, .000100 MIN THK
PER MIL-C-14550.
HOOD MATL: BRASS PER ASTM-B-36
- 9 FINISH: PLATED ZINC PER ASTM-B-633 .000200 MIN THK WITH SUPPLEMENTARY
CHROMATE (Cr3+).



			—	5-211010-1
			R10002677-0106	211010-6
			2A091-001W	211010-5
			—	211010-4
			(1J02-106)	211010-2
			—	211010-1
EYELET	SHEELS	CONTACT	CUSTOMER P/N	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. THOMPSON 19AU098 CHK J. NORTON 19AU098		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± . 1 PLC ± . 2 PLC ± . 3 PLC ± . 4 PLC ± .005[0.13] ANGLES ± ±		APVD J. NORTON 19AU098 NAME CONNECTOR SAVER, AMPLIMITE 15 POSITION, SIZE 1, SERIES 90 —	
		PRODUCT SPEC APPLICATION SPEC		SIZE CAGE CODE DRAWING NO	
MATERIAL SEE CALLOUTS		WEIGHT 0.000000		A1 00779 C-211010	
FINISH SEE CALLOUTS		CUSTOMER DRAWING		RESTRICTED TO — SCALE 4:1 SHEET 1 OF 1 REV A	