

PART NUMBER: 337LBA350M2ED



SNAP-IN/ SNAP MOUNT

Parts are RoHS compliant

Date code when parts became RoHS: 14

FEATURES

bulk filtering, high current, snap mount leads

ELECTRICAL SPECIFICATIONS

Capacitance: 330 uF

Dissipation Factor: 0.15 Max at 120 Hz and 20°C

Temperature Range: -25°C to +85°C

ESR: 753.57 milliOhms Max at 20°C and 120 Hz

Impedance: N/A

Tolerance: -20 % , +20 %

WVDC: 350 Volts DC

SVDC: 400 Volts DC

Ripple Current: 1.88 A at 120 Hz and 85°C

Impedance Ratios:

-25°C/20°C - 8

-40°C/20°C - 12

Leakage Current: .02CV or 3000uA, whichever is less
1019.57 uA after 5 Minutes

Load Life: 2000 hours at 85°C with 100 % of rated voltage and with 100 % of rated ripple current

Capacitance Change: ≤20% of initial measured value

Dissipation Factor: ≤200% of maximum specified value

Leakage Current: ≤100% of maximum specified value

Ripple Current Multipliers

Frequency Multipliers:

50 Hz	120 Hz	400 Hz	1 kHz	10 kHz	100 kHz
0.8	1	1	1.3	1.41	1.43

Temperature Multipliers:

45°C	60°C	70°C	65°C	75°C	85°C	105°C	125°C
1.8	1.6	1.2	1.4	1	1	0	0

PHYSICAL DIMENSIONS

Diameter (D): 35 mm + 1 mm

Length (L): 30 mm + 2 mm

Lead Spacing (S): 10 mm +/- 1 mm

Coating: BLACK PVC sleeving

Lead Wire Diameter (d): 1.5 mm +/- 0.5 mm

Lead Length: 6.3 mm +/- 1 mm

Lead Finish: Matte Tin

