



PRODUCTS

INDUSTRY SOLUTIONS

CAREERS

RESOURCES


CONTACT MOLEX

FIND DISTRIBUTOR

Home: Crimp Housings >

Part Number: 43914-1004

10.00mm Pitch Mini-Fit Sr.™ Receptacle Housing, Dual Row, 12 Circuits



Series image - Reference only

Status:	OBsolete
Replacement:	43914-1104
Series:	43914
Category:	Crimp Housings
Overview:	Mini-Fit Sr. Power Connectors

CHECK DISTRIBUTOR INVENTORY

[Add to My Parts](#)
[Email this page](#)
Go to [Part Detail](#) ▾**Mates With Part(s):**
[43938-1104](#)**Use With Part(s):**
[42815](#) Female Terminal and [43980](#) TPA Clip**Product Environmental Compliance**[EU ELV](#):Product not active[EU RoHS](#):Product not active[EU RoHS Phthalates](#):Product not active[China RoHS](#):[REACH SVHC](#):Product not active[Low-Halogen Status](#):Product not active

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements

EU RoHS, REACH SVHC, & Low-Halogen

Multiple Part Industry Compliance Documents

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Application Tooling**FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling[Check our list of old tooling that used to be available for this part](#)Questions on Product Environmental Compliance? Email ProductCompliance@molex.comRequest Molex's CMRT from conflictminerals@molex.com**Part Detail****COLLAPSE ALL****General**

Status	Obsolete
Category	Crimp Housings
Series	43914
Application	Power
Obsolete Date	01.06.2000
Overview	Mini-Fit Sr. Power Connectors
Product Name	Mini-Fit Sr.™
UPC	800753237841

Physical

Circuits (maximum)	12
Gender	Receptacle
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	10.00mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	50.0A
-------------------------------	-------

PRODUCTS**QUICK LINKS****RESOURCES****STAY CONNECTED**

Antennas

Company Information

Supply Chain Transparency

Application Tooling

Contact Molex

Business Continuity

Cable Assemblies

Cross-Reference

Compliance

Connected Lighting

Koch Industries

ecocare

Connectors

Industries

Feedback | Help

Copper Flex

Investor Relations

Jobs

Electrical Products

Literature

Legal | Trademarks

Industrial Automation

Molex Racing

Mobile Site

Membrane Switches

Press Room / Press Releases

Supplier Portal

Optical Solutions

Product Index

Privacy Policy

Printed Electronic Solutions

Sitemap

Tradeshows

Terms & Conditions

