

For more Information
please call

1-800-Belden1



General Description:

RG-58 type, 19 AWG solid .037" bare copper conductor, gas-injected foam HDPE insulation, Duofoil® (100% coverage) + tinned copper braid shield (90% coverage), polyethylene jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	19	Solid	BC - Bare Copper	0.9398

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FHDPE - Foam High Density Polyethylene	2.794

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	90

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PE - Polyethylene

Overall Cable

Overall Nominal Diameter: 4.953 mm

Mechanical Characteristics (Overall)

Operating Temperature Range:	-40°C To +80°C
Non-UL Temperature Rating:	80°C
Bulk Cable Weight:	34.229 Kg/Km
Max. Recommended Pulling Tension:	177.928 N
Min. Bend Radius/Minor Axis:	50.800 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	No
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

RG Type:	58/U
----------	------

Series Type:	RF 195
--------------	--------

Suitability**Plenum/Non-Plenum**

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)

50

Nom. Inductance:

Inductance (µH/m)

0.209984

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

79.7283

Nominal Velocity of Propagation:

VP (%)

77

Nominal Delay:

Delay (ns/m)

4.331

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

24.9356

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

13.7802

Maximum VSWR:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Max. VSWR
		5	6000	1.25:1

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
5.000	2.461
10.000	3.281
30.000	6.562
50.000	8.203
150.000	13.124
220.000	16.077
450.000	23.295
900.000	33.794
1500.000	44.950
1800.000	49.871
2000.000	52.824
2500.000	60.042
3000.000	67.261
4500.000	86.947
5800.000	102.367
6000.000	104.992

Max. Power Rating:

Freq. (MHz)	Rating (W)
30	890
50	694
150	403
220	336
450	231
900	162
1500	124
1800	113
2000	107
2500	95
3000	87
3500	80
4500	70
5800	62
6000	61

Max. Operating Voltage - Non-UL:

Voltage
300 V RMS

Sweep Test

Sweep Testing: 100% Sweep tested to 6 GHz

Notes (Overall)

Notes: Belden® The Wire in Wireless®

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7806A 0101000	305 MT	11.340 KG	BLACK	C	RF195 WIRELESS 50 OHM COAX PE
7806A 010500	152 MT	6.577 KG	BLACK	C	RF195 WIRELESS 50 OHM COAX PE

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 6 Revision Date: 07-19-2013

© 2013 Belden, Inc
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.