

RBV5000 - RBV5010

PRV : 50 - 1000 Volts

Io : 50 Amperes

FEATURES :


- * High current capability
- * High surge current capability
- * High reliability
- * Low reverse current
- * Low forward voltage drop
- * High case dielectric strength of 2000 V_{DC}
- * Ideal for printed circuit board
- * Very good heat dissipation

MECHANICAL DATA :

- * Case : Reliable low cost construction utilizing molded plastic technique
- * Epoxy : UL94V-O rate flame retardant
- * Terminals : Plated lead solderable per MIL-STD-202, Method 208 guaranteed
- * Polarity : Polarity symbols marked on case
- * Mounting position : Any
- * Weight : 7.7 grams

SILICON BRIDGE RECTIFIERS

RBV25



Dimensions in millimeters

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating at 25 °C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

RATING	SYMBOL	RBV 5000	RBV 5001	RBV 5002	RBV 5004	RBV 5006	RBV 5008	RBV 5010	UNIT
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	Volts
Maximum RMS Voltage	V _{RMS}	35	70	140	280	420	560	700	Volts
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	Volts
Maximum Average Forward Current T _c = 55°C	I _{F(AV)}	50							Amps.
Peak Forward Surge Current Single half sine wave Superimposed on rated load (JEDEC Method)	I _{FSM}	400							Amps.
Current Squared Time at t < 8.3 ms.	i ² t	660							A ² S
Maximum Forward Voltage per Diode at I _F = 25 Amps.	V _F	1.1							Volts
Maximum DC Reverse Current Ta = 25 °C	I _R	10							μA
at Rated DC Blocking Voltage Ta = 100 °C	I _{R(H)}	200							μA
Typical Thermal Resistance (Note 1)	R _{θJC}	1.5							°C/W
Operating Junction Temperature Range	T _J	10							°C
Storage Temperature Range	T _{STG}	- 40 to + 150							°C

Notes :

1. Thermal Resistance from junction to case with units mounted on heatsink.

UPDATE : AUGUST 3, 1998

RATING AND CHARACTERISTIC CURVES (RBV5000 - RBV5010)

FIG.1 - DERATING CURVE FOR OUTPUT RECTIFIED CURRENT




FIG.2 - MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG.3 - TYPICAL FORWARD CHARACTERISTICS PER DIODE




FIG.4 - TYPICAL REVERSE CHARACTERISTICS PER DIODE

