

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0465621264](#)
Status: **Active**
Overview: [EXTreme Ten60Power High-Current Connector](#)
Description: 2.00mm, 5.50mm Pitch EXTreme Ten60Power Vertical Receptacle Assembly with Guide Receivers, 10 Signal Circuits, 3 Power Circuits

Documents:

Drawing (PDF)	Test Summary 464361000-TS-000 (PDF)
Product Specification PS-46436-100-001 (PDF)	Datasheet (PDF)
Application Specification AS-46436-100-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-46562-001-000 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

Application tooling part link


Application Tooling Part Link	62100-7900
-------------------------------	------------

General

Product Family	PCB Receptacles
Series	46562
Application	Board-to-Board, Power, Signal
Comments	See PS-46436-100 for details
Overview	EXTreme Ten60Power High-Current Connector
Product Name	EXTreme Ten60Power
UPC	884982714878

Physical

(p)ower-(s)ignal Configuration	3p - 10s
Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black
Durability (mating cycles max)	200
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	10.934/g
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.58mm
Packaging Type	Tray
Pitch - Mating Interface	2.00mm, 5.50mm
Plating min - Mating	0.127µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[46562](#) Series

Mates With

[464371264](#) EXTreme Ten60Power Right
Angle Plug Assembly

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description

Product #

Removal Tool
for Ten60 Power
Receptacle
Terminals

[621007900](#)

Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	2.5A, 55.0A
Grounding to PCB	No
Voltage - Maximum	600V AC / 250V DC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-46436-100-001
Packaging Specification	PK-46562-001-000
Product Specification	PS-46436-100-001
Sales Drawing	SD-46562-1264
Test Summary	464361000-TS-000

This document was generated on 08/21/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION