

5N Detector Switches

Japan

Type: **ESE11**

Standard type with a wide range of customizable features


■ Features

- Attachable type, wide range of customizable features including operational directions
- Light operating force
- Wide available range for reflow soldering

■ Recommended Applications

- Mechanism and detection for Car audio equipment

■ Explanation of Part Numbers



■ Specifications

Rating	50 μ A 3 Vdc to 10 mA 5 Vdc (Resistive load)
Contact Resistance	500 m Ω max.
Insulation Resistance	100 M Ω max. (100 Vdc)
Dielectric Withstanding Voltage	100 Vac for 1 minute
Operating Force	350 mN max. (Full Travel)
Mounting Height	· Type SV 4.9 mm · Type MV 4.9 mm (MV2, 7 : 5.4 mm) · Type SH 5.25 mm · Type MH 4.25 mm · Type HS, SF 3.6 mm
Poles and Throws	1-pole 1-throw
Full Travel (Pushing distance)	· Type SV 6.1 mm (2.4 mm) · Type MV 6.1 mm (2.4 mm) · Type SH 3.0 mm (2.4 mm) · Type MH 1.7 mm (2.4 mm) · Type HS, SF 6.3 mm (2.4 mm)
Operating Life	50000 cycles min.
Temperature Range	-10 °C to +70 °C
Heat Resistance	+80 °C for 96 hours
Low Temperature Resistance	-25 °C for 96 hours
Humidity Resistance	+40 °C 90 % to 95 % RH for 96 hours

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

Minimum Quantity/Packing Unit	ESE11SV□ ESE11MV□ ESE11SH□ ESE11MH□ ESE11HS□ ESE11SF□	200 pcs. Polyethylene Bag (Bulk)
	ESE11MV□T	800 pcs. Embossed Taping (Reel Pack)
	ESE11MH□T	1500 pcs. Embossed Taping (Reel Pack)
Quantity/ Carton	ESE11SV□ ESE11MV□ ESE11SH□ ESE11MH□ ESE11HS□ ESE11SF□	10000 pcs. Polyethylene Bag (Bulk)
	ESE11MV□T	4800 pcs. Embossed Taping (Reel Pack)
	ESE11MH□T	9000 pcs. Embossed Taping (Reel Pack)

■ Dimensions in mm (not to scale)

	No. 1	ESE11SV1 For wave soldering 1-pole 1-throw	No. 2	ESE11MV1 For reflow soldering 1-pole 1-throw
	Gold plating ESE11SV7		Gold plating ESE11MV5	
Vertical Type	Top view dimensions: 5.2, 6.4, 2.2, 3.0, 6.4, 5.2, 2.45, 1.0, 0.8, 1.27, 1.0, 4.9, 8.5, 1.0, (2.7), 2.3, 1.0, 0.95, 2.3, 0.95, 3.3, 2.3, 0.95, 2.45. Side view dimensions: 1.27, 6.1, 7.75, 0.1, (3.3), 1.2, 0.1. Lever view dimensions: 4-φ1.10 +0.05/-0.05, φ1.25 +0.05/-0.05, 3.3, 2.3, 0.95, 2.45. Labels: Lever center, Recommended PWB piercing plan View from (A), Full travel ON starting position.		Top view dimensions: 1.51.75, 1.0, 2.2, 3.0, 5.2, 6.4, 1.65, 1.0, 1.65±0.1, 1.75, 1.0, 1.85, 1.4, 1.4, 2.0±0.2, 1.4, 3.25, 3.35. Side view dimensions: 1.27, 6.1, 7.75, 0.8, 1.2, 0.1. Lever view dimensions: 2-φ1.3 Hole, 1.4, 3.25, 3.35. Labels: Full travel ON starting position, Recommended land pattern View from (A).	

■ Dimensions in mm (not to scale)

Vertical Type	No. 3 ESE11MV9 For reflow soldering 1-pole 1-throw Recommended land pattern View from (A)	No. 4 ESE11MV2 For reflow soldering 1-pole 1-throw Recommended land pattern View from (A)
	No. 5 ESE11MV7 For reflow soldering 1-pole 1-throw Recommended land pattern View from (A)	No. 6 ESE11SH1C For wave soldering 1-pole 1-throw Gold plating ESE11SH5 Recommended PWB piercing plan View from (A)




■ Dimensions in mm (not to scale)

Horizontal Type	No. 7 ESE11SH2C For wave soldering 1-pole 1-throw Gold plating ESE11SH6 Full travel ON starting position Recommended PWB piercing plan View from (A)	No. 8 ESE11MH1 For reflow soldering 1-pole 1-throw Gold plating ESE11MH3 Recommended land pattern View from (A) Full travel ON starting position
	No. 9 ESE11MH2 For reflow soldering 1-pole 1-throw Gold plating ESE11MH4 Recommended land pattern View from (A) Full travel ON starting position	No. 10 ESE11MH5 For reflow soldering 1-pole 1-throw Recommended land pattern View from (A) Full travel ON starting position

Horizontal Type

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Circuit Diagram

MH, SH Type	MV, SV Type	SF, HS Type
1-pole 1-throw (N.O)	1-pole 1-throw (N.O)	1-pole 1-throw (N.O)
		

■ Packaging Specifications

Standard Reel Dimensions in mm (not to scale)

