

OBSOLETE

SPECIFICATIONS:

MATERIAL:-

MOULDING: PBT UL94V-0

ELECTRICAL:-

CURRENT RATING: 1A AC/DC MAX.

WORKING VOLTAGE: 100V AC/DC

WITHSTANDING VOLTAGE: 500V AC/MINUTE

CONTACT RESISTANCE: 20 mΩ MAX.

INSULATION RESISTANCE: 100 MΩ MIN.

ENVIRONMENTAL:-

TEMPERATURE RANGE: -25°C TO +85°C

OTHERS:-


ACCEPTS: M30-3000046 CRIMP TERMINAL

MATES WITH: WAFER M30-301 XX 46R

M30-401 XX 46R

M30-310 XX 46

M30-410 XX 46



NO. OF WAYS	PART NO.	DIM	
		A	B
2	M30-1300200R	1.25	4.25
3	M30-1300300R	2.50	5.50
4	M30-1300400R	3.75	6.75
5	M30-1300500R	5.00	8.00
6	M30-1300600R	6.25	9.25
7	M30-1300700R	7.50	10.50
8	M30-1300800R	8.75	11.75
9	M30-1300900R	10.00	13.00
10	M30-1301000R	11.25	14.25
11	M30-1301100R	12.50	15.50
12	M30-1301200R	13.75	16.75
13	M30-1301300R	15.00	18.00
14	M30-1301400R	16.25	19.25
15	M30-1301500R	17.50	20.50

NOTES: ALL DIMENSIONS AND NOTES
MARKED * ARE CRITICAL AND
MUST BE CHECKED IN ACCORDANCE
WITH QUALITY DOC. QI-02A

Allan	3	27.06.08	A139
Allan	2	20.02.08	A112
HTUT	1	14.02.07	-

NAME	ISS.	DATE	C/NOTE
------	------	------	--------

APPROVED: *Pan*CHECKED: *Pan*

DRAWN: Allan

ORDER CODE M30-130 XX 00 NO. OF WAYS 	CUSTOMER REF.:
	ASSEMBLY DRG:

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.15mm
X.XXX = ±0.08mm

ANGLES = ±5°
UNLESS STATED

MATERIAL:

SEE NOTES

FINISH: SEE NOTES

S/AREA: mm²

TITLE:

1.25MM PITCH SINGLE ROW
HOUSING

DRAWING NUMBER:

M30-130 XX 00

SHT
1
OF 1