

NOTES :

1- MATERIAL : POLYESTER FIBER GLASS FILED 94-V-0
COLOR BLACK .

TERMINAL : PHOSPHOR BRONZE .


PLATINGS : FINISH 2

POST PLATE (0.00127-0.00152)/.000050-.000060

GOLD IN CONTACT AREA .

(0.00190)/.000075 MIN. PURE TIN IN TAIL AREA BOTH

OVER (0.00127)/.000050 MIN. NICKEL OVERALL .



2- PC BOARD THICKNESS : (1.57) / .062 .

3- JACK FOR MATING WITH F.C.C. 68 PLUGS 90075 MOLEX SERIES .





4- PRODUCT SPECIFICATION PS-95009.

5- APPLICATION SPECIFICATION AS-95001.

6- PACKAGING SPECIFICATION PK-95029.

MOUNTING HOLE PATTERNS

(SEE FROM COMPONENT SIDE)



ENTER DESCRIPTION EC NO: MG2005-0155 DRAWN: CSEBASTI 2004/11/12 CHKD: FCARABET 2004/11/15 APPR: KNOLLER 2004/11/15		DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION ⊙ □	
				mm	INCH	DRAWN BY DP	DATE 86/10/23	TITLE FLUSH MOUNT RIGHT ANGLE MODULAR JACK ASSEMBLY THROUGH HOLE VERSION			
		4 PLACES	± ---	± ---	CHECKED BY	DATE	MOLEX INCORPORATED				
		3 PLACES	± ---	± .010							SHEET NO. 1 OF 4
		2 PLACES	± 0.25	± .014			SDA-95009-F				
		1 PLACE	± 0.35	± ---							THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
		ANGULAR ±1/2°				SIZE A 3					
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									

