

## Features

- Low-Voltage and Standard-Voltage Operation
  - 5.0 ( $V_{CC} = 4.5V$  to  $5.5V$ )
  - 2.7 ( $V_{CC} = 2.7V$  to  $5.5V$ )
  - 2.5 ( $V_{CC} = 2.5V$  to  $5.5V$ )
  - 1.8 ( $V_{CC} = 1.8V$  to  $5.5V$ )
- Internally Organized 128 x 8 (1K), 256 x 8 (2K), 512 x 8 (4K), 1024 x 8 (8K) or 2048 x 8 (16K)
- 2-Wire Serial Interface
- Schmitt Trigger, Filtered Inputs for Noise Suppression
- Bidirectional Data Transfer Protocol
- 100 kHz (1.8V, 2.5V, 2.7V) and 400 kHz (5V) Compatibility
- Write Protect Pin for Hardware Data Protection
- 8-Byte Page (1K, 2K), 16-Byte Page (4K, 8K, 16K) Write Modes
- Partial Page Writes Are Allowed
- Self-Timed Write Cycle (10 ms max)
- High Reliability
  - Endurance: 1 Million Write Cycles
  - Data Retention: 100 Years
  - ESD Protection: >3000V
- Automotive Grade and Extended Temperature Devices Available
- 8-Pin and 14-Pin JEDEC SOIC, 8-Pin PDIP, 8-Pin MSOP, and 8-Pin TSSOP Packages


## Description

The AT24C01A/02/04/08/16 provides 1024/2048/4096/8192/16384 bits of serial electrically erasable and programmable read only memory (EEPROM) organized as 128/256/512/1024/2048 words of 8 bits each. The device is optimized for use in many industrial and commercial applications where low power and low voltage operation are essential. The AT24C01A/02/04/08/16 is available in space saving 8-pin PDIP, (AT24C01A/02/04/08/16), 8-Pin MSOP (AT24001A/02), 8-Pin TSSOP (AT24C01A/02/04/08/16), and 8-Pin and 14-Pin JEDEC SOIC (AT24C01A/02/04/08/16) packages and is accessed via a 2-wire serial interface. In addition, the entire family is available in 5.0V (4.5V to 5.5V), 2.7V (2.7V to 5.5V), 2.5V (2.5V to 5.5V) and 1.8V (1.8V to 5.5V) versions.


## Pin Configurations

| Pin Name | Function           |
|----------|--------------------|
| A0 to A2 | Address Inputs     |
| SDA      | Serial Data        |
| SCL      | Serial Clock Input |
| WP       | Write Protect      |
| NC       | No Connect         |


14-Pin SOIC




8-Pin PDIP




8-Pin TSSOP



8-Pin MSOP



8-Pin SOIC



## 2-Wire Serial EEPROM

1K (128 x 8)

2K (256 x 8)

4K (512 x 8)

8K (1024 x 8)

16K (2048 x 8)

**AT24C01A**

**AT24C02**

**AT24C04**

**AT24C08**

**AT24C16**





| WP Pin Status      | Part of the Array Protected  |                 |                 |                             |                       |
|--------------------|------------------------------|-----------------|-----------------|-----------------------------|-----------------------|
|                    | 24C01A                       | 24C02           | 24C04           | 24C08                       | 24C16                 |
| At V <sub>CC</sub> | Full (1K) Array              | Full (2K) Array | Full (4K) Array | Normal Read/Write Operation | Upper Half (8K) Array |
| At GND             | Normal Read/Write Operations |                 |                 |                             |                       |

## Memory Organization

**AT24C01A, 1K SERIAL EEPROM:** Internally organized with 128 pages of 1-byte each, the 1K requires a 7-bit data word address for random word addressing.

**AT24C02, 2K SERIAL EEPROM:** Internally organized with 256 pages of 1-byte each, the 2K requires an 8-bit data word address for random word addressing.

**AT24C04, 4K SERIAL EEPROM:** The 4K is internally organized with 256 pages of 2 bytes each. Random word addressing AT24C01A/02/04/08/16 requires a 9-bit data word address.

**AT24C08, 8K SERIAL EEPROM:** The 8K is internally organized with 4 blocks of 256 pages of 4 bytes each. Random word addressing requires a 10-bit data word address.

**AT24C16, 16K SERIAL EEPROM:** The 16K is internally organized with 8 blocks of 256 pages of 8 bytes each. Random word addressing requires an 11-bit data word address.

## Pin Capacitance<sup>(1)</sup>

Applicable over recommended operating range from T<sub>A</sub> = 25°C, f = 1.0 MHz, V<sub>CC</sub> = +1.8V.

| Symbol           | Test Condition                                                             | Max | Units | Conditions            |
|------------------|----------------------------------------------------------------------------|-----|-------|-----------------------|
| C <sub>I/O</sub> | Input/Output Capacitance (SDA)                                             | 8   | pF    | V <sub>I/O</sub> = 0V |
| C <sub>IN</sub>  | Input Capacitance (A <sub>0</sub> , A <sub>1</sub> , A <sub>2</sub> , SCL) | 6   | pF    | V <sub>IN</sub> = 0V  |

Note: 1. This parameter is characterized and is not 100% tested.

## DC Characteristics

Applicable over recommended operating range from: T<sub>A</sub> = -40°C to +85°C, V<sub>CC</sub> = +1.8V to +5.5V, T<sub>AC</sub> = 0°C to +70°C, V<sub>CC</sub> = +1.8V to +5.5V (unless otherwise noted).

| Symbol           | Parameter                               | Test Condition                                        | Min                   | Typ  | Max                   | Units |
|------------------|-----------------------------------------|-------------------------------------------------------|-----------------------|------|-----------------------|-------|
| V <sub>CC1</sub> | Supply Voltage                          |                                                       | 1.8                   |      | 5.5                   | V     |
| V <sub>CC2</sub> | Supply Voltage                          |                                                       | 2.5                   |      | 5.5                   | V     |
| V <sub>CC3</sub> | Supply Voltage                          |                                                       | 2.7                   |      | 5.5                   | V     |
| V <sub>CC4</sub> | Supply Voltage                          |                                                       | 4.5                   |      | 5.5                   | V     |
| I <sub>CC</sub>  | Supply Current V <sub>CC</sub> = 5.0V   | READ at 100 kHz                                       |                       | 0.4  | 1.0                   | mA    |
| I <sub>CC</sub>  | Supply Current V <sub>CC</sub> = 5.0V   | WRITE at 100 kHz                                      |                       | 2.0  | 3.0                   | mA    |
| I <sub>SB1</sub> | Standby Current V <sub>CC</sub> = 1.8V  | V <sub>IN</sub> = V <sub>CC</sub> or V <sub>SS</sub>  |                       | 0.6  | 3.0                   | μA    |
| I <sub>SB2</sub> | Standby Current V <sub>CC</sub> = 2.5V  | V <sub>IN</sub> = V <sub>CC</sub> or V <sub>SS</sub>  |                       | 1.4  | 4.0                   | μA    |
| I <sub>SB3</sub> | Standby Current V <sub>CC</sub> = 2.7V  | V <sub>IN</sub> = V <sub>CC</sub> or V <sub>SS</sub>  |                       | 1.6  | 4.0                   | μA    |
| I <sub>SB4</sub> | Standby Current V <sub>CC</sub> = 5.0V  | V <sub>IN</sub> = V <sub>CC</sub> or V <sub>SS</sub>  |                       | 8.0  | 18.0                  | μA    |
| I <sub>LI</sub>  | Input Leakage Current                   | V <sub>IN</sub> = V <sub>CC</sub> or V <sub>SS</sub>  |                       | 0.10 | 3.0                   | μA    |
| I <sub>LO</sub>  | Output Leakage Current                  | V <sub>OUT</sub> = V <sub>CC</sub> or V <sub>SS</sub> |                       | 0.05 | 3.0                   | μA    |
| V <sub>IL</sub>  | Input Low Level <sup>(1)</sup>          |                                                       | -0.6                  |      | V <sub>CC</sub> × 0.3 | V     |
| V <sub>IH</sub>  | Input High Level <sup>(1)</sup>         |                                                       | V <sub>CC</sub> × 0.7 |      | V <sub>CC</sub> + 0.5 | V     |
| V <sub>OL2</sub> | Output Low Level V <sub>CC</sub> = 3.0V | I <sub>OL</sub> = 2.1 mA                              |                       |      | 0.4                   | V     |
| V <sub>OL1</sub> | Output Low Level V <sub>CC</sub> = 1.8V | I <sub>OL</sub> = 0.15 mA                             |                       |      | 0.2                   | V     |

Note: 1. V<sub>IL</sub> min and V<sub>IH</sub> max are reference only and are not tested.

## AC Characteristics

Applicable over recommended operating range from  $T_A = -40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ ,  $V_{CC} = +1.8\text{V}$  to  $+5.5\text{V}$ ,  $CL = 1$  TTL Gate and 100pF (unless otherwise noted).

| Symbol                   | Parameter                                                                    | 2.7-, 2.5-, 1.8-volt |     | 5.0-volt |     | Units         |
|--------------------------|------------------------------------------------------------------------------|----------------------|-----|----------|-----|---------------|
|                          |                                                                              | Min                  | Max | Min      | Max |               |
| $f_{SCL}$                | Clock Frequency, SCL                                                         |                      | 100 |          | 400 | kHz           |
| $t_{LOW}$                | Clock Pulse Width Low                                                        | 4.7                  |     | 1.2      |     | $\mu\text{s}$ |
| $t_{HIGH}$               | Clock Pulse Width High                                                       | 4.0                  |     | 0.6      |     | $\mu\text{s}$ |
| $t_I$                    | Noise Suppression Time <sup>(1)</sup>                                        |                      | 100 |          | 50  | ns            |
| $t_{AA}$                 | Clock Low to Data Out Valid                                                  | 0.1                  | 4.5 | 0.1      | 0.9 | $\mu\text{s}$ |
| $t_{BUF}$                | Time the bus must be free before a new transmission can start <sup>(1)</sup> | 4.7                  |     | 1.2      |     | $\mu\text{s}$ |
| $t_{HD,STA}$             | Start Hold Time                                                              | 4.0                  |     | 0.6      |     | $\mu\text{s}$ |
| $t_{SU,STA}$             | Start Set-up Time                                                            | 4.7                  |     | 0.6      |     | $\mu\text{s}$ |
| $t_{HD,DAT}$             | Data In Hold Time                                                            | 0                    |     | 0        |     | $\mu\text{s}$ |
| $t_{SU,DAT}$             | Data In Set-up Time                                                          | 200                  |     | 100      |     | ns            |
| $t_R$                    | Inputs Rise Time <sup>(1)</sup>                                              |                      | 1.0 |          | 0.3 | $\mu\text{s}$ |
| $t_F$                    | Inputs Fall Time <sup>(1)</sup>                                              |                      | 300 |          | 300 | ns            |
| $t_{SU,STO}$             | Stop Set-up Time                                                             | 4.7                  |     | 0.6      |     | $\mu\text{s}$ |
| $t_{DH}$                 | Data Out Hold Time                                                           | 100                  |     | 50       |     | ns            |
| $t_{WR}$                 | Write Cycle Time                                                             |                      | 10  |          | 10  | ms            |
| Endurance <sup>(1)</sup> | 5.0V, 25°C, Page Mode                                                        | 1M                   |     | 1M       |     | Write Cycles  |

Note: 1. This parameter is characterized and is not 100% tested.

## Device Operation

**CLOCK and DATA TRANSITIONS:** The SDA pin is normally pulled high with an external device. Data on the SDA pin may change only during SCL low time periods (refer to Data Validity timing diagram). Data changes during SCL high periods will indicate a start or stop condition as defined below.

**START CONDITION:** A high-to-low transition of SDA with SCL high is a start condition which must precede any other command (refer to Start and Stop Definition timing diagram).

**STOP CONDITION:** A low-to-high transition of SDA with SCL high is a stop condition. After a read sequence, the stop command will place the EEPROM in a standby power mode (refer to Start and Stop Definition timing diagram).

**ACKNOWLEDGE:** All addresses and data words are serially transmitted to and from the EEPROM in 8-bit words. The EEPROM sends a zero to acknowledge that it has received each word. This happens during the ninth clock cycle.


**STANDBY MODE:** The AT24C01A/02/04/08/16 features a low power standby mode which is enabled: (a) upon power-up and (b) after the receipt of the STOP bit and the completion of any internal operations.

**MEMORY RESET:** After an interruption in protocol, power loss or system reset, any 2-wire part can be reset by following these steps:

1. Clock up to 9 cycles.
2. Look for SDA high in each cycle while SCL is high.
3. Create a start condition as SDA is high.


## Bus Timing

SCL: Serial Clock, SDA: Serial Data I/O




## Write Cycle Timing

SCL: Serial Clock, SDA: Serial Data I/O




Note: 1. The write cycle time  $t_{WR}$  is the time from a valid stop condition of a write sequence to the end of the internal clear/write cycle.


## Data Validity



## Start and Stop Definition



## Output Acknowledge



## Device Addressing

The 1K, 2K, 4K, 8K and 16K EEPROM devices all require an 8-bit device address word following a start condition to enable the chip for a read or write operation (refer to Figure 1).

The device address word consists of a mandatory one, zero sequence for the first four most significant bits as shown. This is common to all the EEPROM devices.

The next 3 bits are the A2, A1 and A0 device address bits for the 1K/2K EEPROM. These 3 bits must compare to their corresponding hard-wired input pins.

The 4K EEPROM only uses the A2 and A1 device address bits with the third bit being a memory page address bit. The two device address bits must compare to their corresponding hard-wired input pins. The A0 pin is no connect.

The 8K EEPROM only uses the A2 device address bit with the next 2 bits being for memory page addressing. The A2 bit must compare to its corresponding hard-wired input pin. The A1 and A0 pins are no connect.

The 16K does not use any device address bits but instead the 3 bits are used for memory page addressing. These page addressing bits on the 4K, 8K, and 16K devices should be considered the most significant bits of the data word address which follows. The A0, A1 and A2 pins are no connect.

The eighth bit of the device address is the read/write operation select bit. A read operation is initiated if this bit is high and a write operation is initiated if this bit is low.

Upon a compare of the device address, the EEPROM will output a zero. If a compare is not made, the chip will return to a standby state.

## Write Operations

**BYTE WRITE:** A write operation requires an 8-bit data word address following the device address word and acknowledgment. Upon receipt of this address, the EEPROM will again respond with a zero and then clock in the first 8-bit data word. Following receipt of the 8-bit data word, the EEPROM will output a zero and the addressing device, such as a microcontroller, must terminate the write sequence with a stop condition. At this time the EEPROM enters an internally-timed write cycle,  $t_{WR}$ , to the nonvolatile memory. All inputs are disabled during this write cycle and the EEPROM will not respond until the write is complete (refer to Figure 2).

**PAGE WRITE:** The 1K/2K EEPROM is capable of an 8-byte page write, and the 4K, 8K and 16K devices are capable of 16-byte page writes.

A page write is initiated the same as a byte write, but the microcontroller does not send a stop condition after the first data word is clocked in. Instead, after the EEPROM

acknowledges receipt of the first data word, the microcontroller can transmit up to seven (1K/2K) or fifteen (4K, 8K, 16K) more data words. The EEPROM will respond with a zero after each data word received. The microcontroller must terminate the page write sequence with a stop condition (refer to Figure 3).

The data word address lower three (1K/2K) or four (4K, 8K, 16K) bits are internally incremented following the receipt of each data word. The higher data word address bits are not incremented, retaining the memory page row location. When the word address, internally generated, reaches the page boundary, the following byte is placed at the beginning of the same page. If more than eight (1K/2K) or sixteen (4K, 8K, 16K) data words are transmitted to the EEPROM, the data word address will "roll over" and previous data will be overwritten.

**ACKNOWLEDGE POLLING:** Once the internally-timed write cycle has started and the EEPROM inputs are disabled, acknowledge polling can be initiated. This involves sending a start condition followed by the device address word. The read/write bit is representative of the operation desired. Only if the internal write cycle has completed will the EEPROM respond with a zero allowing the read or write sequence to continue.

## Read Operations

Read operations are initiated the same way as write operations with the exception that the read/write select bit in the device address word is set to one. There are three read operations: current address read, random address read and sequential read.

**CURRENT ADDRESS READ:** The internal data word address counter maintains the last address accessed during the last read or write operation, incremented by one. This address stays valid between operations as long as the chip power is maintained. The address "roll over" during read is from the last byte of the last memory page to the first byte of the first page. The address "roll over" during write is from the last byte of the current page to the first byte of the same page.

Once the device address with the read/write select bit set to one is clocked in and acknowledged by the EEPROM, the current address data word is serially clocked out. The microcontroller does not respond with an input zero but does generate a following stop condition (refer to Figure 4).


**RANDOM READ:** A random read requires a "dummy" byte write sequence to load in the data word address. Once the device address word and data word address are clocked in and acknowledged by the EEPROM, the microcontroller must generate another start condition. The microcontroller now initiates a current address read by sending a device address with the read/write select bit high. The EEPROM acknowledges the device address and serially clocks out

the data word. The microcontroller does not respond with a zero but does generate a following stop condition (refer to Figure 5).


**SEQUENTIAL READ:** Sequential reads are initiated by either a current address read or a random address read. After the microcontroller receives a data word, it responds with an acknowledge. As long as the EEPROM receives an

acknowledge, it will continue to increment the data word address and serially clock out sequential data words. When the memory address limit is reached, the data word address will “roll over” and the sequential read will continue. The sequential read operation is terminated when the microcontroller does not respond with a zero but does generate a following stop condition (refer to Figure 6).


**Figure 1. Device Address**



**Figure 2. Byte Write**



**Figure 3. Page Write**



(\* = DON'T CARE bit for 1K)

**Figure 4. Current Address Read**




Figure 5. Random Read





Figure 6. Sequential Read





## AT24C01A Ordering Information

| $t_{WR}$ (max)<br>(ms) | $I_{CC}$ (max)<br>( $\mu A$ ) | $I_{SB}$ (max)<br>( $\mu A$ ) | $f_{MAX}$<br>(kHz) | Ordering Code                                                                    | Package                | Operation Range               |
|------------------------|-------------------------------|-------------------------------|--------------------|----------------------------------------------------------------------------------|------------------------|-------------------------------|
| 10                     | 3000                          | 18                            | 400                | AT24C01A-10PC<br>AT24C01A-10SC<br>AT24C01A-10MC<br>AT24C01A-10TC                 | 8P3<br>8S1<br>8M<br>8T | Commercial<br>(0°C to 70°C)   |
|                        | 3000                          | 18                            | 400                | AT24C01A-10PI<br>AT24C01A-10SI<br>AT24C01A-10MI<br>AT24C01A-10TI                 | 8P3<br>8S1<br>8M<br>8T | Industrial<br>(-40°C to 85°C) |
| 10                     | 1500                          | 4                             | 100                | AT24C01A-10PC-2.7<br>AT24C01A-10SC-2.7<br>AT24C01A-10MC-2.7<br>AT24C01A-10TC-2.7 | 8P3<br>8S1<br>8M<br>8T | Commercial<br>(0°C to 70°C)   |
|                        | 1500                          | 4                             | 100                | AT24C01A-10PI-2.7<br>AT24C01A-10SI-2.7<br>AT24C01A-10MI-2.7<br>AT24C01A-10TI-2.7 | 8P3<br>8S1<br>8M<br>8T | Industrial<br>(-40°C to 85°C) |

| Package Type |                                                                   |
|--------------|-------------------------------------------------------------------|
| <b>8M</b>    | 8-Lead, 0.118" Wide, Miniature Small Outline Package (MSOP)       |
| <b>8P3</b>   | 8-Lead, 0.300" Wide, Plastic Dual Inline Package (PDIP)           |
| <b>8S1</b>   | 8-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (JEDEC SOIC) |
| <b>8T</b>    | 8-Lead, 0.170" Wide, Thin Shrink Small Outline Package (TSSOP)    |
| <b>14S</b>   | 14-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (SOIC)      |
| Options      |                                                                   |
| <b>Blank</b> | Standard Operation (4.5V to 5.5V)                                 |
| <b>-2.7</b>  | Low Voltage (2.7V to 5.5V)                                        |
| <b>-2.5</b>  | Low Voltage (2.5V to 5.5V)                                        |
| <b>-1.8</b>  | Low Voltage (1.8V to 5.5V)                                        |

## AT24C01A Ordering Information (Continued)

| $t_{WR}$ (max)<br>(ms) | $I_{CC}$ (max)<br>( $\mu A$ ) | $I_{SB}$ (max)<br>( $\mu A$ ) | $f_{MAX}$<br>(kHz) | Ordering Code                                                                    | Package                | Operation Range               |
|------------------------|-------------------------------|-------------------------------|--------------------|----------------------------------------------------------------------------------|------------------------|-------------------------------|
| 10                     | 1000                          | 4                             | 100                | AT24C01A-10PC-2.5<br>AT24C01A-10SC-2.5<br>AT24C01A-10MC-2.5<br>AT24C01A-10TC-2.5 | 8P3<br>8S1<br>8M<br>8T | Commercial<br>(0°C to 70°C)   |
|                        | 1000                          | 4                             | 100                | AT24C01A-10PI-2.5<br>AT24C01A-10SI-2.5<br>AT24C01A-10MI-2.5<br>AT24C01A-10TI-2.5 | 8P3<br>8S1<br>8M<br>8T | Industrial<br>(-40°C to 85°C) |
| 10                     | 800                           | 3                             | 100                | AT24C01A-10PC-1.8<br>AT24C01A-10SC-1.8<br>AT24C01A-10MC-1.8<br>AT24C01A-10TC-1.8 | 8P3<br>8S1<br>8M<br>8T | Commercial<br>(0°C to 70°C)   |
|                        | 800                           | 3                             | 100                | AT24C01A-10PI-1.8<br>AT24C01A-10SI-1.8<br>AT24C01A-10MI-1.8<br>AT24C01A-10TI-1.8 | 8P3<br>8S1<br>8M<br>8T | Industrial<br>(-40°C to 85°C) |

| Package Type |                                                                   |
|--------------|-------------------------------------------------------------------|
| <b>8M</b>    | 8-Lead, 0.118" Wide, Miniature Small Outline Package (MSOP)       |
| <b>8P3</b>   | 8-Lead, 0.300" Wide, Plastic Dual Inline Package (PDIP)           |
| <b>8S1</b>   | 8-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (JEDEC SOIC) |
| <b>8T</b>    | 8-Lead, 0.170" Wide, Thin Shrink Small Outline Package (TSSOP)    |
| <b>14S</b>   | 14-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (SOIC)      |
| Options      |                                                                   |
| <b>Blank</b> | Standard Operation (4.5V to 5.5V)                                 |
| <b>-2.7</b>  | Low Voltage (2.7V to 5.5V)                                        |
| <b>-2.5</b>  | Low Voltage (2.5V to 5.5V)                                        |
| <b>-1.8</b>  | Low Voltage (1.8V to 5.5V)                                        |



## AT24C02 Ordering Information

| $t_{WR}$ (max)<br>(ms) | $I_{CC}$ (max)<br>( $\mu A$ ) | $I_{SB}$ (max)<br>( $\mu A$ ) | $f_{MAX}$<br>(kHz) | Ordering Code                                                                                     | Package                       | Operation Range               |
|------------------------|-------------------------------|-------------------------------|--------------------|---------------------------------------------------------------------------------------------------|-------------------------------|-------------------------------|
| 10                     | 3000                          | 18                            | 400                | AT24C02-10PC<br>AT24C02N-10SC<br>AT24C02-10SC<br>AT24C02-10MC<br>AT24C02-10TC                     | 8P3<br>8S1<br>14S<br>8M<br>8T | Commercial<br>(0°C to 70°C)   |
|                        | 3000                          | 18                            | 400                | AT24C02-10PI<br>AT24C02N-10SI<br>AT24C02-10SI<br>AT24C02-10MI<br>AT24C02-10TI                     | 8P3<br>8S1<br>14S<br>8M<br>8T | Industrial<br>(-40°C to 85°C) |
| 10                     | 1500                          | 4                             | 100                | AT24C02-10PC-2.7<br>AT24C02N-10SC-2.7<br>AT24C02-10SC-2.7<br>AT24C02-10MC-2.7<br>AT24C02-10TC-2.7 | 8P3<br>8S1<br>14S<br>8M<br>8T | Commercial<br>(0°C to 70°C)   |
|                        | 1500                          | 4                             | 100                | AT24C02-10PI-2.7<br>AT24C02N-10SI-2.7<br>AT24C02-10SI-2.7<br>AT24C02-10MI-2.7<br>AT24C02-10TI-2.7 | 8P3<br>8S1<br>14S<br>8M<br>8T | Industrial<br>(-40°C to 85°C) |

| Package Type |                                                                   |
|--------------|-------------------------------------------------------------------|
| <b>8M</b>    | 8-Lead, 0.118" Wide, Miniature Small Outline Package (MSOP)       |
| <b>8P3</b>   | 8-Lead, 0.300" Wide, Plastic Dual Inline Package (PDIP)           |
| <b>8S1</b>   | 8-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (JEDEC SOIC) |
| <b>8T</b>    | 8-Lead, 0.170" Wide, Thin Shrink Small Outline Package (TSSOP)    |
| <b>14S</b>   | 14-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (SOIC)      |
| Options      |                                                                   |
| <b>Blank</b> | Standard Operation (4.5V to 5.5V)                                 |
| <b>-2.7</b>  | Low Voltage (2.7V to 5.5V)                                        |
| <b>-2.5</b>  | Low Voltage (2.5V to 5.5V)                                        |
| <b>-1.8</b>  | Low Voltage (1.8V to 5.5V)                                        |

## AT24C02 Ordering Information (Continued)

| $t_{WR}$ (max)<br>(ms) | $I_{CC}$ (max)<br>( $\mu A$ ) | $I_{SB}$ (max)<br>( $\mu A$ ) | $f_{MAX}$<br>(kHz) | Ordering Code                                                                                     | Package                       | Operation Range               |
|------------------------|-------------------------------|-------------------------------|--------------------|---------------------------------------------------------------------------------------------------|-------------------------------|-------------------------------|
| 10                     | 1000                          | 4                             | 100                | AT24C02-10PC-2.5<br>AT24C02N-10SC-2.5<br>AT24C02-10SC-2.5<br>AT24C02-10MC-2.5<br>AT24C02-10TC-2.5 | 8P3<br>8S1<br>14S<br>8M<br>8T | Commercial<br>(0°C to 70°C)   |
|                        | 1000                          | 4                             | 100                | AT24C02-10PI-2.5<br>AT24C02N-10SI-2.5<br>AT24C02-10SI-2.5<br>AT24C02-10MI-2.5<br>AT24C02-10TI-2.5 | 8P3<br>8S1<br>14S<br>8M<br>8T | Industrial<br>(-40°C to 85°C) |
| 10                     | 800                           | 3                             | 100                | AT24C02-10PC-1.8<br>AT24C02N-10SC-1.8<br>AT24C02-10SC-1.8<br>AT24C02-10MC-1.8<br>AT24C02-10TC-1.8 | 8P3<br>8S1<br>14S<br>8M<br>8T | Commercial<br>(0°C to 70°C)   |
|                        | 800                           | 3                             | 100                | AT24C02-10PI-1.8<br>AT24C02N-10SI-1.8<br>AT24C02-10SI-1.8<br>AT24C02-10MI-1.8<br>AT24C02-10TI-1.8 | 8P3<br>8S1<br>14S<br>8M<br>8T | Industrial<br>(-40°C to 85°C) |

| Package Type |                                                                   |
|--------------|-------------------------------------------------------------------|
| <b>8M</b>    | 8-Lead, 0.118" Wide, Miniature Small Outline Package (MSOP)       |
| <b>8P3</b>   | 8-Lead, 0.300" Wide, Plastic Dual Inline Package (PDIP)           |
| <b>8S1</b>   | 8-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (JEDEC SOIC) |
| <b>8T</b>    | 8-Lead, 0.170" Wide, Thin Shrink Small Outline Package (TSSOP)    |
| <b>14S</b>   | 14-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (SOIC)      |
| Options      |                                                                   |
| <b>Blank</b> | Standard Operation (4.5V to 5.5V)                                 |
| <b>-2.7</b>  | Low Voltage (2.7V to 5.5V)                                        |
| <b>-2.5</b>  | Low Voltage (2.5V to 5.5V)                                        |
| <b>-1.8</b>  | Low Voltage (1.8V to 5.5V)                                        |



## AT24C04 Ordering Information

| $t_{WR}$ (max)<br>(ms) | $I_{CC}$ (max)<br>( $\mu A$ ) | $I_{SB}$ (max)<br>( $\mu A$ ) | $f_{MAX}$<br>(kHz) | Ordering Code                                                                 | Package                 | Operation Range               |
|------------------------|-------------------------------|-------------------------------|--------------------|-------------------------------------------------------------------------------|-------------------------|-------------------------------|
| 10                     | 3000                          | 18                            | 400                | AT24C04-10PC<br>AT24C04N-10SC<br>AT24C04-10SC<br>AT24C04-10TC                 | 8P3<br>8S1<br>14S<br>8T | Commercial<br>(0°C to 70°C)   |
|                        | 3000                          | 18                            | 400                | AT24C04-10PI<br>AT24C04N-10SI<br>AT24C04-10SI<br>AT24C04-10TI                 | 8P3<br>8S1<br>14S<br>8T | Industrial<br>(-40°C to 85°C) |
| 10                     | 1500                          | 4                             | 100                | AT24C04-10PC-2.7<br>AT24C04N-10SC-2.7<br>AT24C04-10SC-2.7<br>AT24C04-10TC-2.7 | 8P3<br>8S1<br>14S<br>8T | Commercial<br>(0°C to 70°C)   |
|                        | 1500                          | 4                             | 100                | AT24C04-10PI-2.7<br>AT24C04N-10SI-2.7<br>AT24C04-10SI-2.7<br>AT24C04-10TI-2.7 | 8P3<br>8S1<br>14S<br>8T | Industrial<br>(-40°C to 85°C) |

| Package Type |                                                                   |
|--------------|-------------------------------------------------------------------|
| <b>8P3</b>   | 8-Lead, 0.300" Wide, Plastic Dual Inline Package (PDIP)           |
| <b>8S1</b>   | 8-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (JEDEC SOIC) |
| <b>8T</b>    | 8-Lead, 0.170" Wide, Thin Shrink Small Outline Package (TSSOP)    |
| <b>14S</b>   | 14-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (SOIC)      |
| Options      |                                                                   |
| <b>Blank</b> | Standard Operation (4.5V to 5.5V)                                 |
| <b>-2.7</b>  | Low Voltage (2.7V to 5.5V)                                        |
| <b>-2.5</b>  | Low Voltage (2.5V to 5.5V)                                        |
| <b>-1.8</b>  | Low Voltage (1.8V to 5.5V)                                        |

## AT24C04 Ordering Information (Continued)

| $t_{WR}$ (max)<br>(ms) | $I_{CC}$ (max)<br>( $\mu A$ ) | $I_{SB}$ (max)<br>( $\mu A$ ) | $f_{MAX}$<br>(kHz) | Ordering Code     | Package | Operation Range               |
|------------------------|-------------------------------|-------------------------------|--------------------|-------------------|---------|-------------------------------|
| 10                     | 1000                          | 4                             | 100                | AT24C04-10PC-2.5  | 8P3     | Commercial<br>(0°C to 70°C)   |
|                        |                               |                               |                    | AT24C04N-10SC-2.5 | 8S1     |                               |
|                        |                               |                               |                    | AT24C04-10SC-2.5  | 14S     |                               |
|                        |                               |                               |                    | AT24C04-10TC-2.5  | 8T      |                               |
| 10                     | 1000                          | 4                             | 100                | AT24C04-10PI-2.5  | 8P3     | Industrial<br>(-40°C to 85°C) |
|                        |                               |                               |                    | AT24C04N-10SI-2.5 | 8S1     |                               |
|                        |                               |                               |                    | AT24C04-10SI-2.5  | 14S     |                               |
|                        |                               |                               |                    | AT24C04-10TI-2.5  | 8T      |                               |
| 10                     | 800                           | 3                             | 100                | AT24C04-10PC-1.8  | 8P3     | Commercial<br>(0°C to 70°C)   |
|                        |                               |                               |                    | AT24C04N-10SC-1.8 | 8S1     |                               |
|                        |                               |                               |                    | AT24C04-10SC-1.8  | 14S     |                               |
|                        |                               |                               |                    | AT24C04-10TC-1.8  | 8T      |                               |
| 10                     | 800                           | 3                             | 100                | AT24C04-10PI-1.8  | 8P3     | Industrial<br>(-40°C to 85°C) |
|                        |                               |                               |                    | AT24C04N-10SI-1.8 | 8S1     |                               |
|                        |                               |                               |                    | AT24C04-10SI-1.8  | 14S     |                               |
|                        |                               |                               |                    | AT24C04-10TI-1.8  | 8T      |                               |

| Package Type |                                                                   |
|--------------|-------------------------------------------------------------------|
| <b>8P3</b>   | 8-Lead, 0.300" Wide, Plastic Dual Inline Package (PDIP)           |
| <b>8S1</b>   | 8-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (JEDEC SOIC) |
| <b>8T</b>    | 8-Lead, 0.170" Wide, Thin Shrink Small Outline Package (TSSOP)    |
| <b>14S</b>   | 14-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (SOIC)      |
| Options      |                                                                   |
| <b>Blank</b> | Standard Operation (4.5V to 5.5V)                                 |
| <b>-2.7</b>  | Low Voltage (2.7V to 5.5V)                                        |
| <b>-2.5</b>  | Low Voltage (2.5V to 5.5V)                                        |
| <b>-1.8</b>  | Low Voltage (1.8V to 5.5V)                                        |



## AT24C08 Ordering Information

| $t_{WR}$ (max)<br>(ms) | $I_{CC}$ (max)<br>( $\mu A$ ) | $I_{SB}$ (max)<br>( $\mu A$ ) | $f_{MAX}$<br>(kHz) | Ordering Code                                                                 | Package                 | Operation Range               |
|------------------------|-------------------------------|-------------------------------|--------------------|-------------------------------------------------------------------------------|-------------------------|-------------------------------|
| 10                     | 3000                          | 18                            | 400                | AT24C08-10PC<br>AT24C08N-10SC<br>AT24C08-10SC<br>AT24C08-10TC                 | 8P3<br>8S1<br>14S<br>8T | Commercial<br>(0°C to 70°C)   |
|                        | 3000                          | 18                            | 400                | AT24C08-10PI<br>AT24C08N-10SI<br>AT24C08-10SI<br>AT24C08-10TI                 | 8P3<br>8S1<br>14S<br>8T | Industrial<br>(-40°C to 85°C) |
| 10                     | 1500                          | 4                             | 100                | AT24C08-10PC-2.7<br>AT24C08N-10SC-2.7<br>AT24C08-10SC-2.7<br>AT24C08-10TC-2.7 | 8P3<br>8S1<br>14S<br>8T | Commercial<br>(0°C to 70°C)   |
|                        | 1500                          | 4                             | 100                | AT24C08-10PI-2.7<br>AT24C08N-10SI-2.7<br>AT24C08-10SI-2.7<br>AT24C08-10TI-2.7 | 8P3<br>8S1<br>14S<br>8T | Industrial<br>(-40°C to 85°C) |

| Package Type |                                                                   |
|--------------|-------------------------------------------------------------------|
| <b>8P3</b>   | 8-Lead, 0.300" Wide, Plastic Dual Inline Package (PDIP)           |
| <b>8S1</b>   | 8-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (JEDEC SOIC) |
| <b>8T</b>    | 8-Lead, 0.170" Wide, Thin Shrink Small Outline Package (TSSOP)    |
| <b>14S</b>   | 14-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (SOIC)      |
| Options      |                                                                   |
| <b>Blank</b> | Standard Operation (4.5V to 5.5V)                                 |
| <b>-2.7</b>  | Low Voltage (2.7V to 5.5V)                                        |
| <b>-2.5</b>  | Low Voltage (2.5V to 5.5V)                                        |
| <b>-1.8</b>  | Low Voltage (1.8V to 5.5V)                                        |

## AT24C08 Ordering Information (Continued)

| $t_{WR}$ (max)<br>(ms) | $I_{CC}$ (max)<br>( $\mu A$ ) | $I_{SB}$ (max)<br>( $\mu A$ ) | $f_{MAX}$<br>(kHz) | Ordering Code     | Package | Operation Range               |
|------------------------|-------------------------------|-------------------------------|--------------------|-------------------|---------|-------------------------------|
| 10                     | 1000                          | 4                             | 100                | AT24C08-10PC-2.5  | 8P3     | Commercial<br>(0°C to 70°C)   |
|                        |                               |                               |                    | AT24C08N-10SC-2.5 | 8S1     |                               |
|                        |                               |                               |                    | AT24C08-10SC-2.5  | 14S     |                               |
|                        |                               |                               |                    | AT24C08-10TC-2.5  | 8T      |                               |
| 10                     | 1000                          | 4                             | 100                | AT24C08-10PI-2.5  | 8P3     | Industrial<br>(-40°C to 85°C) |
|                        |                               |                               |                    | AT24C08N-10SI-2.5 | 8S1     |                               |
|                        |                               |                               |                    | AT24C08-10SI-2.5  | 14S     |                               |
|                        |                               |                               |                    | AT24C08-10TI-2.5  | 8T      |                               |
| 10                     | 800                           | 3                             | 100                | AT24C08-10PC-1.8  | 8P3     | Commercial<br>(0°C to 70°C)   |
|                        |                               |                               |                    | AT24C08N-10SC-1.8 | 8S1     |                               |
|                        |                               |                               |                    | AT24C08-10SC-1.8  | 14S     |                               |
|                        |                               |                               |                    | AT24C08-10TC-1.8  | 8T      |                               |
| 10                     | 800                           | 3                             | 100                | AT24C08-10PI-1.8  | 8P3     | Industrial<br>(-40°C to 85°C) |
|                        |                               |                               |                    | AT24C08N-10SI-1.8 | 8S1     |                               |
|                        |                               |                               |                    | AT24C08-10SI-1.8  | 14S     |                               |
|                        |                               |                               |                    | AT24C08-10TI-1.8  | 8T      |                               |

| Package Type |                                                                   |
|--------------|-------------------------------------------------------------------|
| <b>8P3</b>   | 8-Lead, 0.300" Wide, Plastic Dual Inline Package (PDIP)           |
| <b>8S1</b>   | 8-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (JEDEC SOIC) |
| <b>8T</b>    | 8-Lead, 0.170" Wide, Thin Shrink Small Outline Package (TSSOP)    |
| <b>14S</b>   | 14-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (SOIC)      |
| Options      |                                                                   |
| <b>Blank</b> | Standard Operation (4.5V to 5.5V)                                 |
| <b>-2.7</b>  | Low Voltage (2.7V to 5.5V)                                        |
| <b>-2.5</b>  | Low Voltage (2.5V to 5.5V)                                        |
| <b>-1.8</b>  | Low Voltage (1.8V to 5.5V)                                        |



## AT24C16 Ordering Information

| $t_{WR}$ (max)<br>(ms) | $I_{CC}$ (max)<br>( $\mu A$ ) | $I_{SB}$ (max)<br>( $\mu A$ ) | $f_{MAX}$<br>(kHz) | Ordering Code                                                                 | Package                 | Operation Range               |
|------------------------|-------------------------------|-------------------------------|--------------------|-------------------------------------------------------------------------------|-------------------------|-------------------------------|
| 10                     | 3000                          | 18                            | 400                | AT24C16-10PC<br>AT24C16N-10SC<br>AT24C16-10SC<br>AT24C16-10TC                 | 8P3<br>8S1<br>14S<br>8T | Commercial<br>(0°C to 70°C)   |
|                        | 3000                          | 18                            | 400                | AT24C16-10PI<br>AT24C16N-10SI<br>AT24C16-10SI<br>AT24C16-10TI                 | 8P3<br>8S1<br>14S<br>8T | Industrial<br>(-40°C to 85°C) |
| 10                     | 1500                          | 4                             | 100                | AT24C16-10PC-2.7<br>AT24C16N-10SC-2.7<br>AT24C16-10SC-2.7<br>AT24C16-10TC-2.7 | 8P3<br>8S1<br>14S<br>8T | Commercial<br>(0°C to 70°C)   |
|                        | 1500                          | 4                             | 100                | AT24C16-10PI-2.7<br>AT24C16N-10SI-2.7<br>AT24C16-10SI-2.7<br>AT24C16-10TI-2.7 | 8P3<br>8S1<br>14S<br>8T | Industrial<br>(-40°C to 85°C) |

| Package Type |                                                                   |
|--------------|-------------------------------------------------------------------|
| <b>8P3</b>   | 8-Lead, 0.300" Wide, Plastic Dual Inline Package (PDIP)           |
| <b>8S1</b>   | 8-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (JEDEC SOIC) |
| <b>8T</b>    | 8-Lead, 0.170" Wide, Thin Shrink Small Outline Package (TSSOP)    |
| <b>14S</b>   | 14-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (SOIC)      |
| Options      |                                                                   |
| <b>Blank</b> | Standard Operation (4.5V to 5.5V)                                 |
| <b>-2.7</b>  | Low Voltage (2.7V to 5.5V)                                        |
| <b>-2.5</b>  | Low Voltage (2.5V to 5.5V)                                        |
| <b>-1.8</b>  | Low Voltage (1.8V to 5.5V)                                        |

## AT24C16 Ordering Information (Continued)

| $t_{WR}$ (max)<br>(ms) | $I_{CC}$ (max)<br>( $\mu A$ ) | $I_{SB}$ (max)<br>( $\mu A$ ) | $f_{MAX}$<br>(kHz) | Ordering Code     | Package | Operation Range               |
|------------------------|-------------------------------|-------------------------------|--------------------|-------------------|---------|-------------------------------|
| 10                     | 1000                          | 4                             | 100                | AT24C16-10PC-2.5  | 8P3     | Commercial<br>(0°C to 70°C)   |
|                        |                               |                               |                    | AT24C16N-10SC-2.5 | 8S1     |                               |
|                        |                               |                               |                    | AT24C16-10SC-2.5  | 14S     |                               |
|                        |                               |                               |                    | AT24C16-10TC-2.5  | 8T      |                               |
| 10                     | 1000                          | 4                             | 100                | AT24C16-10PI-2.5  | 8P3     | Industrial<br>(-40°C to 85°C) |
|                        |                               |                               |                    | AT24C16N-10SI-2.5 | 8S1     |                               |
|                        |                               |                               |                    | AT24C16-10SI-2.5  | 14S     |                               |
|                        |                               |                               |                    | AT24C16-10TI-2.5  | 8T      |                               |
| 10                     | 800                           | 3                             | 100                | AT24C16-10PC-1.8  | 8P3     | Commercial<br>(0°C to 70°C)   |
|                        |                               |                               |                    | AT24C16N-10SC-1.8 | 8S1     |                               |
|                        |                               |                               |                    | AT24C16-10SC-1.8  | 14S     |                               |
|                        |                               |                               |                    | AT24C16-10TC-1.8  | 8T      |                               |
| 10                     | 800                           | 3                             | 100                | AT24C16-10PI-1.8  | 8P3     | Industrial<br>(-40°C to 85°C) |
|                        |                               |                               |                    | AT24C16N-10SI-1.8 | 8S1     |                               |
|                        |                               |                               |                    | AT24C16-10SI-1.8  | 14S     |                               |
|                        |                               |                               |                    | AT24C16-10TI-1.8  | 8T      |                               |


| Package Type |                                                                   |
|--------------|-------------------------------------------------------------------|
| <b>8P3</b>   | 8-Lead, 0.300" Wide, Plastic Dual Inline Package (PDIP)           |
| <b>8S1</b>   | 8-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (JEDEC SOIC) |
| <b>8T</b>    | 8-Lead, 0.170" Wide, Thin Shrink Small Outline Package (TSSOP)    |
| <b>14S</b>   | 14-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (SOIC)      |
| Options      |                                                                   |
| <b>Blank</b> | Standard Operation (4.5V to 5.5V)                                 |
| <b>-2.7</b>  | Low Voltage (2.7V to 5.5V)                                        |
| <b>-2.5</b>  | Low Voltage (2.5V to 5.5V)                                        |
| <b>-1.8</b>  | Low Voltage (1.8V to 5.5V)                                        |

## Packaging Information

### 8P3, 8-Lead, 0.300" Wide, Plastic Dual Inline Package (PDIP)


Dimensions in Inches and (Millimeters)

JEDEC STANDARD MS-001 BA




### 8S1, 8-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (JEDEC SOIC)

Dimensions in Inches and (Millimeters)




### 14S, 14-Lead, 0.150" Wide, Plastic Gull Wing Small Outline (SOIC)

Dimensions in Inches and (Millimeters)



### 8M, 8-Lead, 0.118" Wide, Miniature Small Outline (MSOP)

Dimensions in Millimeters and (Inches)




\* Controlling dimension: millimeters

## Packaging Information

**8T, 8-Lead, Plastic Thin Small Outline Package (TSOP)**

Dimensions in Millimeters and (Inches)\*



\*Controlling dimension: millimeters