



1107B Series

Single Color PLCC-4 Bathtub Type
(High Reliability type, V-Series)

Product features

Package	PLCC-4 Bathtub Type. Water clear epoxy	
Product features	• Outer Dimension 3.5 x 2.8 x 1.9mm(L x W x H) • Wide operation temperature range Storage Temperature : -40℃~110℃ Operating Temperature : -40℃~100℃ Operation Guarantee • Ramification of luminosity group sorting. It is possible to have a uniform transmission with little irregularities even when several are lined up. • Systematization of luminosity groups and color tone groups. Unified to a simple standard. • Corresponding to a use requiring high reliability in cars etc... • Through heat dissipation design, a maximum forward current of $I_F=30\text{mA}(\text{InGaP})$, $I_F=70\text{mA}(\text{AlInGaP})$ is made possible, and a high luminosity is then possible. • Spatial distribution characteristics. (201/2 : 120deg) • No lead package and lead-free soldering compatible • RoHS compliant	
Dominant wavelength	Blue : 469nm (VUB) Green : 528nm (VUG) , 560nm(VYBG) Yellow-Green : 573nm (VYPY) Yellow : 589nm (VFX) Orange : 606nm (VFA) Red : 633nm (VFR)	
Spatial distribution	120 deg.	
Die materials	VUB,VUG : InGaP VYBG, VYPY, VFX, VFA, VFR :AlGaInP	
Optical efficiency	VUB : 4.3 lm/W VFX : 14.3 lm/W VUG : 17.1 lm/W VFA : 14.3 lm/W VYBG : 1.8 lm/W VFR : 12.9 lm/W VYPY : 6.8 lm/W	
Rank grouping parameter	Sorted by luminous intensity and wavelength and taped according to rank.	
Assembly methods (customer)	Corresponding to surface mounter.	
Soldering methods	Corresponding to reflow soldering and manual soldering.	
Taping dimensions	2,000pcs(standard)per reel in a 8mm width tape. Reel diameter:Φ180mm	
ESD	AlInGaP:2kV (HBM) InGaP:1kV (HBM)	

Recommended Applications

SW lighting for car indicators, meter panel, car audio and heater control, etc...



1107B Series

Single Color PLCC-4 Bathtub Type
(High Reliability type, V-Series)

(T=25°C)

Color Variations and Luminous Intensity

Part No.	Material	Emitted Color	Lens Color	Dominant Wavelength		Luminous Intensity			Luminous Flux	
				λ_d (nm)		I_v (mcd)			Φ_v (lm)	
				TYP.	I_F	MIN.	MAX.	I_F	TYP.	I_F
VUB1107B	InGaP	Blue	Water Clear	469	30	56	220	30	450	30
VUG1107B	InGaP	Green		528	30	150	560	30	1,800	30
VYBG1107B	AlGaInP			560	50	27	100	50	200	50
VYPY1107B	AlGaInP	Yellow-Green		573	50	100	330	50	750	50
VFY1107B	AlGaInP	Yellow		589	50	270	820	50	1,500	50
VFA1107B	AlGaInP	Orange		606	50	390	1,000	50	1,500	50
VFR1107B	AlGaInP	Red		633	50	180	560	50	1,350	50

※Note : The luminous intensity(I_v) and dominant wavelength(λ_d) above are the setup values of the sorting machine.
(Tolerance : I_v ... +10%, λ_d ... ± 1 nm)

Absolute Maximum Ratings

Item	Symbol	Absolute Maximum Ratings							Unit
		VUB	VUG	VYBG	VYPY	VFY	VFA	VFR	
Power Dissipation	P _d	120	120	196	196	196	196	196	mW
Forward Current	I _F	30	30	70	70	70	70	70	mA
Pulse Forward Current ※1	I _{FRM}	100	100	100	100	100	100	100	mA
Derating (Ta=65℃ or higher)	ΔI _F	0.6 ※2	0.6 ※2	1.27	1.27	1.27	1.27	1.27	mA/℃
	ΔI _{FRM}	2.0 ※2	2.0 ※2	1.82	1.82	1.82	1.82	1.82	mA/℃
Reverse Voltage	V _R	5	5	5	5	5	5	5	V
Operating Temperature	T _{opr}	-40 ~ +100							℃
Storage Temperature	T _{stg}	-40 ~ +110							℃

※1 I_{FRM} Measurement condition : Pulse Width ≦ 1ms., Duty ≦ 1/20.

※2 Temperature Condition: Ta=60℃ or higher.

Thermal Characteristics

Item	Symbol	Ratings							Unit
		VUB	VUG	VYBG	VYPY	VFY	VFA	VFR	
Junction Temperature (MAX.)	T _j	110	110	120	120	120	120	120	℃
Thermal Resistance (TYP.) (Junction/ Solder Point)	R _(th J-S)	220	220	280	280	280	280	280	℃/W

※R_(th J-S) Measurement Condition / Substrate: FR4(t=1.6mm) Pattern Size: 16mm².

Electro-Optical Characteristics (VUB,VUG)

Item	Conditions	Symbol	Characteristic Ratings		Unit
			VUB	VUG	
Forward Voltage	I _F =30mA	V _F	TYP.	3.5	V
			MAX.	4.0	
Reverse Current	V _R =5V	I _R	MAX.	100	μA
Peak Wavelength	I _F =30mA	λ _p	TYP.	464	nm
Dominant Wavelength	I _F =30mA	λ _d	TYP.	469	nm
Spectral Line Half Width	I _F =30mA	Δλ	TYP.	26	nm
Half Intensity Angle	I _F =30mA	2θ _{1/2}	TYP.	120	deg.

※Note: The dominant wave length (λ_d) above is the setup value of the sorting machine.
(Tolerance: λ_d ...± 1nm)

Electro-Optical Characteristics (VYBG, VYPY, VFY, VFA, VFR)

(T=25℃)

Item	Conditions	Symbol	Characteristic Rating					Unit
			VYBG	VYPY	VFY	VFA	VFR	
Forward Voltage	I _F =50mA	V _F	TYP.	2.2	2.2	2.1	2.1	V
			MAX.	2.6	2.6	2.6	2.6	
Reverse Current	V _R =5V	I _R	MAX.	100	100	100	100	μA
Peak Wavelength	I _F =50mA	λ _p	TYP.	567	577	594	611	nm
Dominant Wavelength	I _F =50mA	λ _d	TYP.	560	573	589	606	nm
Spectral Line Half Width	I _F =50mA	Δλ	TYP.	16	16	15	15	nm
Half Intensity Angle	I _F =50mA	2θ _{1/2}	TYP.	120	120	120	120	deg.

※Note: The dominant wave length (λ_d) above is the setup value of the sorting machine.
(Tolerance: λ_d ...± 1nm)

Luminous Intensity Rank

Standard Chart(Unit: mcd)


Rank	I _v (mcd)		VUB	VUG	VYBG	VYPY	VFY	VFA	VFR
	MIN.	MAX.	I _F =30mA		I _F =50mA				
B2	12	15							
B3	15	18							
B4	18	22							
B5	22	27							
B6	27	33			B6				
B7	33	39							
B8	39	47							
B9	47	56							
BX	56	68	BX						
BY	68	82			BZ				
BZ	82	100							
C1	100	120				C1			
C2	120	150							
C3	150	180		C3					
C4	180	220	C4						C4
C5	220	270							
C6	270	330			C6	C6			
C7	330	390							
C8	390	470		C9				C8	
C9	470	560							C9
CX	560	680							
CY	680	820				CY			
CZ	820	1,000					CZ		
D1	1,000	1,200							
D2	1,200	1,500							
D3	1,500	1,800							
D4	1,800	2,200							
D5	2,200	2,700							

※ Limited width of luminous intensity rank is from Min.4 rank width.

Color Tone Groups (A d)

(unit: nm)

Tolerance: +/-1nm



VUB Type (I_F=30mA)

	A	B	C	D
MIN.	460.0	464.0	468.0	472.0
MAX.	464.0	468.0	472.0	476.0

VUG Type (I_F=30mA)

	A	B	C	D
MIN.	515.0	520.0	525.0	530.0
MAX.	520.0	525.0	530.0	535.0

VYBG Type (I_F=50mA)

	B	C	D
MIN.	555.0	558.0	561.0
MAX.	558.0	561.0	564.0

VYPY Type (I_F=50mA)

	A	B	C
MIN.	567.0	570.0	573.0
MAX.	570.0	573.0	576.0

VFY Type (I_F=50mA)

	D	E	F
MIN.	586.0	589.0	592.0
MAX.	589.0	592.0	595.0

VFA Type (I_F=50mA)





	C	D	E
MIN.	603.0	606.0	609.0
MAX.	606.0	609.0	612.0

VFR Type (I_F=50mA)





	A	B	C
MIN.	620.0	626.0	632.0
MAX.	626.0	632.0	638.0

✳ Limited width of luminous intensity rank is from Min.5 to Min.6 rank width.
(It changes with product.)





Characteristic Graph (VUB,VUG)







Characteristics Chart(VUB,VUG)







Characteristics Chart(VYBG,VYPY)







Characteristics Chart(VYBG,VYPY)



Characteristics Chart(VFY,VFA,VFR)



Characteristics Chart(VFY,VFA,VFR)



**Pb-free
HEAT**

1107B Series


Single Color PLCC-4 Bathtub Type
(High Reliability type, V-Series)

Package Dimensions

(Unit: mm)


Weight: (36.5)mg

Tolerance: ± 0.2



Recommended Soldering Pattern


(Unit: mm)




Taping Specification

(Unit: mm)

Quantity: 2,000pcs/ reel (standard)



Reflow Soldering Conditions



- 1) The above profile temperature gives the maximum temperature of the LED resin surface. Please set the temperature so as to avoid exceeding this range.
- 2) Total times of reflow soldering process shall be no more than 2 times. When the second reflow soldering process is performed, intervals between the first and second reflow should be short as possible (while allowing some time for the component to return to normal temperature after the first reflow) in order to prevent the LED from absorbing moisture.
- 3) Temperature fluctuation to the LED during the pre-heating process shall be minimized. (6°C maximum)

Manual Soldering Conditions

Iron tip temp.	350 °C	(MAX.)
Soldering time and frequency	3 s	(MAX.)
	1 time	(MAX.)

Special Notice to Customers Using the Products and Technical Information Shown in This Data Sheet

- 1) The technical information shown in the data sheets are limited to the typical characteristics and circuit examples of the referenced products. It does not constitute the warranting of industrial property nor the granting of any license.
- 2) For the purpose of product improvement, the specifications, characteristics and technical data described in the data sheets are subject to change without prior notice. Therefore it is recommended that the most updated specifications be used in your design.
- 3) When using the products described in the data sheets, please adhere to the maximum ratings for operating voltage, heat dissipation characteristics, and other precautions for use. We are not responsible for any damage which may occur if these specifications are exceeded.
- 4) The products described in the data sheets are made to be used in standard electronic applications such as office automation appliances, communication devices, audio visual, home appliances, and measuring instruments.
- 5) If the products in the data sheets are to be used for purposes other than the above which requires high level reliability and safety where failure and or malfunction of the product may cause death or other serious effects on the human body such as airplane, space activity, transportation, medical, nuclear), please contact our sales personnel.
- 6) In order to export the products or technologies described in this data sheet which are under the "Foreign Exchange and Foreign Trade Control Law," it is necessary to first obtain an export permit from the Japanese government.
- 7) No part of this data sheet may be reprinted or reproduced without prior written permission from Stanley Electric Co., Ltd.
- 8) The most updated edition of this data sheet can be obtained from the address below:
<http://www.stanley-components.com>