





All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

CODE	DIM "M" MATING LENGTH	CONTACT TYPE
G	.220 [5.59]	SIGNAL
H	.220 [5.59]	SIGNAL
R	.270 [6.86]	SIGNAL
S	.270 [6.86]	SIGNAL
T	.270 [6.86]	SIGNAL
U	.270 [6.86]	SIGNAL
PA	N/A [N/A]	POWER
X	OMITTED	OMITTED

PRODUCT NO.	ROWS	POWER						SIGNAL								POWER				
		E1	P1	P2	P3	P4	P5	P6	1	2	3	4	5	6	7	8	P7	P8	P9	E2
51935-002-- NOTE: ③	D C B A		PA	PA	PA	PA	PA	PA	X	H	U	U	X	X	X	X	PA	PA	PA	
									X	T	G	T	X	X	X	X				
									X	S	S	S	X	X	X	X				
									X	R	R	R	X	X	X	X				



mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
litr	ecn no.	dr	date					COPY				title	
A	V20024	DAI	01/18/02	linear		.XX±.01/0.X±0.3		projection				6P + 32S + 3P	
B	V20464	DAI	03/07/02			.XXX±.005/0.XX±0.13						RIGHT ANGLE SOLDER HEADER w/ GUIDE POST	
C	V21561	CGD	10/02/02	angles		.XXX±.002/0.XXX±0.051							
D	DG05-0216	SJ	07/11/05	dr		0°±2°							
E	DG06-0005	JMG	01/07/06	enrg		D. INGRAM 01/18/02		INCH/MM				product family	PwrBlade
F	DG08-0273	WD	12/24/08	chr		M.MOSTOLLER 01/18/02		scale				size	dwg no
				appd		M.MOSTOLLER 01/18/02		1:1				A	51935-002
sheet index	revision	F	F	F	F								code
	sheet	1	2	3	4								213
													sheet 1 of 4

Pro/E



cage code 22526

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.


PRODUCT NUMBER
51935-002--
NOTE: ③



SECTION C-C



SECTION A-A



SECTION B-B

mat'l code SEE NOTE 2				tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
ltr	ecn no.	dr	date	linear	.XX±.01/0.X±0.3	COPY			title 6P + 32S + 3P RIGHT ANGLE SOLDER HEADER w/ GUIDE POST
F					.XXX±.005/0.XX±0.13	projection			
					.XXXX±.0020/0.XXX±0.051				
				angles	0°±2°			product family PwrBlade	code 213
				dr	D. INGRAM 01/18/02	scale 1:1			
				enrg	M.MOSTOLLER 01/18/02			size	dwg no 51935-002
				chr	M.MOSTOLLER 01/18/02			A	sheet 2 of 4
				appd	M.MOSTOLLER 01/18/02				
sheet index	revision sheet								

Pro/E



B

A

[illegible]

—

cage code	22526
-----------	-------

•

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

PRODUCT NUMBER
51935-002-- NOTE:③

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH
ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTORS NOTES:

2. HOUSING MATERIAL: UL 94 V-0 GLASS FILLED HIGH TEMP THERMO PLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY

- △3. SEE ITEM 1 & 2 IN PRINT 10064183 FOR PLATING SPEC OF 51935-002 AND 51935-002LF RESPECTIVELY.

4. "MANUFACTURER" NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.
5. PRODUCT SPECIFICATION GS-12-149.

PCB - NOTES:

6. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.

7. HOLD DOWN THROUGH HOLES ARE UNPLATED.

8. $\varnothing.0453 \pm 0.0010$ [1.151 ± 0.025] DRILLED HOLES PLATED WITH
 0.0003 [0.008] MIN SnPb OVER $.001$ [0.03]
TO $.003$ [0.08] Cu PLATING TO ACHIEVE
 $\varnothing.040 \pm .003$ [$1.02 \pm .07$] HOLE.

9. "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.

10. A△SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED
WITH THE CURRENT DRAWING REVISION.

mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
ltr	ecn no.	dr	date					COPY					
F				linear		$.XX \pm .01 / 0.X \pm 0.3$		projection		title		6P + 32S + 3P	
						$.XXX \pm .005 / 0.XX \pm 0.13$				RIGHT ANGLE SOLDER HEADER w/ GUIDE POST			
				angles		$.XXX \pm .0020 / 0.XXX \pm 0.051$							
						$0^\circ \pm 2^\circ$							
				dr		D. INGRAM 01/18/02		INCH/MM		product family	PwrBlade	code	213
				engr		M.MOSTOLLER 01/18/02				size	dwg no	sheet	4 of 4
				chr		M.MOSTOLLER 01/18/02		scale		A	51935-002		
				appd		M.MOSTOLLER 01/18/02		1:1					
sheet index	revision sheet												

cage code 22526