




Technical drawing of a rectangular plate with dimensions and hole locations. The plate has a width of 15.24 and a height of 21.0. There are 10 holes arranged in a 2x5 grid. The horizontal distance between the center of the first hole and the center of the last hole is $(P-1) \times 10.16$. The vertical distance between the center of the top row of holes and the center of the bottom row of holes is 4.1. The horizontal distance from the left edge to the center of the first hole is 1.8. The horizontal distance from the center of the first hole to the center of the second hole is 10.16. The horizontal distance from the center of the second hole to the right edge is 2.54. The diameter of the holes is $\phi 1.60$.

Poles	Tolerance
2P-4P	±0.50
5P-8P	±0.60
10P-12P	±0.80

COLOR
0: Black
5: Green
6: Blue
8: Grey (Standard)

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.



TITLE	OSTHQ10.16mm Series (Solder pins staggered by half the pin spacing)						
PART NO.	OSTHQXX4081			DWG NO.	OSTHQXX4081.DWG		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Tony 2006.07.18	Tony 2006.07.18		UNIT: mm	X.	±0.50
					SCALE: NONE	XX	±0.30
					REV: B	XXX	±0.10
				SHEET: 01/01		X°	±1°